INCREMENTAL ENCODERS SERIES HS35R

Dynapar[™] brand

Heavy Duty Hollowshaft Encoder

Key Features

- Phased Array Sensor for Reliable Signal Output
- Rugged Design Withstands up to 400G Shock and 20G Vibration
- Unbreakable Code Disc up to 5000 PPR
- Heavy Duty Design Rated for IP67
- Customizable Mounting Options including Torque Arm with Optional Grounding Strap





SPECIFICATIONS

STANDARD OPERATING CHARACTERISTICS

Code: Incremental, Optical **Resolution:** 1 to 5000 PPR (pulses/revolution) See Ordering Information

Format: Two channel quadrature (AB) with optional Index (Z), and complementary outputs

Phase Sense: A leads B for CW shaft rotation viewing the shaft clamp end of the encoder

Quadrature Phasing: For resolutions 200 to 300 PPR and 1200 PPR and


above: $90^{\circ} \pm 30^{\circ}$ electrical; all other resolutions: $90^{\circ} \pm 15^{\circ}$


Symmetry:

For resolutions 200-300 PPR and above1024 PPR:180° $\pm 25^\circ$ electrical; all other resolutions: 180° $\pm 18^\circ$

Index: 150° to 330° A leads B, CW (from clamp end) (Reverse Phasing, A leads B for CCW also available: See Code 7 in Ordering Information)

Waveforms: Squarewave with rise and fall times less than 1 microsecond into a load capacitance of 1000 pf





Index Width: 150° to 330°

A leads B, CW (from clamp end)

(Reverse Phasing, A leads B for CCW also available: See Code 7 in Ordering Information)

ELECTRICAL Input Power: 5-26VDC, 5-15VDC. 80 mA max., not including output loads.

Outputs:

7272 Push-Pull: 40mA, sink or source 7272 Differential Line Driver: 40 mA, sink or source 7273 Open Collector: 40mA, sink max 4469 Differential Line Driver: 100mA, sink or source High-Power Mosfet Line Driver

Frequency Response: 125 kHz (data & index) Noise Immunity: Tested to EN61326-1 Electrical Immunity: Reverse polarity, short circuit protected with 7272 or 7273 line drivers only Termination: MS Connector; M12 Connector; cable exit w/seal. See Ordering Information Mating Connector:

6 pin MS, style MS3106A-14S-6S (MCN-N4) 7 pin MS, style MS3106A-16S-1S (MCN-N5) 10 pin MS, style MS3106A-18-1S (MCN-N6) 10 pin, NEMA4 style (MCN-N6N4) 10 pin Bayonet, MS3116-F12-10S (MCN-B1) 12 Pin CCW M23 Connector (MCN-C2) Cable w/ 5 pin M12 Connector (112859-XXXX) Cable w/ 8 pin M12 Connector(112860-XXXX)

Note: "MS" type mating connectors and prebuilt cables are rated NEMA 12. "M12" Cable assemblies are rated IP67

MECHANICAL

Bore Diameter: 6mm to 28mm, 1/4" to 1-1/8", electrically isolated

Mating Shaft Length: 1.25", Minimum, 1.60", Recommended

Shaft Speed: 6000 RPM, Maximum (Enclosure Rating is IP64 at speed over 5000 RPM) Starting Torque: 8.0 in-oz. maximum (at 25°C) Running Torque: 5.0 in-oz. maximum (at ambient) Bearings: ABEC 1 Housing and Cover: Powder Coated Aluminum Shaft Material: 6061-T6 Aluminum Disc Material: Mylar (unbreakable) Weight: 1.76lb (28 Oz) Typical

ENVIRONMENTAL

Standard Operating Temperature: -40 to +85°C (0 to +70°C with 4469 line driver, see "Ordering Information"). At shaft speed above 3000 RPM, derate 10°C per 1000 RPM Extended Temperature Range: -40 to +100°C (See ordering information) Storage temperature: -40 to +100°C Shock: 400G, 6mSec Vibration: 5 to 3000 Hz, 20G Humidity: Up to 98% (non-condensing) Enclosure Rating: IP67 (IP64 at shaft speed above 5000 RPM)

INCREMENTAL ENCODERS



SERIES HS35R

Ordering Information

To order, complete the model number with code numbers from the table below:

Code 1: Model	Code 2: PPF	Code 3: Bore Size	Code 4: Fixing	Code 5: Output Format	Code 6: Termination	Code 7: Options				
HS35R										
Ordering Information										
HS35R Heavy-Duty, Hollowshaft Encoder	0001 050 0003 051 0010 060 0012 090 0015 100 0032 102 0050 120 0060 150 0100 200 0120 240 0240 250 0250 307 0300 400 0360 409 500	2 1 1/4" 0 2 5/16" 0 3 8mm 0 4 3/8" 0 5 10mm 4 6 12mm 0 7 1/2" 0 8 5/8" 0 9 15mm 8 A 16mm 0 D 3/4" 0 E 20mm 2 F 7/8" 0 G 24mm 6 H 1"	 0 None 1 4.5" C-face tether 2 8.5" C-face tether 3 Slotted tether (to fit standard AC motor fan cover) Not available when Code 5 is D,E,F,G, Q, R 4 Same as 1 w/cover 5 Same as 3 w/cover C Same as A with 56C cover (Single Only) Available when Code 5 is D,E,F,G, Q, R 6 Same as 1 w/dual cover 7 Same as 3 w/dual cover 8 Same as 2 w/ 180 C-face cover (single or dual output) A Rod tether B Rod tether with ground strap. D Same as B with 56C cover (Single Output) 	 0 ABZ, 5-26VDC push-pull (7272) 1 ABZ, 5-26VDC O/C (7273) 2 ABZ, 5-26VDC O/C w2.2kOhm (7273) H Same as "0" with Extended temp range J Same as "1" with Extended temp range J Same as "2" with Extended temp range K Same as "2" with Extended temp range Not available when Code 6 is H 4 Differential AB only, 5-26VDC, 5-26VDC out (7272) 5 Differential AB only, 5-26VDC in, 5VDC out (7272) A Differential AB only, 5-26VDC in, 5VDC out (7272) A Differential AB only, 5-15VDC in, 5-15VDC out (4469) C Differential AB only, 5-15VDC in, 5-15VDC out (4469) L Same as "4" with Extended temp range M Same as "5" with Extended temp range M Same as "5" with Extended temp range Not available when Code 6 is 0, 1, 5, 6, or H 6 Differential ABZ, 5-26VDC in, 5VDC out (7272) 7 Differential ABZ, 5-26VDC in, 5-26VDC out (7272) 8 Differential ABZ, 5-26VDC in, 5-15VDC out (4469) 9 Differential ABZ, 5-15VDC in, 5-15VDC out (4469) 9 Dual isolated outputs, same as "6" F Dual isolated outputs, same as "8" G Dual isolated outputs, same as "9" N Same as "6" with Extended temp range P Same as "1" with Extended temp range P Same as "1" with Extended temp range R Same as "1" with Extended temp range R Same as "1" with Extended temp range R Same as "2" with Extended temp range R Same as "2" with Extended temp range M ABZ, 10-24VDC Line Driver for cable runs up to 500 ft/120m using the Dynapar cable assemblies listed b	 0 6 Pin Connector 1 7 Pin Connector 2 10 Pin Connector 3 12 Pin Connector 4 10 Pin Bayonet Connector 5 6 Pin+Mating Connector 6 7 Pin+Mating Connector 7 10 Pin+Mating Connector 8 12 Pin+Mating Connector 8 12 Pin+Mating Connector 9 10 Pin Bayonet+Mating Connector 9 10 Pin Bayonet+Mating Connector and Mate G 0.3m (13") Cable H 5 Pin M12 Connector J 8 Pin M12 Connector 	Blank No Option 01 Reverse Phasing (A leads B, CCW) Available when Code 5 is 0-2 and Code 6 is 0 or 5; OR Code 5 is 0-9, A-G and Code 6 is 1-2 or 6-7 PS LED Output				

Cable Assemblies with MS Connector*

108594-XXXX6 Pin MS, Cable Assy. For Use with Single Ended Outputs112123-XXXX6 Pin MS, Cable Assy. For Use with Differential Line Driver w/o Index Outputs108595-XXXX7 Pin MS, Cable Assy. For Use with Single Ended Outputs108596-XXXX7 Pin MS, Cable Assy. For Use with Differential Line Driver w/o Index Outputs100635-XXXX10 Pin MS, Cable Assy. For Use with Differential Line Driver with Index Outputs104448-XXXX10 Bayonet, Cable Assy. For Use with Differential Line Driver with Index Outputs109209-XXXXNEMA4 10 pin MS, Cable Assy. For Use with Differential Line Driver with Index Outputs

Cable Assemblies with M23 Connector*

108615-XXXX 12 M23, Cable Assy. For Use with Differential Line Driver with Index Outputs, CCW

Cable Assemblies with M12 Connector*

112859-XXXX 5 Pin M12, Cable Assy. For Use with Single Ended Outputs

112860-XXXX 8 Pin M12, Cable Assy. For Use with Single Ended Outputs

112860-XXXX 8 Pin M12, Cable Assy. For Use with Differential Line Driver Outputs

*Note: Standard cable length is 10 feet but may be ordered in any length in 5 foot increments. For example, for a 20 foot cable, replace XXXX with -0020.

Mating Connectors (no cable)

MCN-N4	6 pin, style MS3106A-14S-6S
MCN-N5	7 pin, style MS3106A-16S-1S
MCN-N6	10 pin, style MS3106A-18-1S
MCN-N6N4	10 pin, NEMA4 style
MCN-B1	10 pin bayonet, style MS3116-F12-10S
MCN-C2	12 Pin CCW M23 Connector

Accessory Kits:

114573-0001	Tether Kit, 4.5" C-Face Single Point with 3/8" Bolt
114574-0001	Tether Kit, Slotted with T-bolts for Standard
	AC Motor Fan Covers
114575-0001	Tether Kit, 8.5" C-Face Single Point with 1/2" Bolt
114591-0001	Cover Kit, 56 C-Face
114592-0001	Cover Kit, Fan Cover
114593-0001	Dual Cover Kit, 56 C-Face
114928-0001	Dual Cover Kit, 180 C-Face
114594-0001	Dual Cover Kit, Fan Cover
116233-0001	Rod Tether Only
116233-0002	Rod Tether + 56 C-Face Cover (Single)
116233-0004	Rod Tether + Grounding Strap
116233-0005	Rod Tether + Grounding Strap + 56 C-Face
	Cover (Single)

SERIES HS35R



ELECTRICAL CONNECTIONS

6, 7 & 10 Pin MS Connectors and Cables - Code 6 = 0 to 9, A to G

Connector & mate/accessory cable assembly pin numbers and wire color information is provided here for reference. Models with direct cable exit carry the same color coding as shown for each output configuration.

Cable #108594-XXXX 6 Pin Single Ended		4-XXXX Pin	Cable #112123-XXXX 6 Pin Dif Line Drv w/o Index		Cable #108596-XXXX 7 Pin Dif Line Drv w/o Index		Cable #108595-XXXX 7 Pin (If Used)				Cable #114448-XXXX 10 Pin Bayonet				Cable Exit with Seal
Function	Pin	Wire Color	Pin	Wire Color	Pin	Wire Color	Pin	Wire Color	Pin	Wire Color	Pin	Wire Color	Pin	Wire Color	Wire Color
Sig. A	E	BRN	Ε	BRN	Α	BRN	A	BRN	A	BRN	А	BRN	5	BRN	BRN
Sig. B	D	ORN	D	ORN	В	ORN	В	ORN	В	ORN	В	ORN	8	ORN	ORN
Sig. Z*	С	YEL	—	—		—	C	YEL	С	YEL	С	YEL	3	YEL	YEL
Power +V	В	RED	В	RED	D	RED	D	RED	D	RED	D	RED	12	RED	RED
N/C	F	_	—	—		—	E	—	E	_	E	_	7	_	—
Com	A	BLK	Α	BLK	F	BLK	F	BLK	F	BLK	F	BLK	10	BLK	BLK
Case	_	—	—	—	G	GRN	G	GRN	G	GRN	G	GRN	9	_	GRN
Sig. Ā	_	_	С	BRN/WHT	С	BRN/WHT	—	—	Н	BRN/WHT	Н	BRN/WHT	6	BRN/WHT	BRN/WHT
Sig. B	_	_	F	ORN/WHT	E	ORN/WHT	—	_		ORN/WHT	J	ORN/WHT	1	ORN/WHT	ORN/WHT
Sig. Z*	—	—	—	—		—	—	_	J	YEL/WHT	K	YEL/WHT	4	YEL/WHT	YEL/WHT
OV Sense	—	—	—	—	—	_	—	_	—		_	—	2	BLK/WHT	—
+V Sense	—	_	—	—	_		—	_	—	_	—	_	11	GRN	_

5 & 8 Pin M12 Accessory Cables when Code 6 = H or J

Connector pin numbers and cable assembly wire color information is provided here for reference.

Encoder Function		2859-XXXX gle Ended		112860-XXXX Single Ended	Cable # 112860-XXXX 8 Pin Differential		
	Pin	Wire Color	Pin	Wire Color	Pin	Wire Color	
Sig.A	4	BLK	1	BRN	1	BRN	
Sig.B	2	WHT	4	ORG	4	ORG	
Sig. Z*	5	GRY	6	YEL	6	YEL	
Power +V	1	BRN	2	RED	2	RED	
Com	3	BLU	7	BLK	7	BLK	
Sig. A	-	_	-	_	3	BRN/WHT	
Sig. B	_	_	_	_	5	ORG/WHT	
Sig. Z*	_	_	_	_	8	YEL/WHT	

1) Cable Configuration (Table 1): PVC jacket, 105 °C rated, overall foil shield; 3 twisted pairs 24 AWG (output signals), plus 2 twisted pairs 22 AWG (input power)

2) Cable Configuration (Table 2): PVC jacket, 105°C rated, overall foil shield; 24 AWG conductors, minimum

3) Standard cable length is 10 feet but may be ordered in any length in 5 foot increments. For example, for a 20 foot cable, replace -XXXX with -0020 4) *Index not provided on all models. See ordering information.

5) **For watertight applications, use NEMA4 10 pin cable & connector 109209-XXXX.
6) "MS" Type mating connectors and pre-build cables are rated NEMA 12


7) "M12" Cable assemblies are rated IP67

INCREMENTAL ENCODERS



SERIES HS35R

DIMENSIONS [mm]




SHOWN WITH ROD TETHER

INCREMENTAL ENCODERS

SERIES HS35R





Worldwide Brands: NorthStar™ • Dynapar™ • Hengstler™ • Harowe™

WWW.DYNAPAR.COM Headquarters: 1675 Delany Road • Gurnee, IL 60031-1282 • USA

Customer Service: Tel.: +1.800.873.8731 Fax: +1.847.662.4150 custserv@dynapar.com

Technical Support

Tel.: +1.800.234.8731 Fax: +1.847.662.4150 northstar.techsupport@dynapar.com

European Sales Representative

Hengstler GmbH Uhlandstrasse 49, 78554 Aldingen Germany www.hengstler.com

Dynapar[™] brand is a trademark of DYNAPAR. All rights reserved. Specifications subject to change without notice. Document No. 702761-0002, Rev. AB ©2019 Dynapar