



SCALANCE XC206-2SFP EEC manageable Layer 2 IE switch IEC 62443-4-2 certified; 6x 10/100 Mbit/s RJ45 ports; 2x 100/1000 Mbit/s SFP; 1x console port; diagnostics LED; redundant power supply; with painted printed-circuit boards; NAMUR NE21-compliant; temperature range -40 °C to +70 °C; assembly: DIN rail/S7 mounting rail/wall; redundancy functions; office features (RSTP, VLAN,...); PROFINET IO device; Ethernet/IP-compliant; C-PLUG slot;

product type designation	SCALANCE XC206-2SFP EEC
transfer rate	
transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
interfaces / for communication / maximum configuration for modular devices	
number of electrical ports / maximum	6
number of optical ports / maximum	2
interfaces / for communication / integrated	
number of electrical connections	6; RJ45
<ul style="list-style-type: none"> for network components or terminal equipment 	
number of 10/100/1000 Mbit/s RJ45 ports / integrated	6
<ul style="list-style-type: none"> with securing collar 	
interfaces / for communication / plug-in	
number of electrical connections	2; 100/1000 Mbps SFP plug-in transceiver
<ul style="list-style-type: none"> for SFP 	
interfaces / other	
number of electrical connections	1
<ul style="list-style-type: none"> for operator console 	
<ul style="list-style-type: none"> for signaling contact 	1
<ul style="list-style-type: none"> for power supply 	1
type of electrical connection	
<ul style="list-style-type: none"> for operator console 	RJ11
<ul style="list-style-type: none"> for signaling contact 	2-pole terminal block
<ul style="list-style-type: none"> for power supply 	4-pole terminal block
design of the removable storage	
<ul style="list-style-type: none"> C-PLUG 	Yes
signal inputs/outputs	
operating voltage / of the signaling contacts	24 V
<ul style="list-style-type: none"> at DC / rated value 	
operational current / of the signaling contacts	0.1 A
<ul style="list-style-type: none"> at DC / maximum 	
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	DC
<ul style="list-style-type: none"> supply voltage / 1 / rated value 	24 V
<ul style="list-style-type: none"> power loss [W] / 1 / rated value 	6 W
<ul style="list-style-type: none"> consumed current / 1 / at rated supply voltage / maximum 	0.25 A
<ul style="list-style-type: none"> supply voltage / 1 / rated value 	9.6 ... 31.2 V
<ul style="list-style-type: none"> consumed current / 1 / maximum 	0.5 A
<ul style="list-style-type: none"> type of electrical connection / 1 / for power supply 	4-pole terminal block
<ul style="list-style-type: none"> product component / 1 / fusing at power supply input 	Yes

• fuse protection type / 1 / at input for supply voltage	2.5 A / 125 V
ambient conditions	
ambient temperature	
• during operation	-40 ... +70 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	compact
width	60 mm
height	147 mm
depth	125 mm
net weight	0.52 kg
material / of the enclosure	Polycarbonate (PC-GF10) / pressure die cast aluminum
fastening method	
• 35 mm top hat DIN rail mounting	Yes
• wall mounting	Yes
• S7-300 rail mounting	Yes
• S7-1500 rail mounting	Yes
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of $\sim 0.3\text{ s}$	50
cascading in cases of star topology	any (depending only on signal propagation time)
product function / QoS according to DSCP	Yes
product feature	
• Cut Through switching method	No
• Store & Forward switching method	Yes
product functions / management, configuration, engineering	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• RMON	Yes
• SMTP server	No
• port mirroring	Yes
• multiport mirroring	Yes
• CoS	Yes
• PROFINET IO diagnosis	Yes
PROFINET conformity class	B
product function / switch-managed	Yes
telegram length / for Ethernet / maximum	1632 byte
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• BOOTP	No
• GMRP	Yes
• DCP	Yes
• LLDP	Yes
• EtherNet/IP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	

<ul style="list-style-type: none"> ● I&M0 - device-specific information 	Yes
<ul style="list-style-type: none"> ● I&M1 - higher level designation/location designation 	Yes
product function	
<ul style="list-style-type: none"> ● is supported / identification link 	Yes
product functions / diagnostics	
product function	
<ul style="list-style-type: none"> ● port diagnostics 	Yes
<ul style="list-style-type: none"> ● statistics Packet Size 	Yes
<ul style="list-style-type: none"> ● statistics packet type 	Yes
<ul style="list-style-type: none"> ● error statistics 	Yes
<ul style="list-style-type: none"> ● SysLog 	Yes
product functions / VLAN	
product function	
<ul style="list-style-type: none"> ● VLAN - port based 	Yes
<ul style="list-style-type: none"> ● VLAN - protocol-based 	No
<ul style="list-style-type: none"> ● VLAN - IP-based 	No
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
protocol / is supported / GVRP	Yes
product functions / DHCP	
product function	
<ul style="list-style-type: none"> ● DHCP server 	Yes
<ul style="list-style-type: none"> ● DHCP client 	Yes
<ul style="list-style-type: none"> ● DHCP Option 82 	Yes
<ul style="list-style-type: none"> ● DHCP Option 66 	Yes
<ul style="list-style-type: none"> ● DHCP Option 67 	Yes
product functions / redundancy	
product function	
<ul style="list-style-type: none"> ● of the PROFINET IO device / is supported / PROFINET system redundancy 	Yes
<ul style="list-style-type: none"> ● ring redundancy 	Yes
<ul style="list-style-type: none"> ● High Speed Redundancy Protocol (HRP) 	Yes
<ul style="list-style-type: none"> ● high speed redundancy protocol (HRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> ● high speed redundancy protocol (HRP) with standby redundancy 	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
<ul style="list-style-type: none"> ● media redundancy protocol (MRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> ● Media Redundancy Protocol Interconnection (MRP-I) 	Yes
<ul style="list-style-type: none"> ● of the PROFINET IO device / is supported / H-Sync forwarding 	Yes
<ul style="list-style-type: none"> ● redundancy procedure STP 	Yes
<ul style="list-style-type: none"> ● redundancy procedure RSTP 	Yes
<ul style="list-style-type: none"> ● redundancy procedure RSTP+ 	Yes
<ul style="list-style-type: none"> ● redundancy procedure MSTP 	Yes
<ul style="list-style-type: none"> ● Parallel Redundancy Protocol (PRP)/operation in the PRP-network 	Yes
<ul style="list-style-type: none"> ● Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA) 	No
<ul style="list-style-type: none"> ● passive listening 	Yes
protocol / is supported	
<ul style="list-style-type: none"> ● LACP 	Yes
product functions / security	
product function	
<ul style="list-style-type: none"> ● IEEE 802.1x (radius) 	Yes
<ul style="list-style-type: none"> ● broadcast/multicast/unicast limiter 	Yes
<ul style="list-style-type: none"> ● broadcast blocking 	Yes
protocol / is supported	
<ul style="list-style-type: none"> ● SSH 	Yes

• SSL	Yes
product functions / time	
product function	
• SICLOCK support	Yes
• NTP-client	Yes
• SNTP client	Yes
protocol / is supported	
• NTP	Yes
• SNTP	Yes
system modification during operation	
product function / configuration in RUN via CiR/H-CiR	Yes
standards, specifications, approvals	
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
MTBF	47 a
reference code	
• according to IEC 81346-2	KF
• according to IEC 81346-2:2019	KFE
standards, specifications, approvals / CE	
certificate of suitability / CE marking	Yes
product conformity / according to EMC-guideline	2014/30/EU
standard	
• for EMC interference emission	EN 61000-6-4, EN 50121-4
• for immunity to EMC	EN 61000-6-2, EN 50121-4
certificate of suitability / RoHS conformity	Yes; 2011/65/EU
standards, specifications, approvals / hazardous environments	
certificate of suitability	
• ATEX	Yes; EN 60079-0, EN 60079-15
• for ATEX / as marking	II 3 G Ex nA II T4 Gc
• for ATEX / as certificate	KEMA 07ATEX0145 X
• IECEX	Yes; IEC 60079-0, IEC 60079-15
• for IECEX / as marking	Ex nA II T4 Gc
• for IECEX / as certificate	IECEX DEK 14.0025X
• CCC / for hazardous zone according to GB standard	Yes
• CCC / for hazardous zone according to GB standard / as marking	Ex nA IIC T4 Gc
• for cULus HazLoc / as marking	CL1, DIV2, Group A,B,C,D T4, CL1, Zone 2, Group IIC, T4
• for cULus HazLoc / as File Nr.	E240480 (NWHP, NWHP7)
• FM registration	Yes; FM class 3600:2011, FM class 3611:2004, FM class 3810:2005, ANSI/ISA-61010-1:2004
• for FM / as marking	CL1, DIV2, group A,B,C,D T4, CL1, Zone 2, group IIC, T4 Ta: -40 °C +70 °C
• for FM / as certificate	FM16US0205X
standards, specifications, approvals / other	
certificate of suitability	
• railway application in accordance with EN 50121-4	Yes
• Regulatory Compliance Mark (RCM)	Yes
• for UL 61010-2-201 / as File Nr.	E85972 (NRAQ, NRAQ7)
• for UL 60950-1 / as File Nr.	E115352 (NWGQ, NWGQ7)
• EAC approval	Yes
accessories	
product extension / optional / C-PLUG	Yes
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
security information	

security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial security concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial security measures that may be implemented, please visit <https://www.siemens.com/industrialsecurity>. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Security RSS Feed under <https://www.siemens.com/cert>. (V4.6)

last modified:

9/22/2023 