

## External 240V Battery Pack for Select 400V 3-Phase SmartOnline UPS Systems

MODEL NUMBER: **BP240V135**



240V DC battery extends the runtime of select Tripp Lite 400V 3-phase SmartOnline® UPS systems.

### Description

The BP240V135 External Battery Pack extends the runtime of compatible SmartOnline® UPS systems recommending its use, including SVT10KX, SVT20KX and SVT30KX. It comes with heavy-gauge cabling and a high-current DC connector for safe, simple hardwired installation, as well as internal disconnect for battery isolation. A built-in circuit breaker protects your equipment from dangerous overcurrent or overloads. For even more battery runtime, you can daisy-chain multiple BP240V135 battery packs to the compatible UPS system. Tested to IEC 62040-1: 2008/A1: 2013 standards.

### Features

#### Extends Runtime of Select SmartOnline UPS Systems

- Connects to SVT10KX, SVT20KX, SVT30KX and other 3-phase UPS systems recommending its use
- Includes cable with high-current DC connector
- Internal DC disconnect for battery isolation
- Built-in circuit breaker
- Can be daisy-chained with multiple battery packs for extended-run operation
- Tested to IEC 62040-1: 2008/A1: 2013 standards

## Specifications

OVERVIEW	
UPC Code	037332196569
INPUT	
Input Phase	3-Phase
BATTERY	

### Highlights

- Includes cable with high-current DC connector
- Internal DC disconnect for battery isolation
- Built-in circuit breaker
- Daisy-chainable with multiple batteries for longer operation
- Tested to IEC 62040-1: 2008/A1: 2013 standards

### Package Includes

- BP240V135 External Battery Pack
- Battery connection cable
- Owner's manual

Expandable Runtime	No
DC System Voltage (VDC)	240VDC
UPS Connection	DC connector
<b>PHYSICAL</b>	
Material of Construction	Steel
Rack Height	0U
External Battery Pack Form Factor	Tower
Installation Form Factors Supported with Included Accessories	Tower
Shipping Dimensions (hwd / in.)	26.00 x 14.57 x 39.37
Shipping Dimensions (hwd / cm)	66.04 x 37.01 x 100.00
Shipping Weight (lbs.)	466.00
Shipping Weight (kg)	211.37
Unit Dimensions (Height x Width x Depth, mm)	580 x 250 x 826
Unit Dimensions (hwd / in.)	22.840 x 9.850 x 32.500
Unit Dimensions (hwd / cm)	58 x 25 x 82.6
Unit Weight (lbs.)	342
Unit Weight (kg)	155.13
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	EN 62040-1
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	1-year limited warranty