

LC1D18B7

IEC contactor, TeSys Deca, nonreversing, 18A, 10HP at 480VAC, up to 100kA SCCR, 3 phase, 3 NO, 24VAC 50/60Hz coil, open



Main

| | |
|--------------------------------|---|
| Range of Product | TeSys Deca |
| Product or Component Type | Contacteur |
| Device short name | LC1D |
| Contacteur application | Resistive load Motor control |
| Utilisation category | AC-1 AC-4 AC-3 AC-3e |
| Poles description | 3P |
| [Ue] rated operational voltage | Power circuit <= 690 V AC 25...400 Hz Power circuit <= 300 V DC |
| [Ie] rated operational current | 18 A 140 °F (60 °C) <= 440 V AC AC-3 power circuit 32 A 140 °F (60 °C) <= 440 V AC AC-1 power circuit 18 A 140 °F (60 °C) <= 440 V AC AC-3e power circuit |
| [Uc] control circuit voltage | 24 V AC 50/60 Hz |

Complementary

| | |
|---|---|
| Motor power kW | 4 KW 220...230 V AC 50/60 Hz AC-3) 7.5 KW 380...400 V AC 50/60 Hz AC-3) 9 KW 415...440 V AC 50/60 Hz AC-3) 10 KW 500 V AC 50/60 Hz AC-3) 10 KW 660...690 V AC 50/60 Hz AC-3) 4 KW 400 V AC 50/60 Hz AC-4) 4 KW 220...230 V AC 50/60 Hz AC-3e) 7.5 KW 380...400 V AC 50/60 Hz AC-3e) 9 KW 415...440 V AC 50/60 Hz AC-3e) 10 KW 500 V AC 50/60 Hz AC-3e) 10 kW 660...690 V AC 50/60 Hz AC-3e) |
| Maximum Horse Power Rating | 1 Hp 115 V at AC 50/60 Hz for 1 phase 3 Hp 230/240 V at AC 50/60 Hz for 1 phase 5 Hp 200/208 V at AC 50/60 Hz for 3 phase 5 Hp 230/240 V at AC 50/60 Hz for 3 phase 10 Hp 460/480 V at AC 50/60 Hz for 3 phase 15 hp 575/600 V at AC 50/60 Hz for 3 phase |
| Compatibility code | LC1D |
| Pole contact composition | 3 NO |
| Contact compatibility | M2 |
| Protective cover | With |
| [Ith] conventional free air thermal current | 10 A 140 °F (60 °C) signalling circuit 32 A 140 °F (60 °C) power circuit |
| Irms rated making capacity | 140 A AC signalling circuit IEC 60947-5-1 250 A DC signalling circuit IEC 60947-5-1 300 A 440 V power circuit IEC 60947 |
| Rated breaking capacity | 300 A 440 V power circuit IEC 60947 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|---|--|
| [I _{cw}] rated short-time withstand current | 145 A 104 °F (40 °C) - 10 s power circuit 240 A 104 °F (40 °C) - 1 s power circuit 40 A 104 °F (40 °C) - 10 min power circuit 84 A 104 °F (40 °C) - 1 min power circuit 100 A - 1 s signalling circuit 120 A - 500 ms signalling circuit 140 A - 100 ms signalling circuit |
| Associated fuse rating | 10 A gG signalling circuit IEC 60947-5-1 50 A gG ≤ 690 V type 1 power circuit 35 A gG ≤ 690 V type 2 power circuit |
| Average impedance | 2.5 mOhm - Ith 32 A 50 Hz power circuit |
| Power dissipation per pole | 2.5 W AC-1 0.8 W AC-3 0.8 W AC-3e |
| [U _i] rated insulation voltage | Power circuit 690 V IEC 60947-4-1 Power circuit 600 V CSA Power circuit 600 V UL Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA Signalling circuit 600 V UL |
| Overvoltage category | III |
| Pollution degree | 3 |
| [U _{imp}] rated impulse withstand voltage | 6 kV IEC 60947 |
| Safety reliability level | B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1 |
| Mechanical durability | 15 Mcycles |
| Electrical durability | 1.65 Mcycles 18 A AC-3 ≤ 440 V 1 Mcycles 32 A AC-1 ≤ 440 V 1.65 Mcycles 18 A AC-3e ≤ 440 V |
| Control circuit type | AC 50/60 Hz standard |
| Coil technology | Without built-in suppressor module |
| Control circuit voltage limits | 0.3...0.6 U _c -40...158 °F (-40...70 °C) drop-out AC 50/60 Hz 0.8...1.1 U _c -40...140 °F (-40...60 °C) operational AC 50 Hz 0.85...1.1 U _c -40...140 °F (-40...60 °C) operational AC 60 Hz 1...1.1 U _c 140...158 °F (60...70 °C) operational AC 50/60 Hz |
| Inrush power in VA | 70 VA 60 Hz 0.75 68 °F (20 °C)) 70 VA 50 Hz 0.75 68 °F (20 °C)) |
| Hold-in power consumption in VA | 7.5 VA 60 Hz 0.3 68 °F (20 °C)) 7 VA 50 Hz 0.3 68 °F (20 °C)) |
| Heat dissipation | 2...3 W 50/60 Hz |
| Operating time | 12...22 ms closing 4...19 ms opening |
| Maximum operating rate | 3600 cyc/h 140 °F (60 °C) |
| Connections - terminals | Control circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²) flexible without cable end Control circuit screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²) flexible without cable end Control circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²) flexible with cable end Control circuit screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²) flexible with cable end Control circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²) solid without cable end Control circuit screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²) solid without cable end Power circuit screw clamp terminals 1 0.00...0.01 in ² (1.5...6 mm ²) flexible without cable end Power circuit screw clamp terminals 2 0.00...0.01 in ² (1.5...6 mm ²) flexible without cable end Power circuit screw clamp terminals 1 0.00...0.01 in ² (1...6 mm ²) flexible with cable end Power circuit screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²) flexible with cable end Power circuit screw clamp terminals 1 0.00...0.01 in ² (1.5...6 mm ²) solid without cable end Power circuit screw clamp terminals 2 0.00...0.01 in ² (1.5...6 mm ²) solid without cable end |

| | |
|-------------------------------|--|
| Tightening torque | Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2 Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2 Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2 Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2 |
| Auxiliary contact composition | 1 NO + 1 NC |
| Auxiliary contacts type | Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1 |
| Signalling circuit frequency | 25...400 Hz |
| Minimum switching voltage | 17 V signalling circuit |
| Minimum switching current | 5 mA signalling circuit |
| Insulation resistance | > 10 MOhm signalling circuit |
| Non-overlap time | 1.5 Ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact |
| Mounting Support | Rail Plate |

Environment

| | |
|---|--|
| Standards | CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1 |
| Product Certifications | GOST CCC CSA UL RINA BV LROS (Lloyds register of shipping) DNV GL UKCA |
| IP degree of protection | IP20 front face IEC 60529 |
| Protective treatment | THIEC 60068-2-30 |
| Climatic withstand | IACS E10 exposure to damp heat IEC 60947-1 Annex Q category D exposure to damp heat |
| Permissible ambient air temperature around the device | -40...140 °F (-40...60 °C) 140...158 °F (60...70 °C) with derating |
| Operating altitude | 0...9842.52 ft (0...3000 m) |
| Fire resistance | 1562 °F (850 °C) IEC 60695-2-1 |
| Flame retardance | V1 conforming to UL 94 |
| Mechanical robustness | Vibrations contactor open 2 Gn, 5...300 Hz) Vibrations contactor closed 4 Gn, 5...300 Hz) Shocks contactor open 10 Gn for 11 ms) Shocks contactor closed 15 Gn for 11 ms) |
| Height | 3.03 in (77 mm) |
| Width | 1.77 in (45 mm) |
| Depth | 3.39 in (86 mm) |
| Product Weight | 0.73 lb(US) (0.33 kg) |

Ordering and shipping details

| | |
|-------------------|------------------------------------|
| Category | 22354-CTR, TESYS D, OPEN, 9-38A AC |
| Discount Schedule | I12 |
| GTIN | 3389110349399 |
| Returnability | Yes |
| Country of origin | ID |

Packing Units

| | |
|------------------------------|----------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.97 in (5.000 cm) |
| Package 1 Width | 3.54 in (9.000 cm) |
| Package 1 Length | 4.33 in (11.000 cm) |
| Package 1 Weight | 12.66 oz (359.000 g) |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 20 |
| Package 2 Height | 5.91 in (15.000 cm) |
| Package 2 Width | 11.81 in (30.000 cm) |
| Package 2 Length | 15.75 in (40.000 cm) |
| Package 2 Weight | 16.37 lb(US) (7.427 kg) |
| Unit Type of Package 3 | P06 |
| Number of Units in Package 3 | 320 |
| Package 3 Height | 29.53 in (75.000 cm) |
| Package 3 Width | 31.50 in (80.000 cm) |
| Package 3 Length | 23.62 in (60.000 cm) |
| Package 3 Weight | 279.62 lb(US) (126.832 kg) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| PVC free | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Dimensions



- (1) Including LAD 4BB
(2) Minimum electrical clearance

| LC1 | | D09...D18 | D093...D123 | D099...D129 |
|-----------------|------------------------------------|--------------------|----------------------|-------------|
| b | without add-on blocks | 77 | 99 | 80 |
| b1 | with LAD 4BB | 94 | 107 | 95.5 |
| with LA4 D•2 | 110 ⁽¹⁾ | 123 ⁽¹⁾ | 111.5 ⁽¹⁾ | |
| with LA4 DF, DT | 119 ⁽¹⁾ | 132 ⁽¹⁾ | 120.5 ⁽¹⁾ | |
| with LA4 DW, DL | 126 ⁽¹⁾ | 139 ⁽¹⁾ | 127.5 ⁽¹⁾ | |
| c | without cover or add-on blocks | 84 | 84 | 84 |
| | with cover, without add-on blocks | 86 | 86 | |
| c1 | with LAD N or C (2 or 4 contacts) | 117 | 117 | 117 |
| c2 | with LA6 DK10, LAD 6K10 | 129 | 129 | 129 |
| c3 | with LAD T, R, S | 137 | 137 | 137 |
| | with LAD T, R, S and sealing cover | 141 | 141 | |
| (1) | Including LAD 4BB. | | | |

Wiring

