finder

80 Series - Modular timers 16 A

Features	80.01	80.11		
 Multi-function and mono-function timer range 80.01 - Multi-function & multi-voltage 80.11 - On-delay, multi-voltage 17.5 mm wide Six time scales from 0.1s to 24h High input/output isolation 35 mm rail (EN 60715) mount "Blade + cross" - both flat blade and cross head screw drivers can be used to adjust the range and function selectors, the timing trimmer, and to disengage the rail mounting clip New multi-voltage versions with "PWM clever" technology 	 Multi-voltage Multi-function 	• Multi-voltage • Mono-function		
80.01 / 80.11 Screw terminal	DI: Interval SW: Symmetrical flasher (starting pulse on) BE: Off-delay with control signal CE: On- and off-delay with control signal DE: Interval with control signal on	AL Orbeity		
For UL RATINGS SEE: "General technical information" page V	N/-L/+ A2 A1 A1 A2 A1 A1 A1 A2 A1 A1 A1 A1 A2 A1 A1 A1 A1 A2 A1 A1 A1 A1 A1 A1 A2 A1	N' - L' + $A_2 A_1$ $A_2 A_1$ $A_2 A_1$ $A_2 A_1$ $A_2 A_1$ $A_2 A_1$ $A_2 A_1$ $A_2 A_1$ $A_1 A_2$ $A_1 A_2$ $A_1 A_2$ $A_1 A_2$ $A_1 A_2$ $A_1 A_2$ $A_2 A_1$ $A_2 A_1$ $A_2 A_1$ $A_2 A_1$ $A_2 A_1$ $A_2 A_1$ $A_2 A_1$ $A_2 A_1$ $A_2 A_1$ $A_3 A_2$ $A_1 A_2$ $A_2 A_1$ $A_3 A_2$ $A_1 A_2$ $A_2 A_1$ $A_3 A_2$ $A_1 A_2$ $A_2 A_2$ $A_2 A_3$ $A_3 A_4$ $A_3 A_2$ $A_3 A_2$ $A_3 A_3$ $A_3 A_4$ $A_3 A_2$ $A_3 A_3$ $A_3 A_4$ $A_3 A_4$ $A_3 A_5$ $A_3 A_5$ $A_4 A_5$ $A_5 A_5$		
For outline drawing see page 6	Wiring diagram Wiring diagram (without control signal) (with control signal)	Wiring diagram (without control signal)		
Contact specification				
Contact configuration	1 CO (SPDT)	1 CO (SPDT)		
Rated current/Maximum peak current A	16/30	16/30		
Rated voltage/Maximum switching voltage V AC	250/400	250/400		
Rated load AC1 VA	4,000	4,000		
Rated load AC15 (230 V AC) VA	750	750		
Single phase motor rating (230 V AC) kW	0.55	0.55		
Breaking capacity DC1: 30/110/220 V A	16/0.3/0.12	16/0.3/0.12		
Minimum switching load mW (V/mA)	500 (10/5)	500 (10/5)		
Standard contact material	AgCdO	AgCdO		
Supply specification				
Nominal voltage (U _N) V AC (50/60 Hz)	12240	24240		
V DC	12240	24240		
Rated power AC/DC VA (50 Hz)/W	< 1.8 / < 1	< 1.8 / < 1		
Operating range V AC	10.8265	16.8265		
V DC	10.8265	16.8265		
Technical data				
Specified time range		n, (120)min, (0.12)h, (124)h		
Repeatability %	± 1	± 1		
Recovery time ms	100	100		
Minimum control impulse ms Setting accuracy-full range %	50 ± 5			
Setting accuracy-full range % Electrical life at rated load in AC1 cycles Ambient temperature range °C	± 5 100.10 ³	± 5		
Ambient temperature range °C	-10+50			
	IP 20	-10+50 IP 20		
Approvals (according to type)		-		

Inder

Features

- 80.21 Interval, multi-voltage
- 80.41 Off-delay with control signal, multi-voltage 80.91 - Asymmetrical flasher, multi-voltage
- 17.5 mm wide
- Six time scales from 0.1s to 24h
- High input/output isolation

- 35 mm rail (EN 60715) mount
- "Blade + cross" both flat blade and cross hea screw drivers can be used to adjust the range and function selectors, the timing trimmer, and to disengage the rail mounting clip
- New multi-voltage versions with "PWM cleve technology

finder 80 Series - Modular timers 16 A						
Features	80.21	80.41	80.91			
Mono-function timer range 80.21 - Interval, multi-voltage 80.41 - Off-delay with control signal, multi-voltage 80.91 - Asymmetrical flasher, multi-voltage • 17.5 mm wide • Six time scales from 0.1s to 24h • High input/output isolation • 35 mm rail (EN 60715) mount • "Blade + cross" - both flat blade and cross head						
screw drivers can be used to adjust the range and function selectors, the timing trimmer, and to disengage the rail mounting clip • New multi-voltage versions with "PWM clever" technology	Multi-voltage Mono-function	Multi-voltage Mono-function BE: Off-delay with control signal	Multi-voltage Mono-function II: Asymmetrical flasher (starting pulse on)			
80.21 / 80.41 / 80.91 Screw terminal	N/- L/+ A^2 A1 A^2	N/- L/+ -0-0-0-0-1 A2 A1 B1 -0-0-0-1 18 15 16	Le: Asymmetrical flasher (starting pulse on) with control signal N/- L/+ A2 A1 B1 A2 A1 B1 A2 A1 B1 A2 A1 B1 A2 A1 B1 A2 A1 B1 A3 A1 B1 A3 A1 B1 A3 A1 B1 A3 A			
FOR UL RATINGS SEE: "General technical information" page V	Wiring diagram	Wiring diagram	Wiring diagram Wiring diagram (without control (with control			
For outline drawing see page 6	(without control signal)	(with control signal)	signal) signal)			
Contact specification						
Contact configuration	1 CO (SPDT)	1 CO (SPDT)	1 CO (SPDT)			
Rated current/Maximum peak current A	,	16/30	16/30			
Rated voltage/Maximum switching voltage V AC	250/400	250/400	250/400			
Rated load AC1 VA	4,000	4,000	4,000			
Rated load AC15 (230 V AC) VA	750	750	750			
Single phase motor rating (230 V AC) kW Breaking capacity DC1: 30/110/220 V A	0.55	0.55	0.55			
Breaking capacity DC1: 30/110/220 V A Minimum switching load mW (V/mA)	500 (10/5)	500 (10/5)	500 (10/5)			
Standard contact material	AgCdO	AgCdO	AgCdO			
Supply specification	, igeue	Agede	, igeae			
Nominal voltage (U _N) V AC (50/60 Hz)	24240	24240	12240			
V DC	24240	24240	12240			
Rated power AC/DC VA (50 Hz)/W		< 1.8 / < 1	< 1.8 / < 1			
Operating range V AC	16.8265	16.8265	10.8265			
V DC		16.8265	10.8265			
Technical data						
Specified time range	(0.12)s, (120)s, (0.12)min, (120)min, (0	.12)h, (124)h			
Repeatability %	±l	± 1	± l			
Recovery time ms	100	100	100			
Minimum control impulse ms	_	50	50			
Setting accuracy-full range %	± 5	± 5	± 5			
Electrical life at rated load in AC1 cycles	100·10 ³	100·10 ³	100·10 ³			

-10...+50

IP 20

c(UL) us

PG

CE

°C

-10...+50

IP 20

Ambient temperature range

Approvals (according to type)

Protection category

www.findernet.com VII-2012,

-10...+50

IP 20

finder

80 Series - Modular Solid State timer (SST) 1 A

 Features Multi-function and multi-voltage solid-state output timer 17.5 mm wide Six time scales from 0.1s to 24h High input/output isolation 35 mm rail (EN 60715) mount Multi-voltage output (24240 V AC/DC), independent from the input voltage "Blade + cross" - both flat blade and cross he screw drivers can be used to adjust the range and function selectors, the timing trimmer, and to disengage the rail mounting clip Multi-voltage input with "PWM clever" technology 	80.71 Final Sector Se		
For outline drawing see page 6	Wiring diagramWiring diagram(without control signal)(with control signal)		
Output circuit			
Contact configuration	1 NO (SPST-NO)		
Rated current	A 1		
Rated voltage V AC/			
Switching voltage range V AC/	C 19265		
Rated load AC15	A 1		
Rated load DC1	A 1		
	A 0.5		
	A 0.05		
Max. "ON-state" voltage drop	V 2.8		
Input circuit			
Nominal voltage (U _N) V AC (50/60 H			
V			
Rated power VA (50 Hz)/			
Operating range V			
V	C 19265		
Technical data			
Specified time range	(0.12)s, (120)s, (0.12)min, (120)min, (0.12)h, (124)h		
Repeatability	% ± 1		
,	ns 100		
ε	ns 50		
8 Setting accuracy-full range	% ± 5		
Electrical life cyc			
ξ	-20+50		
Protection category	IP 20		
Approvals (according to type)	(٤ 👁		


<pre> finder </pre>	80 Series - Modular timers 6 - 8 A				
Features	80.61	80.82			
 Mono-function timer range 80.61 - Power off-delay (True off-delay), multi-voltage 80.82 - Star-delta, multi-voltage 17.5 mm wide Rotary range selector, and timing trimmer Four time scales from 0.05s to 3 min (type 80.61 Six time scales from 0.1s to 20min (type 80.82 High input/output isolation 35 mm rail (EN 60715) mount 		 Multi-voltage Mono-function 			
80.61 / 80.82		• Transfer time can be regulated (0.051)s			
Screw terminal	BI: Power off-delay (True off-delay)	SD: Star-delta			
	N' - L' + $A_2 A_1$ $A_2 A_1$ $A_3 A_1$ $A_4 A_1$ $A_5 A_1$ $A_5 A_1$ $A_6 A_1$ $A_1 A_2$ $A_1 A_1$ $A_1 A_2$ $A_1 A_1$ $A_2 A_1$ $A_1 A_2$ $A_2 A_1$ $A_1 A_2$ $A_2 A_1$ $A_2 A_1$ $A_2 A_1$ $A_3 A_1$ $A_1 A_2$ $A_2 A_1$ $A_2 A_1$ $A_3 A_1$ $A_3 A_1$ $A_3 A_1$ $A_3 A_1$ $A_3 A_1$ $A_3 A_1$ $A_3 A_1$ $A_3 A_1$ $A_3 A_2$ $A_3 A_1$ $A_3 A_1$ $A_3 A_2$ $A_3 A_2$ $A_3 A_1$ $A_3 A_2$ $A_3 A_3$ $A_3 A_2$ $A_3 A_3$ $A_3 A_3$	N/-L/+ A2 A1 A1 A2 A1 A1 A2 A1 A1 A2 A1 A1 A2 A1 A2 A1 A2 A1 A2 A1 A2 A1 A2 A1 A2 A1 A2 A1 A2 A1 A2 A1 A2 A1 A2 A1 A2 A1 A2 A1 A2 A1 A2 A1 A2 A1 A2 A1 A2 A2 A1 A2 A2 A2 A3			
For UL ratings see: "General technical information" page V For outline drawing see page 6	Wiring diagram (without control signal)	Wiring diagram (without control signal)			
Contact specification					
Contact configuration	1 CO (SPDT)	2 NO (DPST-NO)			
Rated current/Maximum peak current A		6/10			
Rated voltage/Maximum switching voltage V AC		250/400			
Rated load AC1 VA		1,500			
Rated load AC15 (230 V AC) VA	400	300			
Single phase motor rating (230 V AC) kW	0.3	_			
Breaking capacity DC1: 30/110/220 V A	8/0.3/0.12	6/0.2/0.12			
Minimum switching load mW (V/mA	300 (5/5)	500 (12/10)			
Standard contact material	AgNi	AgNi			
Supply specification					
Nominal voltage (U _N) V AC (50/60 Hz	24240	24240			
V DC	24220	24240			
Rated power AC/DC VA (50 Hz)/W	< 0.6/ < 0.6	< 1.3/ < 0.8			
Operating range VAC	16.8265	16.8265			
V DC	16.8242	16.8265			
Technical data					
Specified time range	(0.052)s, (116)s, (870)s, (50180)s	(0.12)s, (120)s, (0.12)min, (120)min			
Repeatability %	, ± 1	± 1			
Recovery time m:		100			
Minimum control impulse ma		_			
Setting accuracy-full range %		± 5			
Electrical life at rated load in AC1 cycles		60·10 ³			
Ambient temperature range °C		-10+50			
Protection category	IP 20	IP 20			
Approvals (according to type)	رد .(۱	us 💽			

VII-2012, www.findernet.com



Ordering information

Example: 80 series, modular timers, 1 CO (SPDT) - 16 A, supply rated at (12...240)V AC/DC.



Technical data

Insulation						
Dielectric strength			80.01/11/21/41/82/91	80.61	80.71	
between inp	ut and output circuit	V AC	4,000	2,500	2,500	
between ope	n contacts	V AC	1,000	1,000	_	
Insulation (1.2/50 µs) between input and out	put	kV	6	4	4	
EMC specifications						
Type of test			Reference standard			
Electrostatic discharge	contact discharge		EN 61000-4-2	0-4-2 4 kV		
	air discharge		EN 61000-4-2	8 kV		
Radio-frequency electromagnetic field (80 ÷ 1	,000 MHz)		EN 61000-4-3	10 V/m		
Fast transients (burst) (5-50 ns, 5 kHz) on Sup	oply terminals		EN 61000-4-4	4 kV		
Surges (1.2/50 µs) on Supply terminals	common mode		EN 61000-4-5	4 kV		
	differential mode		EN 61000-4-5	4 kV		
on start terminal (B1)	common mode		EN 61000-4-5	4 kV		
	differential mode		EN 61000-4-5	4 kV		
Radio-frequency common mode (0.15 ÷ 80 Å	AHz) on Supply terminals		EN 61000-4-6	10 V		
Radiated and conducted emission			EN 55022	class A		
Other data						
Current absorption on signal control (B1)			< 1 mA			
Power lost to the environment	without contact current	W	1.4			
	with rated current	W	3.2			
Screw torque		Nm	0.8			
Max. wire size			solid cable	stranded co	ble	
		mm ²	1x6 / 2x4	1x4 / 2x2.	5	
		AWG	1x10 / 2x12	1x12 / 2x	4	

Sheet of marker tags, for types 80.01/11/21/41/61/71, plastic, 72 tags, 6x12 mm 060.72

Accessories

dani	İmi	in	E	i da	ă îr	ni i
<u>Serii</u>	<u>Ini</u>	ĩ	E	i	d in	ii)
átei	Āni	F	i	i in	ú Ó	ii)
<u>fani</u>	İnii	i	E	i da	iù	i,

Sheet of marker tags, for types 80.82, plastic, 24 tags, 9x17 mm

020.24


5 020.24

COREE				81
Philippin	Anderla	0.000	Carton C	3
Man	101023	11111	CUTAR I	5
CIRIE			0000	1
Print Law		-		н
1000	111111	21121	11192	Ц.




80 Series - Modular timers 1 - 6 - 8 - 16 A


Outline drawings













80.61 Screw terminal



80.11 Screw terminal 17.5 60.8 • 0 Clindee ٩ 88.8 33.8 45 84 0000 • 30.5 [(€ •





80.71 Screw terminal

□ (€


84





30.5 **B B**





VII-2012, www.findernet.com



80 Series - Modular timers 1 - 6 - 8 - 16 A

Functions

U = Supply voltage

S = Signal switch


____ = Output contact

Wiring diagram


	Supply voltage	NO output contact	Contacts		
LED*			Open	Closed	
	OFF	Open	15 - 18	15 - 16	
	ON	Open	15 - 18	15 - 16	
	ON	Open (Timing in Progress)	15 - 18	15 - 16	
	ON	Closed	15 - 16	15 - 18	

The LED on type 80.61 is illuminated only when the supply voltage is applied to the timer; during the timing period the LED is not illuminated.

Without control signal = Start via contact in supply line (A1). With control signal = Start via contact into control terminal (B1).



NOTE: The function must be set before energising the timer.



* With DC supply, positive polarity has to be connected to B1 terminal (according to EN 60204-1).


• Possible to control an external load, such as another relay coil or timer, connected to the control signal terminal B1.


** A voltage other than the supply voltage can be applied to the command Start (B1), example: A1 - A2 = 230 V AC B1 - A2 = 12 V DC

7



Functions





- Possible to control an external load, such as another relay coil or timer, connected to the control signal terminal B1.
- * With DC supply, positive polarity has to be connected to B1 terminal (according to EN 60204-1).
- ** A voltage other than the supply voltage can be applied to the command Start (B1), example: A1 - A2 = 230 V AC B1 - A2 = 12 V DC

VII-2012, www.findernet.com