

9921 Hook-up/Lead - UL AWM Style 1007 and 1569

	<p>For more information please call 1-800-Belden1</p> <p><u>See Put-ups and Colors</u></p>
--	---

Description:

Tinned copper conductor, PVC insulation. Rated 105°C, 300V. Rated 600V peak for electronic circuits, and internal wiring of electronic and electrical equipment.

PHYSICAL CHARACTERISTICS:

CONDUCTOR:

Number of Conductors	1
Total Number of Conductors	1
AWG	22
Stranding	7x30
Conductor Material	TC - Tinned Copper

INSULATION:

Insulation Material	PVC - Polyvinyl Chloride
Insulation Thickness	.015 in.

OVERALL:

Overall Nominal Diameter	.062 in.
--------------------------	----------

APPLICABLE SPECIFICATIONS AND AGENCY COMPLIANCE:

APPLICABLE STANDARDS:

UL AWM Style	UL Style 1007 (300 V 80°C), UL Style 1569 (300 V 105°C)
UL Rating	300 V RMS, 80°C and 300 V, 105°C
CSA Type	TR-64, TRSR-64
CSA Rating	300 V RMS, 90°C and 300 V, 105°C
EU CE Mark (Y/N)	Yes
EU RoHS Compliant (Y/N)	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005

FLAME TEST:

UL Flame Test	VW-1
CSA Flame Test	FT1

PLENUM/NON-PLENUM:

Plenum (Y/N)	N
--------------	---

9921 Hook-up/Lead - UL AWM Style 1007 and 1569

PUT-UPS AND COLORS:

Item	Description	Put-Up (ft.)	Ship Weight (lbs.)	Jacket Color	Notes
9921 001100	22 STR PVC BRN	100	0.4	BROWN	
9921 0011000	22 STR PVC BRN	1000	4	BROWN	P
9921 0015000	#22 STR PVC BRN	5000	20	BROWN	C
9921 001D1000	22 STR PVC BRN	D1000	4	BROWN	
9921 001D5000	22 STR PVC BRN	D5000	20	BROWN	
9921 002100	22 STR PVC RED	100	0.4	RED	
9921 0021000	22 STR PVC RED	1000	4	RED	P
9921 0025000	#22 STR PVC RED	5000	20	RED	C P
9921 002D100	22 STR PVC RED	D100	0.4	RED	
9921 002D1000	22 STR PVC RED	D1000	4	RED	
9921 002D5000	22 STR PVC RED	D5000	20	RED	
9921 003100	22 STR PVC ORG	100	0.4	ORANGE	
9921 0031000	22 STR PVC ORG	1000	4	ORANGE	P
9921 003D1000	22 STR PVC ORG	D1000	4	ORANGE	
9921 003D5000	22 STR PVC ORG	D5000	20	ORANGE	
9921 004100	22 STR PVC YEL	100	0.4	YELLOW	
9921 0041000	22 STR PVC YEL	1000	4	YELLOW	P
9921 0045000	#22 STR PVC YEL	5000	20	YELLOW	C
9921 004D1000	22 STR PVC YEL	D1000	4	YELLOW	
9921 004D5000	22 STR PVC YEL	D5000	20	YELLOW	
9921 005100	22 STR PVC D GRN	100	0.4	GREEN, DARK	
9921 0051000	22 STR PVC D GRN	1000	4	GREEN, DARK	P
9921 0055000	#22 STR PVC DGRN	5000	20	GREEN, DARK	C
9921 005D100	22 STR PVC DGRN	D100	0.4	GREEN, DARK	
9921 005D1000	22 STR PVC DGRN	D1000	4	GREEN, DARK	
9921 005D5000	22 STR PVC DGRN	D5000	20	GREEN, DARK	

9921 Hook-up/Lead - UL AWM Style 1007 and 1569

9921 006100	22 STR PVC LBLU	100	0.4	BLUE, LIGHT	
9921 0061000	22 STR PVC LBLU	1000	4	BLUE, LIGHT	P
9921 007100	22 STR PVC VIO	100	0.4	VIOLET	
9921 0071000	22 STR PVC VIO	1000	4	VIOLET	P
9921 007D1000	22 STR PVC VIO	D1000	4	VIOLET	
9921 007D5000	22 STR PVC VIO	D5000	20	VIOLET	
9921 008100	22 STR PVC GRY	100	0.4	GRAY	
9921 0081000	22 STR PVC GRY	1000	4	GRAY	P
9921 0085000	#22 STR PVC GRY	5000	20	GRAY	C P
9921 008D1000	22 STR PVC GRY	D1000	4	GRAY	
9921 008D5000	22 STR PVC GRY	D5000	20	GRAY	
9921 009100	22 STR PVC WHT	100	0.4	WHITE	
9921 0091000	22 STR PVC WHT	1000	4	WHITE	P
9921 009D100	22 STR PVC WHT	D100	0.4	WHITE	
9921 009D1000	22 STR PVC WHT	D1000	4	WHITE	
9921 009D5000	22 STR PVC WHT	D5000	20	WHITE	
9921 010100	22 STR PVC BLK	100	0.4	BLACK	
9921 0101000	22 STR PVC BLK	1000	4	BLACK	P
9921 0105000	#22 STR PVC BLK	5000	20	BLACK	C
9921 010D100	22 STR PVC BLK	D100	0.4	BLACK	
9921 010D1000	22 STR PVC BLK	D1000	4	BLACK	
9921 010D500	22 STR PVC BLK	D500	2	BLACK	
9921 010D5000	22 STR PVC BLK	D5000	20	BLACK	
9921 013100	22 STR PVC D BLU	100	0.4	BLUE, DARK	
9921 0131000	22 STR PVC D BLU	1000	4	BLUE, DARK	P
9921 0135000	#22 STR PVC DBLU	5000	20	BLUE, DARK	C
9921 013D100	22 STR PVC DBLU	D100	0.4	BLUE, DARK	
9921 013D1000	22 STR PVC DBLU	D1000	4	BLUE, DARK	

9921 Hook-up/Lead - UL AWM Style 1007 and 1569

9921 013D5000	22 STR PVC DBLU	D5000	20	BLUE, DARK	
---------------	-----------------	-------	----	------------	--

C = CRATE REEL PUT-UP.

P = STRIPE COLORS ON STOCK SOLID COLORS. STRIPING ADDER OF \$8.00/M' FOR 1 OR 2 STRIPES. 10 000' MINIMUM ORDER FOR COLOR COMBINATION. PUT-UP WILL BE SUBJECT TO TWO PIECES (+ OR -) 10% PER SPOOL WITH A MINIMUM LENGTH OF 100'.

Revision Number: 1 Revision Date: 11-17-2006

© Copyright 2006 Belden, Inc
All Rights Reserved.

Although Belden ("Belden") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with the following environmental regulations: California Proposition 65 Consent Judgment For Wire & Cable Mfgs.(San Francisco Superior Court Nos. 312962 And 320342); EU RoHS (Directive 2002/95/EC, 27-Jan-2003);Material manufactured prior to the compliance date may still be in stock at Belden facilities and in our Distributor's inventory. EU ELV (Directive 2000/53/EC, 18-Sept-2000); EU WEEE (Directive 2002/96/EC, 27-Jan-2003); And EU BFR (Directive 2003/11/EC, 6-Feb-2003). The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information and belief at the date of its publication. The information provided in the Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.