

7424A Multi-Conductor - 600V FCC Control Cables for Moderate Flexing



No longer Available
1-800-BELDEN1

For more Information
please call

1-800-Belden1



General Description:

16 AWG stranded (26x30) bare copper conductors, PVC insulation , unshielded, oil- and abrasion-resistant PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
5	16	26x30	BC - Bare Copper

Total Number of Conductors: 5

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.022

Insulation Resistance: 6.1 Megaohms minimum @ 1000 ft.

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.040

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black printed #1
2	Black printed #2
3	Black printed #3
4	Black printed #4
5	Green/Yellow

Overall Nominal Diameter: 0.360 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-40°C To +90°C
Other Temperature Range:	Flexing: -5°C To +90°C
UL Temperature Rating:	90°C (UL AWM Style 2587)
Bulk Cable Weight:	90 lbs/1000 ft.
Max. Recommended Pulling Tension:	175 lbs.
Min. Bend Radius/Minor Axis:	3.600 in.
Min. Bend Radius (Continuous Flexing):	5.400 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

AWM Specification:	UL Style 2587 (600 V 90°C)
CSA Specification:	AWM I/II A/B
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes

7424A Multi-Conductor - 600V FCC Control Cables for Moderate Flexing

EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	VW-1
CSA Flame Test:	FT1

Suitability

Oil Resistance:	Yes
-----------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

4.0

Max. Operating Voltage - UL:

Voltage

600 V RMS (UL AWM Style 2587)

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 1 Revision Date: 09-25-2012

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.