

## Specifications for BNC Connectors

BNC style connectors are miniature, light-weight, weatherproof interconnecting devices characterized by their two-stud, quick disconnect bayonet lock coupling arrangement. Their design functions satisfactorily from DC to 11 GHz in static applications, or from DC to 4GHz in applications involving vibration. The connectors typically yield a low VSWR (reflected signal) to 4GHz. Primary applications include radio telecommunications, broadcast equipment, medical equipment, computer, Precision Video, High definition studio broadcast, video switching and test instrumentation where frequent coupling and de-coupling are necessary. Bomar's BNCs are available in an extensive variety of configurations and cable sizes and are impedance matched to either 50 ohm or 75 ohm.

MATERIALS							
Connector Parts	Material	Equivalent Standard					
Connector Body and Parts	Brass	ISOCuZn38Pb2 Body Part					
Male Contact Pin	Brass	QQ-B-626					
Commercial Grade	Zinc Alloy/Brass						
Outer Contact	Brass	QQ-B-750					
Socket Contact	Beryllium Copper	QQ-C-530 / MIL-H-7199					
	Phosphor Copper	CuBe2					
Crimp Ferrule	Annealed Copper	QQ-C-576					
Insulators, Standard Versions	Teflon	L-P403 / BS4271					
	Delrin	Grade B					
Rubber Gaskets	Silicone Rubber	ASTM-E1418PSI					
Plating	Nickel (Silver Optional)	MIL-G-45204					

ELECTRICAL							
Requirement	Requirement Perform						
Impedance	50W	75W					
Frequency Range	0-4GHz	0-1 GHz					
VSWR	1.30 Max.		MIL-C-39012				
RF Insertion Loss	0.2 db Min. at 3 GHz		MIL-C-39012				
RF Leakage	-55 db Min. at 3 GHz	3 GHz MIL-C-39012					
Test Voltage ( At Sea Level)	1500V rms		MIL-STD-202				
Working Voltage ( At Sea Level )	500V rms		MIL-STD-202				
Insulation Resistance	5000 Meg ohms Min.		MIL-STD-202				
Contact Resistance	3 Milli ohms Max.		MIL-C-39012				

MECHANICAL & ENVIRONMENTAL					
Requirement	Performance	Test † Specification			
Durability	500 Insertions & Extractions Min.	MIL-C-39012			
Shock	50 G	MIL-STD-202			
Vibration	20 G from 80-2000 Hz	MIL-STD-202			
Cable Retention (Cable Types)	60 lbs. Minimum Pull Test	MIL-C-39012			
Coupling Nut	60 lbs. Maximum	MIL-C-39012			
Temperature Range	Teflon: -55 to +199 C				
Temperature Kange	Delrin: -40 to +85 C				
Moisture Resistance	Continuous Test	MIL-STD-202			
Salt Spray	48 Hours	MIL-STD-202			

1

†Products are made to conform to the Mil standard but are for commercial applications and are not QPL

FOR TECHNICAL SUPPORT: PHONE 973-347-4040 / FAX973-347-2111 Back to Index

## **3 Piece Crimp**

Part Number (Male)	Patts	(I.D.) **	Fig. No.	RG/U Cable		
10A205A		.200 In.	Fig. 1	6, 21 AWG Center Conductor		
310A205A18	2	.200 In.	Fig. 1	6 CATV, 18 AWG Center Conductor	100	100
310A205F	2	.124 In.	Fig. 1	58A/U, 58C/U Stranded, 141, Thin PVC		
310A205FS	2	.124 In.	Fig. 1	58/U Solid Conductor	Fig.1	
10A205FV	2	.125 In.	Fig. 2	58/U Thin-Net Plenum		-
310A205FV2	8	.125 In.	Fig. 2	Mini 59, RGB Cable (23 AWG)	1	
0A205FV3	2	.125 In.	Fig. 2	Mini 59, RGB Cable (26 AWG)	Provide State	
310A204G	2	.150 In.	Fig. 1	59, 62, 210		
310A205G20	2	.150 In.	Fig. 1	RG59 20 AWG Center Cond.		
310A205G23	2	.150 In.	Fig. 1	Belden 8241		
310A205MV	2	.125 In.	Fig. 3	174, 178, 196, Mini RGB Cable 50 W	THE REAL	
310B205MV	2	.125 In.	Fig. 3	174, 178, 196, Mini RGB Cable 75 W		
310A205N	8	.090 In.	Fig. 3	179, 187	AA THE REAL PROPERTY AND A THE	
310A205P	8	.125 In.	Fig. 1	223		
310B205Q	2	.205 In.	Fig. 1	Belden 8281 True 75 Ohms	Fig.4	
310A204T	2	.150 In.	Fig. 2	59, 62, Plenum		
310A208W2	2	.103 In.	Fig.1	Mini 59, RGB Cable (26 AWG)		

## **Twist-On and 2 Piece Crimp**

BNC Twist-On connectors are field installable and require no tooling other than a stripping tool for the cable preparation. The center conductor is inserted into Bomar's unique Posi-Con <sup>TM</sup> contact, as the connector is twisted onto the cable's outer jacket. BNC 2 Piece crimp connectors make use of a fully captivated pin. Just insert the center conductor into the connector body, slide the ferrule over the braid, and apply a single hex-crimp to the ferrule. These connectors are easy to install and reliable and are recommended only for the lower data transmission speeds.

Part Number	Porto	Gender	Fig. No.	RG/U Cable
310A405A	2	Male	Fig. 8	6, Thick net
310A405F	2	Male	Fig. 8	58A/U Solid Cond, 141, Thin PVC
310A405F1	2	Male	Fig. 8	58/U Solid Cond172"178 "
310A405F2	2	Male	Fig. 8	58/U Thin Plenum158"162"
310A405F3	2	Male	Fig. 8	Thin Plenum .150"
310A405G	2	Male	Fig. 8	59, 62, 210 PVC
310A405T	2	Male	Fig. 8	59, 62, 210 Plenum
320A405F	2	Female	Fig. 8A	58 Solid (PVC)
320A405G	2	Female	Fig. 8A	59, 62, 210 (PVC)
310X205F	2	Male	Fig. 6	RG58 (PVC)
310X205G	2	Male	Fig. 6	RG59, 62 (PVC)
320X205F	2	Female	Fig. 7	RG58 (PVC)
320X205G	2	Female	Fig. 7	RG59, 62 (PVC)
RoHS compliant	nt			




Fig.6




#### **Standard Clamp**

BNC standard clamp style is a simplified version of the original military clamp style. It is required that the contact be soldered to the center conductor of the cable.

Part Number	Porto	Gender	Fig. No.	RG/U Cable
310A105A	2	Male	9	6
310A105D	2	Male	9	11A
310A105F	2	Male	9	58, 58A, 58C, 141
310A105G	2	Male	9	59, 62, 210
310A105M	2	Male	9	174, 188, 316
320A105F*	2	Female	10	58, 58A, 58C, 141
320A105G*	2	Female	10	59, 62, 214







RoHS compliant


### Specialty Broadcast Plugs Click here for

#### Click here for complete Broadcast Catalog

Broadcast grade BNC connectors are perfectly matched to 75 ohm impedance's. The superior plugs are for studio wiring and other broadcast uses. Solid precision machined brass, not die-cast, hold up under the toughest conditions. Here, we are showing the eight most popular but there are many more versions matched to the popular cable manufacturer's part number.



Part Number	Porto	Gender	Belden Cable
SBC1505A	N.	Male	1505A
SBC1694A Male	8281	Male	1694A
SBC1695A	2	Male	1695A
SBC7731A	2	Male	7731A
SBC8218	2	Male	8218
SBC8241	2	Male	8241
SBC8281	2		






Part Number	Ports	Description	Fig No.	Hole ID
321A245A	2	R/M Crimp, RG6	13	.500
321A245F	2	R/M Crimp, RG58 , Thin-net PVC	13	.500
321A245FV	8	R/M Crimp, Thin-Net Plenum	14	.500
321A245G	8	R/M Crimp, RG59, 62, 210	13	.500
321A245M	8	R/M Crimp, RG174, 188, 196, 316	14	.500
321B245M*	2	R/M Crimp, RG174, 188, 196, 316	14	.500
321B245N*	2	R/M Crimp, RG179, 187	15	.500
326A515	2	F/M Solder (Grounded)	16	.375
326R515	8	F/M Solder (Isolated) White Bushing	17	.375
326R515RD	8	F/M Solder (Isolated) Red Bushing	17	.375
326R515GN	8	F/M Solder (Isolated) Green Bushing	17	.375
326R515BL	2			

### **Panel Jacks and Plugs**

BNC panel plugs and jacks are of machined brass construction for maximum reliability and quality. All contacts are plated with a minimum of five microinches of gold. The square panel types mount on .500 inch centers. The bulkhead type mounts into a .380 "D" shaped panel hole. All connector bodies are bright-nickel plated.

Part Number	Potto	Description	Notations	Fig. No.
316A524C	S.	Male Bulkhead Panel Mount	.380" Mtg. Hole	19
317A507	2	Male Panel Mount	. 500 Mtg. Hole Centers	20
321A205F	2	Female Panel Mount, Crimp	Fits RG58/U Cables	21
321A205G	2	Female Panel Mount, Crimp	Fits RG59, 62, 210 Cables	21
321A205M	2	Female Panel Mount, Crimp	Fits RG174, 178, 196	21
327A507	2	Female Panel Mount, Solder	.500 Mtg. Hole Centers	22
RoHS compliant	1			



"L"

Dim

.717

.914

.788

.925

.925

1.36

1.36

1.36

1.36

1.36

1.3

Fig. No.

26

27

27A

27B

27B

23

24

25

23

24

25

## **PC Board Vertical Jacks**

BNC vertical mount jacks are available in straight PC mounts and "through-panel" styles. The "through-panel", 364 Series, is made in both isolated and grounded versions and are ideal for applications where multiple insertions will require a connector which can endure the stress of higher torque.




Ports Body Plating or Material Part Number Description Insul. Mat. Con. Plating 361A514\* 22 Nickel / Brass Straight PC Mount 50W Teflon Gold 361A505\* 2 Nickel / Brass Straight PC Mount 50 W Delrin Gold 361A534\* 2 Nickel / Brass 3 Post PC Mount 50 W Delrin Gold 2 361A505APF Nickel/Zinc 4 Post W/ Press Fit Center Pin 50W Delrin Gold 2 4 Post W/ Press Fit Center Pin 75W 361A705APF Nickel/Zinc Delrin Gold 3648595 v White Valox PC Mount, Thru-Panel, 50 W Delrin Gold 364S595B Black Valox PC Mount, Thru-Panel, 50 W Delrin Gold ÷ 364S595M PC Mount, Thru-Panel, 50 W Nickel/Zinc Delrin Gold 3648795\* PC Mount, Thru-Panel, 75 W Ļ White Valox Delrin Gold 364S795B\* J Black Valox PC Mount, Thru-Panel, 75 W Delrin Gold 364S795M\* Nickel/Zinc PC Mount, Thru-Panel, 75 W Delrii Gold

Fig. 23

Fig. 24

Fig. 25

RoHS compliant reflow or wave solder RoHS compliant wave solder only



These BNC jacks are manufactured to the highest standards to assure stability in maintaining impedance matching at 50 ohm and 75 ohm applications. The 50 ohm versions have been approved by most of the U.S. manufacturers of LAN cards, and the 75 ohm is in wide use in High Definition Video applications which require the use of a True 75 ohm connector. Contacts are phosphor bronze and will remain resilient even after hundreds of insertions.

		Black Valox	Lo-Profile W/ Posts (TPX) N/A	50W	.515	Gold	31
Part Number	Ports	Body Material	Description	Imp.	Height F.M.S.	Contact Plating	Fig. No.
364M095	8	Nickel/Zinc	4 Post Low Profile, Metal	50W	.453	Gold	38
364M0975	2	Nickel /Zinc	4 Post Low Profile, Metal	75W	.453	Gold	38
364A595	~	White Valox	Standard Profile W/ Posts	50W	.610	Gold	28
364A595T	82	White Valox	Standard Profile W/ Posts (TPX)	50W	.610	Gold	28
364A595NP*	~	White Valox	Standard Profile WO Posts	50W	.610	Gold	35
364A595NPT*	2	White Valox	Standard Profile WO Posts (TPX)	50W	.610	Gold	35
364A595B	~	Black Valox	Standard Profile W/ Posts	50W	.610	Gold	30
364A595BT	2	Black Valox	Standard Profile W/ Posts (TPX)	50W	.610	Gold	30
364A595BNP*	~	Black Valox	Standard Profile WO Posts	50W	.610	Gold	35
364A595BNPT*	82	Black Valox	Standard Profile WO Posts (TPX)	50W	.610	Gold	35
364A595BL	~	White Valox	Lo Profile W/ Posts	50W	.515	Gold	29
364A595BLT	2	White Valox	Lo Profile W/ Posts (TPX)	50W	.515	Gold	29
364A595BLNP*	× 1	White Valox	Lo-Profile W/O Posts	50W	.515	Gold	34
364A595BLB	~	Black Valox	Lo-Profile W/ Posts	50W	.515	Gold	31
364A595BLBT	2		ĺ				

(75W)

364A595BLBNP*	×	Black Valox	Lo-Profile W/O Posts	50W	.515	Gold	34
364M595	× .	Nickel /Zinc	Standard Profile W/ Posts	50W	.620	Gold	32
364M595T	2	Nickel /Zinc	Standard Profile W/ Posts (TPX)	50W	.620	Gold	32
364M595M	~	Nickel /Zinc	Super Lo-Profile W/ Clips	50W	.340	Gold	35A
364M595MT	22	Nickel /Zinc	Super Lo-Profile W/ Clips (TPX)	50W	.340	Gold	35A
364M595L	× .	Nickel / Zinc	Lo-Profile W/ Posts	50W	.529	Gold	33
364M595LT	22	Nickel / Zinc	Lo-Profile W/ Posts (TPX)	50W	.529	Gold	33
364A595NP	× .	White Valox	Standard Profile WO Posts	50W	.610	Gold	35
364A595NPT	22	White Valox	Standard Profile WO Posts (TPX)	50W	.610	Gold	35
364A595BNP*	× .	Black Valox	Standard Profile WO Posts	50W	.610	Gold	35
364A595BLNP*	× .	White Valox	Lo-Profile W/O Posts	50W	.515	Gold	-
364A595BLBNP*	× 1	Black Valox	Lo-Profile W/O Posts	50W	.515	Gold	34
364A795	~	White Valox	Standard Profile W/ Posts (TPX)	75W	.610	Gold	28
364A795T	8	White Valox	Standard Profile W/ Posts	75W	.610	Gold	28
364A795B	× 1	Black Valox	Standard Profile W/ Posts	75W	.610	Gold	30
364A795BT	2	Black Valox	Standard Profile W/ Posts (TPX)	75W	.610	Gold	30
364A795BL	× 1	White Valox	Lo-Profile W/ Posts	75W	.515	Gold	29
364A795BLT	2	White Valox	Lo-Profile W/ Posts (TPX)	75W	.515	Gold	29
364A795BLB	×	Black Valox	Lo-Profile W/ Posts	75W	.515	Gold	31
364A795BLBT	8	Black Valox	Lo-Profile W/ Posts (TPX)	75W	.515	Gold	31
364M795	× 1	Metal	Standard Profile W/ Posts	75W	.620	Gold	32
364M795T	2	Metal	Standard Profile W/ Posts (TPX)	75W	.620	Gold	32
364M795L	× 1	Metal	Lo-Profile W/ Posts	75W	.529	Gold	33
364M795LT	22	Metal	Lo-Profile W/ Posts (TPX)	75W	.529	Gold	33
364F595BL	~	White Valox	9400pF 500V Decoupled	50W	.515	Gold	36
364F595BLB	× 1	Black Valox	9400 pF 500V Decoupled	50W	.515	Gold	37
364H595BL	× 1	White Valox	9400 pF 1500V Decoupled	50W	.515	Gold	36
364H595BLB	× .	Black Valox	9400 pF 1500V Decoupled	50W	.515	Gold	37
364NT	8	Zinc/Brass	Jam Nut ( 364 Series)	N/A			36N
364LW	8	Zinc/ Steel	Lock Washer ( 364Series)	N/A			37N
364 KNT	2	Brass/Nickel	Knurled Nut (364 Series)	N/A			38N









har

Fig. 32

Fig. 34















(TPX) insulator for re-flow solder



## Hardware

Fig. 36N	Fig. 37N



FOR TECHNICAL SUPPORT: PHONE 973-347-4040 / FAX 973-347-2111 Back to Index

5

#### - Page 5 -

- Page 6 -



## 

The **V-Bite (B)** is an industry award winning design PCB connector with all the advantages a designer could want. It edge mounts to the board which offers the lowest profile and utilizes very little PCB real estate. It lends itself to surface mount and through-hole soldering techniques. There are versions for IR and convection reflow soldering. Because the connector locks into place both above and below the PCB it disperses rotational torque relief to the board and not the solder points. The **V-Bite (B)** design offers the lowest VSWR ratings due to the straight through-put contact design. No right angles for reflection. Available in 50 and 75 ohm, threaded and non-threaded. Other options for PCB thickness available. Other interfaces available. **(See "F", BNC Twin and TNC sections.)** 

Part Number	Porto	Description	Imp	Contact	Fig. No.		
361V504ER	2	BNC Jack W/ Teflon For Reflow Solder	BNC Jack W/ Teflon For Reflow Solder 50W Pho				
361V504ET	2	BNC Threaded Jack W/ Teflon For Reflow Solder	50W	Phos./Gold	39		
361V509E	× .	BNC Jack W/ Polyethylene Insulator	50W	Phos./Tin	39A		
361V509ET	×	BNC Threaded Jack W/ Polyethylene Insulator	50W	Phos./Tin	39		
361V704ER	2	BNC Jack W/ Teflon For Reflow Solder	75W	Phos./Gold	39A		
361V704ET	2	BNC Threaded Jack W/ Teflon For Reflow Solder	75W	Phos./Gold	39		
361V704EFT	2	BNC Threaded Jack W/ Teflon Insulator/Flange	75W	Phos./Gold	39B		
361V709E	~	BNC Jack W/ Polyethylene Insulator	75W	Phos./Gold	39A		
361V709ET	~	BNC Threaded Jack W/ Polyethylene Insulator	75W	Phos./Gold	39		
361KNT	3	Knurled Nut (361 Series)	NA				
3M61V704	2	Mini- BNC Jack W/ Teflon for Reflow Solder	75W	Phos./Gold	39C		
RoHS complian	t reflow o	r wave solder YRoHS compliant wave solder only					




Low Profile .270 High FMS Anti Rotational VSWR 1.15:1 Patented V-Bite® Snaps Into PCB Surface Mount Center Contact Pick & Place Version Available





Fig. 39B



**Reduced Size PCB Right Angle Mount** 

The Super Low<sup>TM</sup> Profile BNC PC jack reduces the amount of board space needed to mount a PC jack. Board clips hold the unit in place for soldering. The smallest, lowest profile right angle


BNC jack available. The Lo-Deco<sup>TM</sup> features a four post design that offers greater stability after wave soldering. Also featured is a gold plated contact and nickel plated cast zinc body. Smooth, sleek and aesthetically pleasing design is tumbled to remove casting lines.

Fig 35A

Part Number	Ports	Description	Imp.	Contact	Fig. No.
364M595M	× .	BNC Super Low Profile Jack	50W	Phos./Gold	35A
364M595MT	2	BNC Super Low Profile Jack	50W	Phos./Gold	35A
364M795M	× .	BNC Super Low Profile Jack	75W	Phos./Gold	35A
364M795MT	2	BNC Super Low Profile Jack	75W	Phos./Gold	35A
364M095	~	BNC Lo-Deco Jack	50W	Phos./Gold	38
364M0975	~	BNC Lo-Deco Jack	75W	Phos./Gold	38

RoHS compliant reflow or wave solder ✓ RoHS compliant wave solder only





PC Layout for Super Low Profile




#### **Dual PC Jacks (Threaded)**

Right Angle or Vertical Stacked: When board space becomes a serious issue and you still need the robust, full size, BNC connectors, a dual stacked right angle or vertical version will do the trick. Assembly insertion time is cut in half as well. The Dual 364 series is available in both Valox isolated and all metal construction.

(shown with closed back option FS)







THREAD 1/2-28 UNEF-2B

		Fig. 38D F	ig. 38E		
		Right Angle			
Part Number	Ports	Description	Imp.	Contact	Fig.No.
364A2595	~	Dual Right Angle, White Valox	50W	Phos/Gold	38A
364A2595T	2	Dual Right Angle, White Valox (TPX)	50W	Phos./Gold	38A
364A2795	× .	Dual Right Angle, White Valox	75W	Phos/Gold	38A
364A2795T	2	Dual Right Angle, White Valox (TPX)	75W	Phos/Gold	38A
364A2595B	× .	Dual Right Angle, Black Valox	50W	Phos./Gold	38A
364A2795B	× .	Dual Right Angle, Black Valox	75W	Phos./Gold	38A
364M2595	× .	Dual Right Angle, Metal	50W	Phos./Gold	38B
364M2595T	2	Dual Right Angle, Metal (TPX)	50W	Phos/Gold	38B
364M2795	× .	Dual Right Angle, Metal	75W	Phos./Gold	38B
364M2795T	2	Dual Right Angle, Metal (TPX)	75W	Phos/Gold	38B
3M64M2795	× .	Dual Right Angle, Metal Mini-BNC	75W	Phos-Gold	38C
364KNT	2	Knurled Nut for Dual BNC	N/A	Brass/Nickel	38D
		Vertical			
Part Number	Potto	Description	Imp.	Contact	Fig.No.
36482595	× .	Dual Vertical, White Valox	50W	Phos/Gold	40D
36482795	× .	Dual Vertical, White Valox	75W	Phos./Gold	40D
364S2595B	× .	Dual Vertical, Black Valox	50W	Phos./Gold	40D
364S2795B	× .	Dual Vertical, Black Valox	75W	Phos/Gold	40D
364S2595M	× .	Dual Vertical, Metal	50W	Phos/Gold	
364S2795M	× .	Dual Vertical, Metal	75W	Phos./Gold	
		Tool			
Part Number	Ports	Description	Imp.	Contact	Fig.No.
BD36400	-	Hex Shafted Tool for Knurled Nut	N/A	Steel/Nickel	38E
RoHS comp	liant rel	flow or wave solder <b>KoHS</b> compliant wave solder only Note:Hardware is optional and must be ordered			

## Multi-Port PC Jacks (Non-Threaded)

Side By Side: These right angle units are available in dual or quad configurations. These units are not threaded for panel installation using a jam nut. Up one fourth the installation time.

Part Number	Potto	Description	Imp.	Contact	Fig. No.
365A2595	~	Dual Right Angle, Side By Side White Valox	50W	Phos./Gold	38B
365A2795	×	Dual Right Angle, Side By Side White Valox	75W	Phos./Gold	38B
365A2595B	~	Dual Right Angle, Side By Side Black Valox	50W	Phos./Gold	38B
365A2795B	~	Dual Right Angle, Side By Side Black Valox	75W	Phos./Gold	38B
365A4595	× .	Quad Right Angle, Side By Side White Valox	50W	Phos./Gold	38C
365A4795	~	Quad Right Angle, Side By Side White Valox	75W	Phos/Gold.	38C
365A4595B	~	Quad Right Angle, Side By Side Black Valox	50W	Phos./Gold	38C
365A4795B	×	Quad Right Angle, Side By Side Black Valox	75W	Phos./Gold	38C



## **LED Indicator PC Jacks**

This unthreaded BNC PCB series is available with amber and green LEDs' that are embedded into the Valox body alongside of each BNC port. They can be used to indicate various situations, or conditions of communications through the connector. Single and dual, and quad side by side styles are available.


Ports	Description	Imp	Contact	Fig. No.
~	BNC Single Port, White	50W	Phos./Gold	38E
~	BNC Single Port, Black	50W	Phos./Gold	
~	BNC Dual Port, White	50W	Phos./Gold	
~	BNC Dual Port, Black	50W	Phos./Gold	
~	BNC Quad Port, White	50W	Phos./Gold	38
~	BNC Quad Port, Black	50W	Phos./Gold	38
	***** 	BNC Single Port, White BNC Single Port, Black BNC Dual Port, Black BNC Dual Port, Black BNC Dual Port, Black BNC Quad Port, White	Image: Solution of the second seco	Description     Imp     Contact       **     BNC Single Port, White     50W     Phos/Gold       **     BNC Single Port, Black     50W     Phos/Gold       **     BNC Dual Port, Black     50W     Phos/Gold       **     BNC Dual Port, Black     50W     Phos/Gold       **     BNC Dual Port, Black     50W     Phos/Gold       **     BNC Quad Port, White     50W     Phos/Gold


RoHS compliant reflow or wave solder 🛛 👻 RoHS compliant wave solder only






## PCB and Panel Layouts for 365 Series







182 (2 H

Panel Cut Out Quad




LED BNC





## **Adapters**

Number	PORS	Description	Fig. No.
Number 330A505	2	Male/ Male Inline Barrel Splice	35
332A505	2	Female/Female Inline Splice	36
335A544	21	Female/Female Inline Bulkhead Mount (Grounded)	37
335R544	8	Female/Female Inline Isolated Bulkhead (Metal Outer Thread)	37
343A205F	8	Crimp "T" Adapter for RG58 Cable	41
343A205G	2	Crimp "T" Adapter for RG59, 62 Cables	41
343A505	2	Female/Male/Female "T" Adapter (Yes, it runs with Netware™)	38
345A505	2	Female/Female "T" Adapter	39
351A505	2	Female/Male Right Angle Adapter	40
383U505	33	The Goalie™	42
383U205F	2	The Goalie Brute™ Crimp Version for RG58 Cable	45
383U205G	2	The Goalie Brute™ Crimp Version for RG59, 62 Cables	45
383K505*	2	The Goalie Brute™	43
383P505*	2	The Insulated Goalie	44
353U205F*	2	Male/Female/Female Right Angle Double-Down™ Crimp for RG58	49
353U205G*	2	Male/Female/Female Right Angle Double-Down™ Type for RG59	49
353U505*	2	Male/Female/Female Right Angle Double-Down™	48
393U205F*	2	Male/Female/Female Straight Double-Down™ Crimp for RG58	47
393U205G*	8	Male/Female/Female Straight Double-Down™ Crimp for RG59	47
393U505*	2	Male/Female/Female Straight Double-Down™	46
RoHS com	oliant		
	Fig. 40		



## **Specialty LAN Adapters**

Double Down<sup>TM</sup> adapters are designed to allow parallel cables entering a patch panel, or a BNC LAN terminal port to be guided at a right angle to the input jack. Two versions accomplish this: one is a right angle with side-by-side jacks for areas with little rear clearance, and the other is a straight version for installations where width between panel jacks in limited. Crimp types are for permanent installations. Goalie, and Goalie Brute allow parallel cable 90° entry which require a minimum of rotational cable space.









\*Minimum quantity Requirements May Apply - Contact Sales

#### **Terminators**

BNC terminators are available in standard 1% tolerance versions and in the economy 5% tolerance styles. The standard types have removable color coded caps for easy identification. The economy type are color coded as well but caps are not removable.

Part Number	Porto	Description	Fig No.
310X054A	1	50 W with Red Cap	50
310C054	8	50 W with Grounding Chain	51
310X074	1	75 W with Blue Cap	50
HBC310X075	5	75 W Precision .1% Tolerance	52
310X094	1	93 W with Yellow Cap	50
HBC310X075	8	75 W Precision .1% Tolerance	53
EJ175	10	50 W Economy	52A
EJ177	8	75 W Economy	52A
EJ179	5	93 W Economy	52A









Fig. 52A



# Coax Crimp Tools

Professional grade hex-crimp tools for coaxial connectors are available in ratchet and non-ratcheting types, both provide dependable service. Ratchet tools feature replaceable dies. Included is a convenient release mechanism to unlatch the ratchet in the event of an improper crimp. Each too also crimps the contact pin to the conductor.						
Part Number	Description					
BD10100	Hex Crimp Ratchet for "F" Types, RG59, RG6					
BDHD100	Hex Crimp Ratchet for Belden 8281					
BDHD200	Hex Crimp Ratchet for BNC/TNC RG58,59,62 and MV					
BDHD100	Hex Crimp Ratchet for Mini-RG59					
BD11012	Hex Crimp Ratchet for "N" Crimp RG11, RG213, RG214					
BDHD100	Hex Crimp Ratchet for BNC/TNC RG6, RG59					