ENM Counting Instruments > Electrical Counters > E6B Electrical Counter - Two-Hole Panel Mount > T14 DC Powered Hour Meter II. > T14 DC Powered Hour Meter II. > T18 AC Powered Hour Meter II. > T18 AC Powered Hour Meter II. > T32 AC/DC DIN Rail Mount Hour Meter > T40 Quartz DC Hour Meter > T40 3-Hole Quartz DC Hour Meter > T40 Square Mount Quartz DC Hour Meter II. > T41 Quartz DC Hour Meter II. > T41 Quartz DC Hour Meter II. > T50 Quartz AC Hour Meter II. > T50 Square Mount Quartz AC Hour Meter - Brushed Aluminum > T51 Quartz AC Hour Meter II. > T12C AC Powered Hour Meter > T1100 Series LCD Hour Meter/C1100 Series Counter > Item # C1101AB

Item # C1101AB T1100/C1100 LCD Hour Meter/Counter




T1100/C1100 LCD Hour Meter/Counter

C1100 LCD Counter - Black Bezel Counter

Specifications		
Voltage	8-28 V DC	
Note		
Case	Black bezel counter	
Reset	Yes	
Counter Speed	50 C.P.S.	
Display Digits	6-Digit	

Item # C1101AB, T1100/C1100 LCD Hour Meter/Counter

Dimensional Drawing





Technical Data

658

LCD Hour Meter-Counter-Module Electronics

8 154545

TII0IAB



TIIOIAS



CI I 0 I AB



CIIOIAS

ENM's new series T1100 Hour Meter timer features a 6-digit, 7 segment LCD display. This model is ideal for maintenance applications. The Hour Meter model displays an hour glass and decimal point. The accumulated hours are stored on powerless, non-volatile data backup using CMOS EEPROM technology, where small space and reliable instruments are required with memory that does not rely on a battery.

Part No.	Voltage	Case	
T1101AB	8-28VDC	Black Hour Meter	
T1101AS	8-28VDC	Chrome Hour Meter	
C1101AB	8-28VDC	Black Counter	
C1101AS	8-28VDC	Chrome Counter	

Specifications	
Capacity:	99999.9 Hour meter (00 to 999999) Up Counter (999999 to 00) Down Counter Automatic recycle to zero.
Display height:	6 digits, 5mm LCD
Operating voltage:	8-28VDC, other AC and DC voltages are also available
Count speed:	100 C.P.S.
Operating current:	3mA maximum 8 to 24Vdc and 10mA @ 28Vdc
Operating temperature:	Standard -40C to +85C
Vibration resistance:	Withstands 10 to 75 Hz. at 1 to 8 G's.
Shock resistance:	SAEJ137853G
Accuracy:	Better than +/-0.01%
Humidity:	95%RH+32C for 2 hours
Protected from:	Alternator load dump, inductive switching and reverse polarity.
Memory capacity:	Cmos Eeprom. Nonvolatile memory has data retention in excess of 10 years without power.
Bezel style:	Chrome or Black are available.

Features

- Non-volatile memory (no battery)
- High reliability
- Low cost and small size
- Low operating current
- Wide operating voltage and temperature range
- Very high shock and vibration specs
- Non reset option available
- Solid state electronics
- Quartz crystal
- Made in the USA







SERIES T1100/C1100

Dimensional Data


658

T1100 LCD HOUR METER







T1101AB Black Bezel Hour Meter T1101AS Chrome Bezel Hour Meter




C1100 COUNTER MODULE



C1101AB Black Bezel Counter C1101AS Chrome Bezel Counter





LIMITED WARRANTY

ENM Company products are warranted to the consumer to be free from defects in material and workmanship for a period of I year. All ENM products which fall within the warranty period due to defects in material or workmanship will be repaired or replaced, at ENM's option, without charge to the consumer when returned with proof of purchase to any authorized ENM dealer in the United States, transportation charges prepaid, provided there is no evidence of improper installation, tampering, or other abuse. All implied warranties, including any implied warranty of merchantability or fitness for a particular purpose, shall be limited in duration to the express warranty period specified above.

ENM disclaims any liability for consequential damages due to breach of any written or implied warranty on its products.

