


9841 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-485 Applications



Description:

24 AWG stranded (7x32) TC conductors, polyethylene insulation, twisted pairs, overall Beldfoil® (100% coverage) + TC braid shield (90% coverage), 24 AWG stranded TC drain wire, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	24	7x32	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material
PE - Polyethylene

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	90

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
24	7x32		TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cabling

Overall Nominal Diameter: 0.232 in.

Pair

Pair Color Code Chart:

Color
White/Blue and Blue/White

Pair Lay Length & Direction:

Lay Length (in.)	Twists/ft. (twist/ft)	Direction
2.500	4.800	Left Hand Lay

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +80°C
UL Temperature Rating:	80°C
Bulk Cable Weight:	36 lbs/1000 ft.
Max. Recommended Pulling Tension:	72.300 lbs.
Min. Bend Radius (Install)/Minor Axis:	2.500 in.

9841 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-485 Applications

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
AWM Specification:	UL Style 2919 (30 V 80°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	82841, 89841

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
120

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
12.8

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
23

Nominal Velocity of Propagation:

VP (%)
66

Nominal Delay:

Delay (ns/ft)
1.6

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
24

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
3.4

Nom. Attenuation:

Attenuation (dB/100 ft.)
0.6 (@ 1 MHz)

Max. Operating Voltage - UL:

Voltage
300 V RMS
30 V RMS (UL AWM Style 2919)

Max. Recommended Current:

Current

9841 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-485 Applications

2.1 Amps per conductor @ 25°C

Put Ups and Colors:









Item #	Putup	Ship Weight	Color	Notes	Item Desc
9841 060100	100 FT	4.300 LB	CHROME		1 PR #24 PE SH PVC
9841 0601000	1,000 FT	40.000 LB	CHROME	C	1 PR #24 PE SH PVC
9841 060500	500 FT	20.000 LB	CHROME	C	1 PR #24 PE SH PVC

Notes:

C = CRATE REEL PUT-UP.

Overall Foil/Braid Shield

Low-Capacitance Computer Cables for EIA RS-485 Applications
Plenum-Rated and Non-Plenum

Description	Part No.	UL NEC/ C(UL) CEC Type	No. of Pairs	Color Code	Standard Lengths		Standard Unit Weight		Nom. DCR		Nominal OD		Nom. Imp. (Ω)	Nom. Vel. of Prop.	Nom. Capacitance					
					Ft.	m	Lbs.	kg	Cond.	Shield	Inch	mm			* pF/ Ft.	* pF/ m	** pF/ Ft.	** pF/ m		
24 AWG Stranded (7x32) TC Conductors • Overall Beldfoil® (100% Coverage) + TC Braid Shield (90% Coverage) • 24 AWG Stranded TC Drain Wire																				
Polyethylene Insulation • Chrome PVC Jacket																				
UL AWM Style 2919 (30V 80°C) DMX 512 	9841	NEC:	1	See	100	30.5	4.3	2.0	24.0Ω/M'	3.4Ω/M'	.232	5.89	120	66%	12.8	42.0	23.0	75.5		
		CM		Chart 5	500	152.4	20.0	9.1	78.7Ω/km	11.0Ω/km	For Plenum versions of 9841, see 82841 or 89841.									
		CEC:		(Tech Info	1000	304.8	40.0	18.2												
		CM		Section)																
	9842	NEC:	2	See	100	30.5	5.8	2.6	24.0Ω/M'	2.2Ω/M'	.340	8.64	120	66%	12.8	42.0	23.0	75.5		
		CM		Chart 5	500	152.4	29.5	13.4	78.7Ω/km	7.2Ω/km	For Plenum versions of 9842, see 82842.									
		CEC:		(Tech Info	1000	304.8	57.0	25.9												
		CM		Section)																
	9843	NEC:	3	See	100	30.5	7.1	3.2	24.0Ω/M'	2.3Ω/M'	.360	9.14	120	66%	12.8	42.0	23.0	75.5		
		CM		Chart 5	500	152.4	34.5	15.7	78.7Ω/km	7.7Ω/km										
		CEC:		(Tech Info	1000	304.8	67.0	30.5												
		CM		Section)																
	9844	NEC:	4	See	500	152.4	43.0	19.5	24.0Ω/M'	2.1Ω/M'	.390	9.91	120	66%	12.8	42.0	23.0	75.5		
		CM		Chart 5	1000	304.8	83.0	37.7	78.7Ω/km	6.9Ω/km										
		CEC:		(Tech Info																
		CM		Section)																
Plenum • Foam FEP Insulation • Natural Flammarrest® Jacket																				
300V RMS 	82841	NEC:	1	See	500	152.4	13.0	6.0	24.0Ω/M'	3.1Ω/M'	.204	5.18	120	76%	12	39.4	22	72.2		
		CMP		Chart 5	1000	304.8	26.0	11.8	78.7Ω/km	10.2Ω/km										
300V RMS 	82842	NEC:	2	See	500	152.4	19.0	8.6	24.0Ω/M'	2.4Ω/M'	.273	6.93	120	76%	12	39.4	22	72.2		
		CMP		Chart 5	1000	304.8	42.0	19.1	78.7Ω/km	7.9Ω/km										
300V RMS 	89841	NEC:	1	See	500	152.4	13.5	6.1	24.0Ω/M'	3.1Ω/M'	.202	5.13	120	76%	12	39.4	22	72.2		
		CMP		Chart 5	1000	304.8	27.0	12.3	78.7Ω/km	10.2Ω/km										
300V RMS 	89842 <small>new</small>	NEC:	2	See	500	152.4	25.5	11.6	24.0Ω/M'	3.1Ω/M'	.305	7.75	120	76%	12	39.4	22	72.2		
		CMP		Chart 5	1000	304.8	49.0	22.2	78.7Ω/km	10.2Ω/km										

DCR = DC Resistance • TC = Tinned Copper

*Capacitance between conductors.

**Capacitance between one conductor and other conductors connected to shield.