

8135 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232/485



Description:

28 AWG stranded (7x36) TC conductors, Datalene® insulation, overall Beldfoil® (100% coverage) + TC braid shield (65% coverage), 28 AWG stranded TC drain wire, PVC jacket

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
5	28	7x36	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material
Datalene®	FPE - Foam Polyethylene

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape w/Shorting Fold	100
2		Braid	TC - Tinned Copper	65

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
28	7x36		TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cabling

Overall Nominal Diameter: 0.288 in.

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue & Blue/White
2	White/Orange & Orange/White
3	White/Green & Green/White
4	White/Brown & Brown/White
5	White/Gray & Gray/White

Pair Lay Length & Direction:

Lay Length (in.)	Twists/ft. (twist/ft)
0.830	14.400

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +80°C

UL Temperature Rating: 80°C (UL AWM Style 2919)

Bulk Cable Weight: 43 lbs/1000 ft.

8135 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232/485

Min. Bend Radius (Install)/Minor Axis: 2 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CL2
AWM Specification:	UL Style 2919 (30 V 80°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test: UL1685 UL Loading

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
120

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
11

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
20

Nominal Velocity of Propagation:

VP (%)
78

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
65

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
4.2

Max. Operating Voltage - UL:

Voltage
30 V RMS (UL AWM Style 2919); 150 V RMS

Max. Recommended Current:

Current
0.9 Amps per conductor @ 25°C

Notes (Overall)

Notes: Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.

Put Ups and Colors:

8135 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232/485

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8135 060100	100 FT	4.300 LB	CHROME		5 PR #28 FHDPE SH PVC
8135 0601000	1,000 FT	40.000 LB	CHROME	C	5 PR #28 FHDPE SH PVC

Notes:

C = CRATE REEL PUT-UP.

Introduction

Belden® paired cable products are manufactured in a variety of gage sizes, dimensions, insulation materials, shielding configurations, and jacketing materials including Plenum and High-Temperature versions to meet the technical requirements of many different types of systems.

Paired cables allow balanced signal transmission, which results in lower crosstalk through common mode rejection. Due to the improved noise immunity of twisted pairs, they generally permit higher data speeds than multi-conductor cables.

As an aid to proper cable selection, both the suggested working voltages and the maximum temperature ratings are indicated for each applicable paired cable selection.


Most of our paired cables are available from stock. Many of these are available off the shelf from distributors. If you have a new or unusual application or you cannot find a paired cable in this catalog section that meets your technical requirements, contact Technical Support at 1-800-BELDEN-1.

Paired Cables Packaging

Belden's unique UnReel® cable dispenser is available for many of the paired cable products listed in this section. The letter "U" before the specified put-up length denotes UnReel packaging.

Overall Foil/Braid Shield

Low-Capacitance Computer Cables for EIA RS-232 and EIA RS-485 Applications

Description	Part No.	UL NEC/ C(UL) CEC Type	No. of Pairs	Color Code	Standard Lengths		Standard Unit Weight		Nom. DCR		Nominal OD		Nom. Imp. (Ω)	Nom. Vel. of Prop.	Nom. Capacitance			
					Ft.	m	Lbs.	kg	Cond.	Shield	Inch	mm			* pF/ Ft.	* pF/ m	** pF/ Ft.	** pF/ m
28 AWG Stranded (7x36) TC Conductors • Overall Beldfoil® (100% Coverage) + TC Braid Shield (65% Coverage) • 28 AWG Stranded TC Drain Wire																		
Datalene® Insulation • Chrome PVC Jacket																		
 <p>Shorting Fold</p>	UL AWM Style 2919 (30V 80°C)	8132	NEC: CL2	2	See Chart 5 (Tech Info Section)	100 500 1000	30.5 152.4 304.8	3.6 14.5 29.0	1.6 6.6 13.2	65.0Ω/M' 213.0Ω/km	5.1Ω/M' 16.6Ω/km	.220 5.59	120	78%	11.0	36.1	20.0	65.6
	8133	NEC: CL2	3	See Chart 5 (Tech Info Section)	100 500 1000	30.5 152.4 304.8	3.8 15.0 34.0	1.7 6.8 15.5	65.0Ω/M' 213.0Ω/km	5.2Ω/M' 17.1Ω/km	.270 6.86	120	78%	11.0	36.1	20.0	65.6	
	8134	NEC: CL2	4	See Chart 5 (Tech Info Section)	100 500 1000	30.5 152.4 304.8	4.3 18.0 39.0	2.0 8.2 17.7	65.0Ω/M' 213.0Ω/km	4.4Ω/M' 14.3Ω/km	.290 7.37	120	78%	11.0	36.1	20.0	65.6	
	8135	NEC: CL2	5	See Chart 5 (Tech Info Section)	100 500 1000	30.5 152.4 304.8	4.6 42.0 19.1	2.1 19.1 23.8	65.0Ω/M' 213.0Ω/km	4.2Ω/M' 13.8Ω/km	.300 7.62	120	78%	11.0	36.1	20.0	65.6	
	8138	NEC: CL2	8	See Chart 5 (Tech Info Section)	100 500 1000	30.5 152.4 304.8	5.6 27.0 52.0	2.5 12.3 23.6	65.0Ω/M' 213.0Ω/km	3.7Ω/M' 12.3Ω/km	.330 8.38	120	78%	11.0	36.1	20.0	65.6	
	8142	NEC: CL2	12.5 (12 pairs + 1 single)	See Chart 5 (Tech Info Section)	100 500 1000	30.5 152.4 304.8	6.8 33.0 66.0	3.1 15.0 29.9	65.0Ω/M' 213.0Ω/km	3.1Ω/M' 10.1Ω/km	.375 9.53	120	78%	11.0	36.1	20.0	65.6	
	8148	NEC: CL2	18	See Chart 5 (Tech Info Section)	100 500 1000	30.5 152.4 304.8	8.5 47.5 92.0	3.9 21.6 41.8	65.0Ω/M' 213.0Ω/km	2.6Ω/M' 8.4Ω/km	.465 11.81	120	78%	11.0	36.1	20.0	65.6	
	8155	NEC: CL2	25	See Chart 5 (Tech Info Section)	100 500 1000	30.5 152.4 304.8	11.1 64.0 121.0	5.0 29.1 55.0	65.0Ω/M' 213.0Ω/km	2.3Ω/M' 7.6Ω/km	.565 14.35	120	78%	11.0	36.1	20.0	65.6	

DCR = DC Resistance • TC = Tinned Copper

*Capacitance between conductors.

**Capacitance between one conductor and other conductors connected to shield.

Datalene insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.