

QUINT-PS/1AC/24DC/3.5


Order No.: 2866747



DIN rail power supply unit 24 V DC/3.5 A, primary-switched mode, 1-phase. The SFB technology (Selective Fusebreaking Technology) can be also used to trigger standard power circuit-breakers quickly and reliably.



Commercial data	
EAN	4046356113779
Pack	1 Pcs.
Customs tariff	85044081
Weight/Piece	0.816 KG
Catalog page information	Page 238 (NTK-2008)



Product description

QUINT POWER power supply units - highest system availability due to SFB technology

Compact power supply units of the new QUINT POWER generation maximize the availability of your system. Even the standard power circuit-breakers can be tripped reliably and quickly with the SFB technology (Selective Fusebreaking Technology) and six times the nominal current for 12 ms. Defective current paths are disconnected selectively, the defect is limited and the important system parts remain in operation. A comprehensive diagnostics is carried out by continuously monitoring the output voltage and current. This preventive function monitoring visualizes the critical operating modes and reports them to the control unit before an error occurs.

Technical data		
Input data		
Nominal input voltage	100 V AC 240 V AC	
AC input voltage range	85 V AC 264 V AC	
DC input voltage range	90 V DC 350 V DC	
Short-term input voltage	300 V AC	
AC frequency range	45 Hz 65 Hz	
DC frequency range	0 Hz	
Current consumption	Approx. 1.4 A (120 V AC)	
	Approx. 0.8 A (230 V AC)	
Inrush surge current	< 20 A (typical)	
Power failure bypass	> 20 ms (120 V AC)	
	> 80 ms (230 V AC)	
Input fuse	5 A (slow-blow, internal)	
Recommended backup fuse	6 A (characteristic B)	
	10 A (characteristic B)	
	16 A (characteristic B)	
Name of protection	Transient surge protection	
Protective circuit/component	Varistor	
Output data		
Nominal output voltage	24 V DC ±1%	
Setting range of the output voltage	18 V DC 29.5 V DC (> 24 V constant capacity)	
Output current	3.5 A (-25°C 70°C)	
	4 A (with POWER BOOST, -25°C 40°C permanent)	
	15 A (with SFB technology, 12 ms)	
Connection in parallel	Yes, for redundancy and increased capacity	
Connection in series	Yes	
Control deviation	< 1 % (change in load, static 10% 90%)	
	< 2 % (change in load, dynamic 10% 90%)	
	< 0.1 % (change in input voltage ±10%)	
Residual ripple	< 50 mVPP (with nominal values)	
Maximum power dissipation idling	3.5 W	
Power loss nominal load max.	12 W	

General data

General data		
Width	32 mm	
Height	130 mm	
Depth	125 mm	
Weight	0.5 kg	
Operating voltage display	LED green	
Efficiency	> 88 % (for 230 V AC and nominal values)	
Insulation voltage input/output	4 kV AC (type test)	
	2 kV AC (routine test)	
Degree of protection	IP20	
Class of protection	I, with PE connection	
MTBF	> 500 000 h in acc. with IEC 61709 (SN 29500)	
Ambient temperature (operation)	-25 °C 70 °C (> 60°C derating)	
Ambient temperature (storage/transport)	-40 °C 85 °C	
Max. permissible relative humidity (operation)	95 % (at 25°C, no condensation)	
Mounting position	Horizontal DIN rail NS 35, EN 60715	
Assembly instructions	Can be aligned: horizontally 5 mm, in addition to active components of 15 mm, vertically 5 cm	
Electromagnetic compatibility	Conformance with EMC directive 2004/108/EC	
Immunity to interference	EN 61000-6-2	
Standard – Electrical equipment of machines	EN 60204	
Standard – Safety transformers for switched-mode power supply units	IEC 61558-2-17	
Standard - Electrical safety	IEC 60950/VDE 0805 (SELV)	
Standard – Electronic equipment for use in electrical power installations and their assembly into electrical power installations	EN 50178/VDE 0160 (PELV)	
Standard – Safety extra-low voltage	IEC 60950 (SELV) and EN 60204 (PELV)	
Standard - Safe isolation	DIN VDE 0100-410	
	DIN VDE 0106-1010	
Standard – Protection against electric shock	DIN 57100-410	
Standard – Protection against shock currents, basic requirements for protective separation in electrical equipment	DIN VDE 0106-101	
Standard – Limitation of mains harmonic currents	EN 61000-3-2	
Standard – Equipment safety	GS (tested safety)	
Standard network variation (undervoltage)	Semi F47-200	
Certificate	CB Scheme	

UL approvals	UL Listed UL 508
	UL/C-UL Recognized UL 60950
Connection data, input	
Type of connection	Pluggable screw connection
Conductor cross section solid min.	0.2 mm²
Conductor cross section solid max.	2.5 mm²
Conductor cross section stranded min.	0.2 mm²
Conductor cross section stranded max.	2.5 mm²
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	12
Stripping length	7 mm
Screw thread	M3
Connection data, output	
Type of connection	Pluggable screw connection
Conductor cross section solid min.	0.2 mm²
Conductor cross section solid max.	2.5 mm²
Conductor cross section stranded min.	0.2 mm²
Conductor cross section stranded max.	2.5 mm²
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	12
Stripping length	7 mm
Signaling	DO OK II
Output name	DC OK active
Output description	U _{out} > 0.9 x U _N : High signal
Maximum switching voltage	+ 24 V DC
Output voltage	+ 24 V DC
Maximum inrush current	≤ 20 mA (short circuit resistant)
Continuous load current	≤ 20 mA
Status display	"DC OK" LED green
Note on status display	UOUT < 0.9 x UN: LED flashing
Conductor cross section solid min.	0.2 mm²
Conductor cross section solid max.	2.5 mm²
Conductor cross section stranded min.	0.2 mm²
Conductor cross section stranded max.	2.5 mm²

Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	12
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm
Screw thread	M3
Output name	DC OK floating
Output description	Relay contact, $U_{OUT} > 0.9 \times U_N$: Contact closed
Maximum switching voltage	≤ 30 V AC/DC
Maximum inrush current	≤ 1 A
Continuous load current	≤ 1 A
Status display	"DC OK" LED green
Note on status display	UOUT < 0.9 x UN: LED flashing
Output name	POWER BOOST, active
Output description	IOUT < IN: High signal
Maximum switching voltage	+ 24 V DC
Output voltage	+ 24 V DC
Maximum inrush current	≤ 20 mA (short circuit resistant)
Continuous load current	≤ 20 mA
Status display	LED "BOOST", yellow
Note on status display	I _{out} > I _N : LED on

Certificates / Approvals



Accessories







Certification ABS, CB, CSA, CUL, GL, UL, UL Listed

UL-EX LIS / CUL-EX LIS / LR / NV / BV Certifications applied for:

Item	Designation	Description

General	

2938235	UWA 182/52	Universal wall adapter

Drawings

Block diagram

