# **Detailed Specifications & Technical Data**





8205 Multi-Conductor - High-Conductivity Copper Speaker Cable Twisted Jacketed Con





## **Description:**

20 AWG stranded (7x28) tinned copper conductors, PVC insulation, twisted pairs, PVC jacket.

## **Physical Characteristics (Overall)**

#### Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material						
1	20	7x28	TC - Tinned Copper						

#### Insulation

**Insulation Material:** 

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.013

#### **Outer Shield**

**Outer Shield Material:** 

<b>Outer Shield Material</b>
Unshielded

#### **Outer Jacket**

**Outer Jacket Material:** 

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.025

#### **Overall Cabling**

Overall Nominal Diameter: 0.180 in.

#### Pair

Pair Color Code Chart:

Number	Color					
1	Black & Red					

Operating Temperature Range:	-20°C To +80°C
Bulk Cable Weight:	15.300 lbs/1000 ft.
Max. Recommended Pulling Tension:	28 lbs.
Min. Bend Radius (Install)/Minor Axis:	2 in.

### **Applicable Specifications and Agency Compliance (Overall)**

## **Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005

# **Detailed Specifications & Technical Data**





## 8205 Multi-Conductor - High-Conductivity Copper Speaker Cable Twisted Jacketed Con

EU Directive 2002/96/EC (WEEE): Yes EU Directive 2003/11/EC (BFR): Yes CA Prop 65 (CJ for Wire & Cable): Yes MII Order #39 (China RoHS): Yes **Flame Test** FT4 C(UL) Flame Test: Plenum/Non-Plenum Plenum (Y/N): No

#### **Electrical Characteristics (Overall)**

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

Max. Operating Voltage - UL:

Voltage 300 V RMS

Max. Recommended Current:

3.7 Amps per conductor @ 20°C

## **Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8205 060U1000	1,000 FT	18.000 LB	CHROME		1 PR #20 PVC FRPVC
8205 060U500	500 FT	9.000 LB	CHROME		1 PR #20 PVC FRPVC
8205 060100	100 FT	2.300 LB	CHROME		1 PR #20 PVC FRPVC
8205 0601000	1,000 FT	18.000 LB	CHROME	С	1 PR #20 PVC FRPVC
8205 060500	500 FT	9.000 LB	CHROME		1 PR #20 PVC FRPVC

Notes: C = CRATE REEL PUT-UP.

## Introduction

Belden® paired cable products are manufactured in a variety of gage sizes, dimensions, insulation materials, shielding configurations, and jacketing materials including Plenum and High-Temperature versions to meet the technical requirements of many different types of systems.

Paired cables allow balanced signal transmission, which results in lower crosstalk through common mode rejection. Due to the improved noise immunity of twisted pairs, they generally permit higher data speeds than multi-conductor cables.

As an aid to proper cable selection, both the suggested working voltages and the maximum temperature ratings are indicated for each applicable paired cable selection.

Most of our paired cables are available from stock. Many of these are available off the shelf from distributors. If you have a new or unusual application or you cannot find a paired cable in this catalog section that meets your technical requirements, contact Technical Support at 1-800-BELDEN-1.

#### **Paired Cables Packaging**

Belden's unique UnReel® cable dispenser is available for many of the paired cable products listed in this section. The letter "U" before the specified put-up length denotes UnReel packaging.



# **Unshielded**

Audio, Control and Instrumentation Cables

Description	Part	UL NEC/ C(UL) CEC Type	No. of Pairs	Color Code	Standard Lengths		Standard Unit Weight		Insulation Thickness		Jacket Thickness		Nominal OD	
	No.				Ft.	m	Lbs.	kg	inch	mm	Inch	mm	inch	mm
AWG Stranded (7x28	,		ctors • T	wisted Pa	irs									
PVC Insulation • Ch														
00V RMS	8205	NEC: CMG CEC: CMG FT4	1	See Chart 3 (Tech Info Section)	100 U-500 500 U-1000 1000	30.5 U-152.4 152.4 U-304.8 304.8	2.6 9.0 9.0 18.0 18.0	1.2 4.1 4.1 8.2 8.2	.013	.33	.025	.64	.180	4.57
L AWM Style 2464 100V 80°C)	9750	NEC: CMG CEC: CMG FT4	3	See Chart 3 (Tech Info Section)	500 1000	152.4 304.8	26.5 50.0	12.0 22.7	.013	.33	.035	.89	.299	7.59
	9751	NEC: CMG CEC: CMG FT4	6	See Chart 3 (Tech Info Section)	100 500 1000	30.5 152.4 304.8	9.1 45.0 89.0	4.1 20.5 40.5	.013	.33	.035	.89	.366	9.30
	9752	NEC: CMG CEC: CMG FT4	9	See Chart 3 (Tech Info Section)	100 500 1000	30.5 152.4 304.8	13.1 65.5 125.0	5.9 29.8 56.8	.013	.33	.035	.89	.429	10.9
	9755	NEC: CMG CEC: CMG FT4	15	See Chart 3 (Tech Info Section)	100 1000	30.5 304.8	17.9 194.0	8.1 88.2	.013	.33	.040	1.02	.545	13.84
9 AWG Solid Bare Cop	per Conduc	tors • Twisted	l Pair											
PVC Insulation • Ch														
00V RMS	8486	NEC: CM CEC: CM	1	Brown, Tan	U-500 U-1000 1000	U-152.4 U-304.8 304.8	9.5 18.0 19.0	4.3 8.2 8.6	.015	.38	.025	.64	.182	4.62
8 AWG Stranded (7x26	) Tinned Co	pper Conduc	tors • T	wisted Pai	r									
PVC Insulation • Ch	rome PVC	Jacket												
000V RMS	8461	NEC: CMG CEC: CMG FT4	1	Black, White	100 U-500 500 U-1000	30.5 U-152.4 152.4 U-304.8	3.2 14.0 13.5 26.0	1.4 6.4 6.1 11.8	.022	.56	.028	.71	.234	5.94

