
# **Detailed Specifications & Technical Data**

**ENGLISH MEASUREMENT VERSION** 



## 9L28010 Flat - Gray Ribbon 9L280XX Series







## **Description:**

Belden's .050" pitch gray ribbon cable was designed for general purpose electronic interconnect applications. The cable provides reliable mass-termination to standard IDC connectors.

## **Physical Characteristics (Overall)**

### Conductor

### AWG:

# Conductors	AWG	Stranding	<b>Conductor Material</b>
10	28	7x36	TC - Tinned Copper

Conductor Spacing Center to Center: .050 +/- .002

Conductor Spacing Outside Center to Outside .45 +/- .008

Center:

#### Insulation

### **Insulation Material:**

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.010

Insulation Resistance: >10, 000 Megaohms

## **Outer Shield**

#### **Outer Shield Material:**

Outer Shield Material Unshielded

## **Overall Cabling**

Overall Nominal Thickness: .035 +/- .003

Overall Nominal Width: .50 +/- .008

## **Mechanical Characteristics (Overall)**

Operating Temperature Range: -40°C To +105°C

## **Applicable Specifications and Agency Compliance (Overall)**

## **Applicable Standards & Environmental Programs**

UL AWM Style:	2651
UL Rating:	105°C, 300 V RMS, VW-1
CSA Specification:	AWM I A 105°C 300 V FT1
CSA Rating:	105°C, 300 V RMS, FT1
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes

# **Detailed Specifications & Technical Data**





## 9L28010 Flat - Gray Ribbon 9L280XX Series

CA Prop 65 (CJ for Wire & Cable):

MII Order #39 (China RoHS):

Yes

Flame Test
UL Flame Test:

VW-1

CSA Flame Test:

FT1

Plenum/Non-Plenum
Plenum (Y/N):

No

## **Surface Printing (Overall)**

Surface Printing: BELDEN-T 28 AWG CSA AWM I A 105°C 300 V FT1 LL7874 (UL LOGO) AWM STYLE 2651 VW-1 E12683

## **Electrical Characteristics (Overall)**

## Nom. Characteristic Impedance:

Description	Impedance (Ohm)	
(GS)	150	
(GSG)	105	

#### Nom. Inductance:

Description	Inductance (µH/ft)		
@ 1 MHz (GS)	.29		
@ 1 MHz (GSG)	.20		

### Nom. Capacitance Conductor to Conductor:

Description	Capacitance (pF/ft)
@ 1 kHz (GSG)	18
@ 1 MHz (GS)	10
@ 1 MHz (GSG)	15

## **Nominal Velocity of Propagation:**

Description	VP (%	)
	72	

### **Nominal Delay:**

Delay (ns/ft) 1.40 NS/FT. (GSG)

## Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 68.2 OHMS/1000 FT. MAX.

## Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
10	2.8
20	4.8
30	6.5
40	8.3
50	9.8
60	12
70	13
80	14
90	15.8
100	17

### Max. Operating Voltage - UL:

Voltage 300 V RMS

### Max. Recommended Current:

Current
1 Amp per conductor @ 20°C

# **Detailed Specifications & Technical Data**

## **ENGLISH MEASUREMENT VERSION**



# 9L28010 Flat - Gray Ribbon 9L280XX Series

**Dielectric Withstand Voltage:** 2, 000 V RMS

Typical Unbalanced Crosstalk:

Description	Pulse Rise Time (NS) (MHz)	Near End % (MHz)	Far End % (MHz)
10 ft. sample length	3	4.8	7
10 ft. sample length	5	3.5	4.7
10 ft. sample length	7	3	3

## Notes (Overall)

Notes: GS=Ground-Signal Mode; GSG=Ground-Signal-Ground Mode

# Polarity Identification (Overall)

Polarity Identification: RED POLARITY STRIPE ON #1 CONDUCTOR

## **Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9L28010 008H100	100 FT	1.200 LB	GRAY		10 #28 STR PVC RIBBON
9L28010 008H300	300 FT	3.600 LB	GRAY		10 #28 STR PVC RIBBON

# **Gray Ribbon 9L280XX Series**

.050" Pitch, 28 AWG, PVC

#### **Product Description**

Belden's (9L280XX Series) .050" pitch extruded gray ribbon cable was designed for general purpose electronic interconnect applications. The cable provides reliable mass-termination to standard .100" contact IDC connectors, flexibility, consistent electricals and breakouts can be made easily with the tear feature design. The cable is constructed of stranded 28 AWG (7x36) tinned copper conductors. Insulation material consists of Gray PVC, with a Red polarity stripe for proper circuit alignment. Various conductor counts are standard; other sizes are available upon request. The cable is UL approved and CSA certified, and passes the VW-1 Vertical Wire Flame Test.

Color Code: Gray with Red polarity stripe (standard).

**Application:** Internal interconnection or internal wiring of electronic equipment.

#### **Physical Specifications**


Conductor	28 AWG (7x36) Tinned Copper
Insulation	.010" Nom. Wall Gray PVC
Pitch	.050" ± .002"
Temperature Rating	-40 to +105°C
Flammability Rating	UL: VW-1; CSA: FT1
UL Approval	File #E12683, Style 2651
CSA Approval	File #LL7874, CSA AWM I A 105°C 300V FT1
Packaging	H100, H300, R300


#### **Electrical Specifications**

Voltage Rating	300V RMS
Current Rating	1A
Conductor Resistance	68.2Ω/1000 ft.
Insulation Resistance	>1 x 10¹⁰Ω • 10 ft. (3m)
Impedance*	105Ω
Capacitance* (@ 1 MHz)	15 pF/ft. (49 pF/m)
Inductance* (@ 1 MHz)	.20 μH/ft. (.66 μH/m)
Propagation Delay*	1.40 ns/ft. (4.6 ns/m)

<sup>\*</sup>Test Configuration: G-S-G (ground-signal-ground).

### **Unbalanced Crosstalk\***






Part No. Standard [UL & CSA]	No. of Cond.	Dimensions			
		Width "A"		Span "B"	
		Inch	mm	Inch	mm
9L28009	9	.45 ±.008	11.43 ±.20	.40 ±.008	10.16 ±.20
9L28010	10	.50 ±.008	12.70 ±.20	.45 ±.008	11.43 ±.20
9L28014 <sup>†</sup>	14	.70 ±.008	17.78 ±.20	.65 ±.008	16.51 ±.20
9L28015**	15	.75 ±.008	19.05 ±.20	.70 ±.008	17.78 ±.20
9L28016	16	.80 ±.008	20.32 ±.20	.75 ±.008	19.05 ±.20
9L28020	20	1.00 ±.008	25.40 ±.20	.95 ±.008	24.13 ±.20
9L28024 <sup>†</sup>	24	1.20 ±.008	30.48 ±.20	1.15 ±.008	29.21 ±.20
9L28025	25	1.25 ±.008	31.75 ±.20	1.20 ±.008	30.48 ±.20
9L28026	26	1.30 ±.008	33.02 ±.20	1.25 ±.008	31.75 ±.20
9L28034	34	1.70 ±.008	43.18 ±.20	1.65 ±.008	41.91 ±.20
9L28036**	36	1.80 ±.012	45.72 ±.30	1.75 ±.012	44.45 ±.30
9L28037**	37	1.85 ±.012	46.99 ±.30	1.80 ±.012	45.72 ±.30
9L28040	40	2.00 ±.012	50.80 ±.30	1.95 ±.012	49.53 ±.30
9L28050	50	2.50 ±.012	63.50 ±.30	2.45 ±0.12	62.23 ±.30
9L28060	60	3.00 ±.012	76.20 ±.30	2.95 ±.012	74.93 ±.30
9L28064	64	3.20 ±.012	81.28 ±.30	3.15 ±.012	80.01 ±.30

<sup>\*\*</sup> Available in H100 packaging only.

#### **Dimensions**





<sup>†</sup> Not available in R300 packaging.