Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



9952 Multi-Conductor - 2 Conductors Cabled-Communication and Instrumentation Cable





Description:

16 AWG stranded (19x29) tinned copper conductors, conductors cabled, nylon skin over insulation, PVC insulation, tinned copper braid shield (90% coverage), PVC jacket.

Physical Characteristics (Overall)	
Conductor	
AWG:	
# Conductors AWG Stranding Conductor Material	
2 16 19x29 TC - Tinned Copper	
Insulation	
Insulation Material:	
Layer # Insulation Material Wall Thickness (in.)	
1 PVC - Polyvinyl Chloride .012 2 Nylon .004	
2 Nylon .004	
Insulation Resistance:	500 megohms/1000 ft. @ 500 VDC
Outer Shield	
Outer Shield Material:	
TypeOuter Shield Material Coverage (%)BraidTC - Tinned Copper90	
Outer Jacket	
Outer Jacket Material: Outer Jacket Material Nom. Wall Thickness (in.)	
PVC - Polyvinyl Chloride .025	
Overall Cabling Overall Cabling Lay Length & Direction:	
Length (in.) Twists (ft.)	
2.125 5.6	
Overall Cabling Color Code Chart:	
Number Color	
1 White	
2 Black	
Overall Nominal Diameter:	0.250 in.
Mechanical Characteristics (Overall)	
Operating Temperature Range:	-20°C To +105°C
UL Temperature Rating:	105°C
Bulk Cable Weight:	38.200 lbs/1000 ft.
Max. Recommended Pulling Tension:	60.800 lbs.
Min. Bend Radius (Install)/Minor Axis:	2.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

Yes



ENGLISH MEASUREMENT VERSION

-

9952 Multi-Conductor - 2 Conductors Cabled-Communication and Instrumentation Cable

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Military Specification:	MIL-W-16878E/17 (insulated conductor)
Flame Test	
UL Flame Test:	UL1685 UL Loading, VW-1
Plenum/Non-Plenum	
Plenum (Y/N):	No
57 Nom. Capacitance Cond. to Other Conductor & Sh	ield:
95	
Nom. Conductor DC Resistance: DCR @ 20°C (Ohm/1000 ft) 4.3 Nominal Outer Shield DC Resistance:	
DCR @ 20°C (Ohm/1000 ft) 5.7	
Max. Operating Voltage - UL:	
Voltage 600 V RMS	
Max. Recommended Current:	
Current 6.5 Amps per conductor @ 25°C	
Put Ups and Colors:	

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9952 009100	100 FT	4.600 LB	WHITE		2 #16 PVC/NY SHLD PVC
9952 0091000	1,000 FT	42.000 LB	WHITE	С	2 #16 PVC/NY SHLD PVC
9952 009500	500 FT	19.000 LB	WHITE		2 #16 PVC/NY SHLD PVC

Notes: C = CRATE REEL PUT-UP.

Introduction

Belden® multi-conductor cables are manufactured in a wide variety of gage sizes, dimensions, insulation materials, shielding configurations, and jacketing materials including Plenum and High-Temperature versions. These cables meet the technical requirements of many different types of systems. In fact, Belden offers one of the broadest lines of UL Listed, NEC and CEC multi-conductor cables available from any single source.

Applications for multi-conductor cables include computers, communications, instrumentation, sound, control, audio, and data transmission. Each of these cables is designed to protect signal integrity under critical conditions by reducing hum, noise, and crosstalk.

To assist you in selecting the proper cable for your application, both the suggested working voltages and the maximum temperature ratings are indicated for each applicable product in this section.

Most of our multi-conductor cables are available from stock. Many of these are available off the shelf from distributors. If you have a new or unusual application or you cannot find a multi-conductor cable in this catalog section that meets your technical requirements, contact Technical Support at 1-800-BELDEN-1.

Multi-Conductor Cables Packaging

BELDEN

Belden's unique UnReel® cable dispenser is available for many of the multi-conductor products listed in this section. The letter "U" before the specified put-up length denotes UnReel packaging.

Selection Guide

Shielded Multi-Conductor Computer Cables for RS-232 Applications

4.2

				Cable	Series*	
Specifica	tions		9925	9608	9533	9939
Conductor Si	ze:	28				
(AWG)		24	1	1	1	
		22				1
		20				
		18				
	Pac	ge No.	4.18	4.17	4.11	4.19
Insulation:	S-R PVC	, 		1	1	1
	Polyethylene					
	Polypropylen	e				
	Datalene [®] [†]		1			
Shield:	Overall Foil				1	
	Drain Wire		1		1	
	Overall Foil/B	raid	1	1		1
	Braid Covera		65%	65%		65%
Drain Wire O			Yes	No	Yes	No
No. of Cond.	Available:	1				
		2				
		3	1	1	1	1
		4	1	1	1	1
		5	1	1	1	1
		6	1	1	1	1
		7	1	1	1	1
		8	1	1	1	1
		9	1	1	1	1
		10	1	1	1	1
		11				
		12				
		13				
		15	1	1	1	1
		17				
		18				
		19				
		20			1	
		25	1	1	1	1
		27				
		30			1	
		31				
		37	1	1		1
		40			1	
		50		1	1	1
Capacitance	** (pF/ft.)		12.0	30.0	30.0	35.0

*All cables are LII -listed

**Capacitance may vary on some cables [†]Foam high density polyethylene.

Overall Braid Shield

MIL-W-16878 (Type B) Conductors, Shielded and Jacketed⁺ **Communication and Instrumentation Cables**

Description	Part UL NEC/ No.			Standard Lengths		Standard Unit Weight		Insulation Thickness		Jacket Thickness		Nomin	Nominal OD		Nominal Capacita			
	No.	C(UL) CEC Type	of Cond.	Code	Ft.	m	Lbs.	kg	Inch	mm	Inch	mm	Inch	mm	pF/ Ft.	pF/ m	pF/ Ft.	** pF/ m
22 AWG Stranded (19	9x34) 1	C Condu	ctors •	.003″ (.76	6mm) Clea	ar Nylon S	Skin ov	/er Ins	sulatio	n • Tir	nned C	Coppe	r Braid	d Shiel	ld (90	0% C	overa	age)
PVC Insulation • V	Vhite	PVC Jac	cket															
600V RMS 105°C VW-1	9965	—	1	White	1000	304.8	10.0	4.5	.010	.25	.010	.25	.100	2.54	—	—	100	328
	9966	_	2	White, Black	100 500 1000	30.5 152.4 304.8	2.9 10.5 19.0	1.3 4.8 8.7	.010	.25	.020	.51	.176	4.47	52	171	87	285
	9967	—	3 ^{††}	White, Black, Red	100 500 1000	30.5 152.4 304.8	3.4 13.0 24.0	1.5 5.9 10.9	.010	.25	.020	.51	.184	4.67	45	148	88	289
	9968	—	4††	White, Black, Red, Green	100 500 1000	30.5 152.4 304.8	3.9 14.5 29.0	1.8 6.6 13.2	.010	.25	.020	.51	.200	5.08	42	138	69	226

20 AWG Stranded (19x32) Tinned Copper Conductors • .004" (.10mm) Clear Nylon Skin over Insulation • TC Braid Shield (90% Coverage)

PVC Insulation •	White	PVC Ja	icket															
600V RMS 105°C VW-1	9961	_	1	White	500 1000	152.4 304.8	4.5 9.0	2.0 4.1	.011	.27	.010	.25	.109	2.77	_	_	103	338
	9962	—	2 ^{††}	White, Black	100 500 1000	30.5 152.4 304.8	3.3 11.0 22.0	1.5 5.0 10.0	.011	.27	.020	.51	.192	4.88	53	174	91	299
	9963	—	3 ^{††}	White, Black, Red	100 500 1000	30.5 152.4 304.8	3.9 14.5 29.0	1.8 6.6 13.2	.011	.27	.025	.64	.210	5.33	49	161	84	276
	9964		4††	White, Black, Red, Green	100 500 1000	30.5 152.4 304.8	4.6 18.0 39.0	2.1 8.2 17.7	.011	.27	.025	.64	.226	5.74	40	131	100	328

16 AWG Stranded (19x29) Tinned Copper Conductors • .004" (.10mm) Clear Nylon Skin over Insulation • TC Braid Shield (90% Coverage) PVC Insulation • White PVC Jacket

i vo moulution			lonet															
600V RMS 105°C	9951	_	1	White	1000	304.8	20.0	9.1	.012	.30	.016	.41	.143	3.63	_	_	138	453
VW-1	9952	—	2 ^{††}	White, Black	100 500	30.5 152.4	4.6 19.0	2.1 8.7	.012	.30	.025	.64	.250	6.35	57	187	95	312
				Diaon	1000	304.8	42.0	19.1										
	9953	—	3††	White, Black, Red	100 500 1000	30.5 152.4 304.8	5.2 26.0 56.0	2.4 11.9 25.5	.012	.30	.025	.64	.264	6.71	58	190	101	331
	9954	_	4††	White, Black, Red, Green	100 500 1000	30.5 152.4 304.8	7.7 34.5 73.0	3.5 15.7 33.1	.012	.30	.027	.69	.291	7.39	49	161	94	308

TC = Tinned Copper

* Capacitance between conductors.

** Capacitance between one conductor and other conductors connected to shield.

[†] Manufactured to Government specifications: MIL-W-16878 Rev. D. ^{††} Conductors cabled.

