


2412 Multi-Conductor - Enhanced Category 6 Nonbonded-Pair Cables



For more Information
please call

1-800-Belden1



General Description:

CAT6+ (350MHz), 4-Pair, U/UTP-Unshielded, Riser-CMR, Premise Horizontal Cable, 23 AWG Solid Bare Copper Conductors, Polyolefin Insulation, Tape Separator, Ripcord, PVC Jacket

Usage (Overall)

Suitable Applications: Premise Horizontal Cable, Gigabit Ethernet, POE, POE+, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM

Physical Characteristics (Overall)

Conductor

AWG:

| # Pairs | AWG | Stranding | Conductor Material |
|---------|-----|-----------|--------------------|
| 4 | 23 | Solid | BC - Bare Copper |

Total Number of Conductors: 8

Insulation

Insulation Material:

| Insulation Material |
|---------------------|
| PO - Polyolefin |

Outer Shield

Outer Shield Material:

| Outer Shield Material |
|-----------------------|
| Unshielded |

Outer Jacket

Outer Jacket Material:

| Outer Jacket Material |
|--------------------------|
| PVC - Polyvinyl Chloride |

Outer Jacket Diameter:

| Nom. Dia. (in.) |
|-----------------|
| 0.223 |

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Separator Material: Patented Dielectric Tape

Overall Nominal Diameter: 0.220 in.

Pair

Pair Color Code Chart:

| Number | Color |
|--------|--------------------------------|
| 1 | White/Blue Stripe and Blue |
| 2 | White/Orange Stripe and Orange |
| 3 | White/Green Stripe and Green |
| 4 | White/Brown Stripe and Brown |

Mechanical Characteristics (Overall)

Storage Temperature Range: -20°C To +75°C

Installation Temperature Range: +5°C To +50°C

Operating Temperature Range: 0°C To +75°C

Bulk Cable Weight: 24 lbs/1000 ft.

Max. Recommended Pulling Tension: 40 lbs.

Min. Bend Radius/Minor Axis: 0.750 in.

Min. Bend/Installation: 2.250 in.

2412 Multi-Conductor - Enhanced Category 6 Nonbonded-Pair Cables

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

| | |
|---------------------------------------|--|
| NEC(UL) Specification: | CMR |
| CEC/C(UL) Specification: | CMR |
| EU Directive 2011/65/EU (ROHS II): | Yes |
| EU CE Mark: | Yes |
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2002/95/EC (RoHS): | Yes |
| EU RoHS Compliance Date (mm/dd/yyyy): | 01/01/2004 |
| EU Directive 2002/96/EC (WEEE): | Yes |
| EU Directive 2003/11/EC (BFR): | Yes |
| CA Prop 65 (CJ for Wire & Cable): | Yes |
| MII Order #39 (China RoHS): | Yes |
| Telecommunications Standards: | Category 6 - TIA 568.C.2 |
| ANSI Specification: | ANSI/NEMA WC-66, ANSI/ICEA S-90-661, ANSI/UL 444 |
| Other Specification: | Third party verified to Category 6 |

Applicable Patents:

Country

www.belden.com/p

Flame Test

| | |
|-------------------|-----------------------|
| UL Flame Test: | UL1666 Vertical Riser |
| C(UL) Flame Test: | FT4 |
| CSA Flame Test: | FT4 |

Plenum/Non-Plenum

| | |
|----------------|------|
| Plenum (Y/N): | No |
| Plenum Number: | 2413 |

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/ft)

17.000

Maximum Capacitance Unbalance (pF/100 m): 330

Nominal Velocity of Propagation:

VP (%)

70

Maximum Delay:

Delay (ns/100 m)

537 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m)

35.000

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)

7.800

Max. Operating Voltage - UL:

Voltage

300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

3.000

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

| Freq. (MHz) | Max. Attenuation (dB/100 m) | Min. NEXT (dB) | Min. PSNEXT (dB) | Min. ACR (dB) | Min. PSACR (dB) | Min RL (dB) |
|-------------|-----------------------------|----------------|------------------|---------------|-----------------|-------------|
| 1 | 2.000 | 75.3 | 75.3 | 73.3 | 73.3 | 20.000 |
| 4 | 3.700 | 66.3 | 66.3 | 62.6 | 62.6 | 23.000 |

2412 Multi-Conductor - Enhanced Category 6 Nonbonded-Pair Cables

| | | | | | | |
|-------|--------|------|------|-------|-------|--------|
| 8 | 5.200 | 61.8 | 61.8 | 56.6 | 56.6 | 24.500 |
| 10 | 5.800 | 60.3 | 60.3 | 54.5 | 54.5 | 25.000 |
| 16 | 7.400 | 57.2 | 57.2 | 49.9 | 49.9 | 25.000 |
| 20 | 8.300 | 55.8 | 55.8 | 47.5 | 47.5 | 25.000 |
| 25 | 9.300 | 54.3 | 54.3 | 45.1 | 45.1 | 24.300 |
| 31.25 | 10.400 | 52.9 | 52.9 | 42.5 | 42.5 | 23.600 |
| 62.5 | 15.000 | 48.4 | 48.4 | 33.4 | 33.4 | 21.500 |
| 100 | 19.300 | 45.3 | 45.3 | 26.0 | 26.0 | 20.800 |
| 155 | 24.600 | 42.4 | 42.4 | 17.9 | 17.9 | 19.500 |
| 200 | 28.300 | 40.8 | 40.8 | 12.5 | 12.5 | 18.700 |
| 250 | 32.100 | 39.3 | 39.3 | 7.2 | 7.2 | 18.000 |
| 300 | 35.600 | 38.1 | 36.1 | 2.5 | 0.5 | 17.500 |
| 350 | 38.900 | 37.1 | 35.1 | -1.8 | -3.8 | 17.000 |
| 400 | 42.000 | 36.3 | 34.3 | -5.7 | -7.7 | 16.600 |
| 450 | 45.000 | 35.5 | 33.5 | -9.5 | -11.5 | 16.200 |
| 500 | 47.900 | 34.8 | 32.8 | -13.1 | -15.1 | 15.900 |
| 550 | 50.600 | 34.2 | 32.2 | -16.4 | -18.4 | 15.600 |

Premise Cable Electrical Table 2:

| Freq. (MHz) | Input (Unfitted) Imp. (Ohms) | Fitted Impedance | Min. ACRF (dB) | Min. PSACRF (dB) |
|-------------|------------------------------|------------------|----------------|------------------|
| 1 | 100 ± 15 | 102 ± 15 | 70.8 | 67.8 |
| 4 | 100 ± 15 | 100 ± 15 | 58.8 | 55.8 |
| 8 | 100 ± 15 | 100 ± 15 | 52.7 | 49.7 |
| 10 | 100 ± 15 | 100 ± 15 | 50.8 | 47.8 |
| 16 | 100 ± 15 | 100 ± 15 | 46.7 | 43.7 |
| 20 | 100 ± 15 | 100 ± 15 | 44.8 | 41.8 |
| 25 | 100 ± 15 | 100 ± 15 | 42.8 | 39.8 |
| 31.25 | 100 ± 15 | 100 ± 15 | 40.9 | 37.9 |
| 62.5 | 100 ± 15 | 100 ± 15 | 34.9 | 31.9 |
| 100 | 100 ± 15 | 100 ± 15 | 30.8 | 27.8 |
| 155 | 100 ± 22 | 100 ± 15 | 27.0 | 24.0 |
| 200 | 100 ± 22 | 100 ± 15 | 24.8 | 21.8 |
| 250 | 100 ± 32 | 100 ± 15 | 22.8 | 19.8 |
| 300 | 100 ± 32 | 100 ± 15 | 21.3 | 18.3 |
| 350 | 100 ± 32 | 100 ± 15 | 19.9 | 16.9 |
| 400 | 100 ± 32 | 100 ± 15 | 18.8 | 15.8 |
| 450 | 100 ± 32 | 100 ± 15 | 17.7 | 14.7 |
| 500 | 100 ± 32 | 100 ± 15 | 16.8 | 13.8 |
| 550 | 100 ± 32 | 100 ± 15 | 16.0 | 13.0 |

Notes (Overall)

Notes: Jacket sequentially marked at 2 ft./1m intervals. Third party verified to ANSI/TIA-568-C.2, Category 6. Values above 350 MHz are for Engineering Information Only. In addition to the colors below, Pink is also available as a special, p/n 2412 012 U1000, or 2412 012 A1000.

Reference (Overall)

Previous Part Number:

24566415, 25066515T, 24566745, 24566745T, 24566745T+HU, 24566736T, 24566715, 24566715T, 25066885, 25066885T, 25066815T, 24566945, 24566945T, 24566945T+HU, 24566931, 24566931T, 24566931T+HU, 24566936T, 24566915, 24566915T, 24566915T+HU, 24566015, 24566015T, 24566P15, 24566P15T, 24566185, 24566185T, 24566185T+HU, 24566115T, 24566345, 24566345T, 24566345T+HU, 24566336T, 24566315, 24566315T, 24566315T+HU, 24566485, 24566485T, 24566415T, 24566415T

Put Ups and Colors:

| Item # | Putup | Ship Weight | Color | Notes | Item Desc |
|---------------|----------|-------------|-------------|-------|--------------------------|
| 2412 002A1000 | 1,000 FT | 27.000 LB | RED | C | CAT6+ 4PR U/UTP CMR RIB |
| 2412 003A1000 | 1,000 FT | 27.000 LB | ORANGE | | CAT6+ 4PR U/UTP CMR RIB |
| 2412 003U1000 | 1,000 FT | 24.000 LB | ORANGE | | CAT6+ 4PR U/UTP CMR BOX |
| 2412 004A1000 | 1,000 FT | 27.000 LB | YELLOW | | CAT6+ 4PR U/UTP CMR RIB |
| 2412 004U1000 | 1,000 FT | 24.000 LB | YELLOW | | CAT6+ 4PR U/UTP CMR BOX |
| 2412 0041000 | 1,000 FT | 24.000 LB | YELLOW | | CAT6+ 4PR U/UTP CMR REEL |
| 2412 0042500 | 2,500 FT | 60.000 LB | YELLOW | | CAT6+ 4PR U/UTP CMR REEL |
| 2412 005A1000 | 1,000 FT | 27.000 LB | GREEN, DARK | | CAT6+ 4PR U/UTP CMR RIB |
| 2412 005U1000 | 1,000 FT | 24.000 LB | GREEN, DARK | | CAT6+ 4PR U/UTP CMR BOX |
| 2412 0051000 | 1,000 FT | 24.000 EA | GREEN, DARK | | CAT6+ 4PR U/UTP CMR REEL |
| 2412 006A1000 | 1,000 FT | 27.000 LB | BLUE, LIGHT | | CAT6+ 4PR U/UTP CMR RIB |
| 2412 006U1000 | 1,000 FT | 24.000 LB | BLUE, LIGHT | | CAT6+ 4PR U/UTP CMR BOX |
| 2412 0061000 | 1,000 FT | 24.000 EA | BLUE, LIGHT | | CAT6+ 4PR U/UTP CMR REEL |
| 2412 0061400 | 1,400 FT | 35.000 LB | BLUE, LIGHT | | CAT6+ 4PR U/UTP CMR REEL |

2412 Multi-Conductor - Enhanced Category 6 Nonbonded-Pair Cables

| | | | | | |
|---------------|----------|------------|-------------|---|--------------------------|
| 2412 0062500 | 2,500 FT | 60.000 LB | BLUE, LIGHT | | CAT6+ 4PR U/UTP CMR REEL |
| 2412 0065000 | 5,000 FT | 125.000 LB | BLUE, LIGHT | C | CAT6+ 4PR U/UTP CMR REEL |
| 2412 007A1000 | 1,000 FT | 27.000 LB | VIOLET | | CAT6+ 4PR U/UTP CMR RIB |
| 2412 007U1000 | 1,000 FT | 24.000 LB | VIOLET | | CAT6+ 4PR U/UTP CMR BOX |
| 2412 008A1000 | 1,000 FT | 27.000 LB | GRAY | | CAT6+ 4PR U/UTP CMR RIB |
| 2412 008U1000 | 1,000 FT | 24.000 LB | GRAY | | CAT6+ 4PR U/UTP CMR BOX |
| 2412 0081000 | 1,000 FT | 24.000 EA | GRAY | | CAT6+ 4PR U/UTP CMR REEL |
| 2412 009A1000 | 1,000 FT | 27.000 LB | WHITE | | CAT6+ 4PR U/UTP CMR RIB |
| 2412 009U1000 | 1,000 FT | 24.000 LB | WHITE | | CAT6+ 4PR U/UTP CMR BOX |
| 2412 0091000 | 1,000 FT | 24.000 EA | WHITE | | CAT6+ 4PR U/UTP CMR REEL |
| 2412 0092500 | 2,500 FT | 60.000 LB | WHITE | | CAT6+ 4PR U/UTP CMR REEL |
| 2412 0095000 | 5,000 FT | 125.000 LB | WHITE | C | CAT6+ 4PR U/UTP CMR REEL |
| 2412 010A1000 | 1,000 FT | 27.000 LB | BLACK | | CAT6+ 4PR U/UTP CMR RIB |
| 2412 010U1000 | 1,000 FT | 24.000 LB | BLACK | | CAT6+ 4PR U/UTP CMR BOX |
| 2412 0101000 | 1,000 FT | 24.000 EA | BLACK | | CAT6+ 4PR U/UTP CMR REEL |

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 6 Revision Date: 06-09-2016

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).