


## 7933A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable



For more Information  
please call

1-800-Belden1



### General Description:

24 AWG Bonded-Pairs solid bare copper conductors, polyolefin insulation, overall Beldfoil® shield (100% coverage) with drain wire, .030" industrial grade sunlight- and oil-resistant PVC jacket, drain wire. Sequential marking at two foot intervals.

### Usage (Overall)

**Suitable Applications:**

Industrial Ethernet, Harsh Environments, 200MHz Category 5e, M-12 Compatible, 100Base TX, 100BaseVG ANYLAN, 155A TM, 622A TM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, Noisy Environments, RJ-45 Compatible, EtherNet/IP

### Physical Characteristics (Overall)

#### Conductor

**AWG:**

# Pairs	AWG	Stranding	Conductor Material
2	24	Solid	BC - Bare Copper

**Total Number of Conductors:** 4

#### Insulation

**Insulation Material:**

Insulation Material
PO - Polyolefin

#### Outer Shield

**Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

**Outer Shield Drain Wire AWG:**

AWG	Stranding	Drain Wire Conductor Material
24	7x32	TC - Tinned Copper

#### Outer Jacket

**Outer Jacket Material:**

Outer Jacket Material
Industrial Grade PVC - Polyvinyl Chloride

#### Overall Cable

**Overall Nominal Diameter:** 0.235 in.

#### Pair

**Pair Color Code Chart:**

Number	Color
1	White/Orange Stripe & Orange
2	White/Green Stripe & Green

### Mechanical Characteristics (Overall)

**Storage Temperature Range:** -40°C To +85°C

**Installation Temperature Range:** -25°C To +75°C

**Operating Temperature Range:** -40°C To +75°C

## 7933A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

<b>Bulk Cable Weight:</b>	30 lbs/1000 ft.
<b>Max. Recommended Pulling Tension:</b>	20 lbs.
<b>Min. Bend Radius/Minor Axis:</b>	0.500 in.

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

<b>NEC/(UL) Specification:</b>	CMR
<b>CEC/C(UL) Specification:</b>	CMR
<b>EU Directive 2011/65/EU (ROHS II):</b>	Yes
<b>EU Directive 2000/53/EC (ELV):</b>	Yes
<b>EU Directive 2002/95/EC (RoHS):</b>	Yes
<b>EU RoHS Compliance Date (mm/dd/yyyy):</b>	01/01/2004
<b>EU Directive 2002/96/EC (WEEE):</b>	Yes
<b>EU Directive 2003/11/EC (BFR):</b>	Yes
<b>CA Prop 65 (CJ for Wire &amp; Cable):</b>	Yes
<b>MII Order #39 (China RoHS):</b>	Yes
<b>Other Specification:</b>	NEMA WC-63.1 Category 5e, UL verified to Category 5e, EtherNet/IP Compliant

#### Applicable Patents:

<b>Country</b>
www.belden.com/p

#### Flame Test

<b>UL Flame Test:</b>	UL1666 Riser
<b>CSA Flame Test:</b>	FT4

#### Suitability

<b>Suitability - Outdoor:</b>	Yes
<b>Sunlight Resistance:</b>	Yes
<b>Oil Resistance:</b>	Yes

#### Plenum/Non-Plenum

<b>Plenum (Y/N):</b>	No
----------------------	----

### Electrical Characteristics (Overall)

#### Nom. Mutual Capacitance:

<b>Capacitance (pF/ft)</b>
15

<b>Maximum Capacitance Unbalance (pF/100 m):</b>	150
--	-----

#### Nominal Velocity of Propagation:

<b>VP (%)</b>
70

#### Maximum Delay:

<b>Delay (ns/100 m)</b>
538 @ 100MHz

#### Max. Delay Skew:

<b>Delay Skew (ns/100 m)</b>
45

#### Maximum Conductor DC Resistance:

<b>DCR @ 20°C (Ohm/100 m)</b>
9.38

## 7933A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

### Max. Operating Voltage - UL:

<b>Voltage</b>
300 V RMS

### Maximum DCR Unbalanced:

<b>DCR Unbalance @ 20°C (%)</b>
3

## Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)	Min. SRL (dB)
1	2.0	65.3	62.3	63.0	60.0	20.0	23
4	4.1	56.3	53.3	51.0	49.0	23.6	23.0
8	5.8	51.8	48.8	46.0	43.0	25.4	24.5
10	6.5	50.3	47.3	43.0	41.0	26.0	25.0
16	8.2	47.3	44.3	39.0	36.0	26.0	25.0
20	9.3	45.8	42.8	36.5	33.5	26.0	25.0
25	10.4	44.3	41.3	33.9	30.9	25.5	24.3
31.25	11.7	42.9	39.9	31.0	28.0	25.0	23.6
62.5	17.0	38.4	35.4	22.0	19.0	23.5	21.5
100	22.0	35.3	32.3	14.0	11.0	22.5	20.1
155	28.1	32.5	29.5	4.4	1.4	15.8	
200	32.0	30.8	27.8	4.0	1.0	15.0	

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	102.5 ± 7.5	63.8	60.8
4	100 ± 15	102.5 ± 7.5	51.7	48.7
8	100 ± 15	101 ± 6	45.7	42.7
10	100 ± 15	101 ± 6	43.8	40.8
16	100 ± 15	101 ± 6	39.7	36.7
20	100 ± 15	101 ± 6	37.7	34.7
25	100 ± 15	101 ± 6	35.8	32.8
31.25	100 ± 15	101 ± 6	33.9	30.9
62.5	100 ± 15	101 ± 6	27.8	24.8
100	100 ± 15	101 ± 6	23.8	20.8
155	100 ± 25	100 ± 15	19.9	16.9
200	100 ± 25	100 ± 15	17.7	14.7

## Notes (Overall)

**Notes:** EtherNet IP is a trademark of ControlNet International Ltd. under license by DeviceNet Vendor Association, Inc. Operating Temperature subject to length de-rating.

**Notes (Cont'd.):** Cable passes -40C Cold Bend per UL 1581.

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7933A 0101000	1,000 FT	33.000 LB	BLACK	C	2 PR #24 PP FS FRPVC
7933A 0102000	2,000 FT	66.000 LB	BLACK	C	2 PR #24 PP FS FRPVC
7933A 1NH1000	1,000 FT	33.000 LB	TEAL 1NH	C	2 PR #24 PP FS FRPVC

**Notes:**  
C = CRATE REEL PUT-UP.

Revision Number: 9    Revision Date: 03-11-2014

© 2014 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

## 7933A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.