

BEST 5





2000 Series Digital Panel Meters

MODUTEC



2100 Series with DIP switch selections and multiple power options.

Backlighting Options

- Positive Green Black on Green Background
- Negative Green Green on Black Background
- Positive Red Black on Red Background
- Negative Red Red on Black Background
- Non-Backlit LCD Black on Grey Background

Customize for features that are important to you and rely on industry standards for routine digital PM elements.

You need flexibility. We provide it. We customize our meters to meet your specifications.

- Scalable in engineering units
- Custom labels for special readouts
- User Selectable functions, decimal point, offset, span, process voltage or current, DC voltage
- · Red or green backlit display

You need reliability. The MODUTEC 2000 Series operates in the harshest environments.

- Splash and hose proof meeting NEMA 4, NEMA 12, and IPC 55 standards
- Resistant to damage with a high impact polycarbonate case
- Wide operating temperature ranging from -4°F to +140°F (-20°C to +60°C)


You need standards. The Modutec 2000 Series gives you industry standards designed in.

- 1/8 DIN industry standard cut-out and 1 inch depth
- Screw terminals
- Over range indication
- Low cost
- The Moduted 2100 includes user-friendly dipswitch selection features

Applications


- ► Telecommunications
- **▶** Water Purification
- ► Sewage Treatment
- ► Flow
- **▶** Process
- ► Desalinization
- ► Temperature
- ► AC & DC Amps
- ► AC & DC Volts

2000 & 2100 Series Dimensional Drawings (mm/in)




Panel Cutout Notes:

- 1. For optimum water resistance use cutout height of 43 MM (1.693 Inches).
- 2. Panel thickness .81 to 6.35 MM (.032 to .250 Inches).



Rear View






Figure A

Figure B


Decimal Point: Three positions, external selection

Normal Mode Rejection: ≥ 40 db 50Hz-60Hz

		89.9		>
		3.54		
┫	•			⊕
	0		0	
	•		•	
₫	990	90000	0	⊕
	_+ :	=05250	= AC	Power
	>	IN H DP1 DP2 DP3 DP3	AC F	

Input Type	Figure	A (mm/in)	B (mm/in)		
AC	Α	25.1/.99	29.2/1.15		
DC	Α	25.1/.99	29.2/1.15		
Temperature	Α	25.1/.99	29.2/1.15		
4-20mA Process	В	37.8/1.49	50.8/2.00		
Frequency	Α	25.1/.99	29.2/1.15		

Connection for High Current Measurement



2000 and 2100 Series Specifications

Display

Digits: 3 ¹/₂ digits, 7 segments Backlit LCD (1999)

Polarity: Automatic (-) displayed

Overload: Three lower digits blank for readings

greater than 1999

Performance

Conversion Rate: 2.5 per second

Common Mode Rejection: ≥ 100db 50 Hz-60 Hz¹

Tempco: ±200 PPM/°C typical²

Zero Adjust: Automatic Warmup: 10 minutes

Digit Height: 0.5" (12.7 mm)

Operating Range: $-4^{\circ}F$ to $140^{\circ}F$ ($-20^{\circ}C$ to $+60^{\circ}C$) Storage Range: -22°F to 158°F (-30°C to + 70°C)

Power Options

115V +10%, -15% 50Hz to 400Hz at 2VA 230V +10%, -15% 50Hz to 400Hz at 2VA

10 to 28VDC 150 mA (including backlighting) 10 to 15VDC or 20 to 32VDC 150mA (including backlighting)

Weight

2 oz.

FCC Compliance


Complies with the class B Limits of FCC rules and regulations, part 15, sub part J for conducted and radiated emissions.

Specifications continued on back page.

¹ except isolated DC powered which is ≥ 80 db 50 Hz-60Hz

² except thermocouple inputs which are .1°/ degree zero tempco for selectable process ranges is only ±.2 count/°C

2000 & 2100 Series Connection Drawings



2000 Series Scaling Chart

Model 2100, of the 2000 Series, provide the unique ability to switch-select a range and then scale and offset that range. Input will be displayed in engineering units. For example, by changing switch positions and recalibrating, a 2133-3419-04 may be set-up for any of the following displays:

- 4 to 20mA input display -148°F to 932°F (-100°C to +500°C) temperature
- 1 to 5V input displaying 60kPa to 300kPa differential pressure
- 0 to 10V input displaying +700°F to +950°F (+682°C to +932°C) temperature
- 0 to 50mV input displaying 0 to 300 amperes

Scaling Capability

Zero Range Adjustment 4mA to 20mA, 1V to 5V

- -1000 counts to +1500 counts. Switch selectable in four ranges: a 25-turn potentiometer enables continuous adjustment.
- 0 to 200mV, 0 to 2V, 0 to 10V
- -1500 counts to +1500 counts. Switch selectable in six ranges: a 25-turn potentiometer enables continuous adjustment.

Full Scale Span Adjustment All ranges

 $0\ to\ 2000\ counts.$ Switch selectable in four ranges: a 25-turn potentiometer enables continuous adjustment.

Other ranges and scaling available.



How to Order

	а	b				С	d		e	f
2	0	3	3 ¹	-	3	4	61	-	04	2

Configuration 0 = 1/8 DIN1 = UPM2 = TRMS (Inst) 3 = TRMS (Power)

Display 1 = Non Bklit 3 = Pos Grn Bklit 4 = Neg Grn Bklit 5 = Neg Red Bklit 6 = Pos Red Bklit

DPM Power² 1 = 9 VDC 0 = loop power $2 = \pm 5VDC$ 3 = +5 volts 4 = 115VAC 5 = 230VAC7 = 12 or 24VDC (Iso) 6 = 10 to 28 VDC8 = 12 VDC 9 = 24VDC

00 = 100mVDC (1999 counts) 01 = 200mVDC scaled 0 to 199.9 02 = 2VDC scaled 0 to 1.999 03 = 20VDC04 = 200VDC

05 = 1V to 5 VDC scaled 0 to 100.0 06 = 10VDC scaled 0 to 10.00 07 = 500VDC

10 = 200uADC 11 = 2mADC 12 = 20mADC 13 = 200mADC

Input

18 = 4 to 20mADC Sq Rt³

19 = 4 to 20mADC scaled 0 to 100.03

21 = 200.0mVAC RMS 22 = 2.000VAC RMS 23 = 20.00VAC RMS

24 = 200.0VAC RMS 25 = 500VAC RMS

27 = 500VAC Avg 28 = 80.0 - 130.0VAC Avg

29 = 80 - 260VAC Avg 30 = 250VAC RMS

31 = 2.000mAAC RMS 32 = 20.00mAAC RMS

33 = 200.0mAAC RMS 34 = 2.000AAC RMS

36 = 5.00AAC4 RMS 37 = 50.0AAC4 RMS

38 = 0 - 5AAC4 AVG 39 = 0 - 50AAC4 AVG

60 = 40 to 440Hz

61 = 40.0 to 199.9Hz 70 = 100 Ohms Pt 1° Resolution

71 = 100 Ohms Pt .1° Resolution

80 = Type J Thermocouple 81 = Type K Thermocouple 82 = Type T Thermocouple

Backlit Power² 00 = No Backlight 01 = 5VDC 02 = 12VDC 03 = 24VDC04 = 115VAC05 = 230VAC06 = 10 to 28VDC 07 = 12 or 24VDC

Display5 2 = 15003 = 10001 = 20004 = 600 5 = 5006 = 300 7 = 2008 = 100

2000 and 2100 Series Specifications (continued)							
DC Inputs	Accuracy	Input Resistance	Overload Protection				
200mVDC & 2VDC	$\pm (.1\% + 1 \text{ count}) \text{ typical}$ $\pm (.2\% + 1 \text{ count}) \text{ max}.$	≥ 100 Meg Ohms	200V continuous 300V intermittent				
20VDC & 200VDC	\pm (.1% +1 count) typical \pm (.2% +1 count) max.	1 Meg Ohm	350V continuous 500V intermittent				
DC Current	\pm (.1% +1 count) typical \pm (.2% +1 count) max.	200mV drop full scale	3 times f.s. current				
Universal Selectable Process	±(.1% +2 counts)	4 to 20mA, 10 Ohms ≥ 200mV, ≥ 200K Ohms 2V and up, ≥ 1Meg Ohm	4 to 20 mA, ±100mA Voltage Inputs, 200V continuous 300V intermittent				
AC Inputs	Accuracy	Input Resistance	Overload Protection				
AC Voltage	±(.5% + 1 count)	1 Meg Ohm	350V continuous 500V intermittent				
5A AC Current	±(.5% +1 count)	Current transformer	3 times f.s. current				
50A AC Current	±(.5% +5 counts)	Current transformer	3 times f.s. current				
Frequency Inputs	Accuracy ±.2Hz (40 to 70Hz)	Distortion					
40.0 to 199.9Hz	armonic distortion						
40 to 440Hz	±1Hz	≤ .1 Hz for up to 20% third harmonic distortion					
Temperature Inputs	Accuracy	Input Characteristic	Overload Protection				
Type J thermocouple -10°F to +1200°F (-23°C to +649°C)	±(.1% +1 count) accuracy ±1.3°C (2.8°F) conformity error	45 uV max per 100 Ohms thermocouple lead resistance	200V continuous				
Type K thermocouple -40°F to +1500°F (-40°C to +815°C)	±(.1% +1 count) accuracy ±1.2°C (2.5°F) conformity error	45 uV max per 100 Ohms thermocouple lead resistance	200V continuous				
Type T thermocouple							
-100°F to +600°F (-73°C to +315°C)	±1.5°C (3.5°F) conformity error	45 uV max per 100 Ohms thermocouple lead resistance	200V continuous				
100 Ω Pt. α =.00385 -200°F to +600° F (-129°C to +315°C)	±(.2% + 1 count) max	1mA RTD current	±5V				
100 Ω Pt. α =.00385 -100.0°F to +199.9°F (-73°C to +98°C)	±(.2% + 1 count) max	1mA RTD current	±5V				

¹ Change Order Number to "4" for 200 VDC Input

² Backlit power must be the same as the selected DPM power.

³ Available on Non-Backlit meters only.

⁴ Rated for use with 5A or 50A external current transformer supplied with DPM. See high current connection on inside page.

⁵ For 5A current transformer inputs only.



For over 60 years, Jewell Instruments and our predecessor companies have provided high quality panel meter solutions for a wide range of aerospace, industrial and commercial applications. Jewell and MODUTEC are some of the most trusted brands in the industry. They are known for:

- reliable, high quality, products
- superb applications knowledge
- custom designs for unique requirements
- "extended staff" relationships with customers
- creative engineering expertise

Jewell Instruments

The only panel meter manufacturer that offers a full spectrum of panel meters. Analog, digital. Any size, and shape. Surface mount, window mount, bezel mount. We have decades of broad-based experience resulting in our superior breadth of product — and our ability to meet your custom needs. Jewell Instruments can provide a proven, quick and cost-effective solution to your panel meter needs.

Analog panel meters can be either electrical or electronic. Application areas include:

Electrical

- Field Strength Meters
- Power Generation
- Power Distribution Panel
- Control Panels
- Switchgear Panels
- Power Supplies
- Power Conditioners
- Voltage Regulators
- UPS Systems
- Automatic Transfer Switches
- Generator Paralleling Switchgear

Electronic

- Liquid Level
- Flow
- Pressure Monitors
- Volume Units
- Tension Control
- Laboratory Equipment
 Kilns
- Test Equipment Marine
- Broadcast Equipment
 Chart Recorders
- Stereo Equipment Medical
- Field Strength

Temperature

Battery Level

Speed

Digital panel meter applications include:

Digital

- Telecommunications
- Welders
- Agricultural
- Water Purification
- Desalinization

Digital Panel Meters

	Categories								
	BL Series	1000 Series	BGE Series	PMC Series	2000 Series	2100 Series	DW Series	1800 Series	
Display									
LCD	•	•	•	•	•	•	•	•	
Backlit LCD	•	•	•	•	•	•			
LED						•		•	
Mounting									
Surface	•	•					•		
Window	•		•	•			•		
Bezel	•	•	•		•	•	•	•	
Connections									
Pins	•	•	•						
Solder Pads	•								
Screw Terminal Connector	•			•	•	•		•	
Banana Plugs				•					
Inputs									
DC Volt	•	•	•		•	•	•	•	
DC AMP	•	•		•	•	•	•	•	
AC Volt	•				•	•	•		
AC AMP	•				•	•	•		
Frequency	•				•	•			
RTD	•				•	•		•	
Thermocouple	•				•	•			
DPM Power									
5 Volt DC	•	•	•				•	•	
+/- 5 Volt DC	•	•							
9 Volt DC	•	•	•				•		
Loop Powered	•	•		•	•	•	•		
115 VAC	•				•	•	•		
230 VAC	•				•	•	•		
12 or 24 VDC (Isolated)	•				•	•			
10 to 28 VDC (Isolated)	•	•					•		
10 to 30 VDC (Isolated)	•								
Page Number	15	15	15	16	16	16	17	17	





PMC Series - MODUTEC

The *PMC Series* is designed to meet the unique needs of process instrumentation applications. It is self-powered from a 4-20mA control loop. It includes our standard features, such as selectable decimal points and large digits.



2000 Series — MODUTEC

The *Series 2000* is the ideal industrial application panel meter. This 1/8" DIN meter is splash and hose proof, with a wide temperature range. The polycarbonate case makes it resistant to knocks. With all of these rugged features, the *Series 2000* remains a slim meter, easy to fit in the design of your industrial application.





2100 Series — MODUTEC

The *Series 2100* is the next generation *2000* with all the features of the *2000*, but now with DIP switch selections for decimal points and inputs. We've also added multiple power options.

