



POTTING BOXES

Order data on page 173

OKW
GEHÄUSE
SYSTEME



FOR EASY ENCAPSULATION

Sizes (L x W x H in inches)

Duroplast

0.787 x 0.787 x 0.516 –
3.937 x 3.937 x 1.575

PA 6.6

0.551 x 0.551 x 0.458 –
1.819 x 1.819

ABS

0.484 x 0.484 x 0.602 –
2.657 x 1.409 x 1.823

detailed drawings see our website
www.okwenclosures.com

THE PRODUCT

OKW POTTING BOXES – a comprehensive range of boxes for potting electronic assemblies. With special cost advantages for series-type production.

Potted assemblies are protected from shock as well as temperature, dampness and chemical influences. The versions made of Duroplast are less resistant to impact than the Polyamide 6.6 or ABS models.

YOUR ADVANTAGE

Duroplast

Resistant to deformation and extreme temperatures.



Polyamide 6.6

Good value for money. High-impact.

ABS

Good value for money. Preferably for potting small assemblies.


POTTING BOXES*1

POTTING BOXES	Article	Outside dim. in inches			Version	Part-No.	
		L	W	H		case	lid
Duroplast	Duroplast	0.787	0.787	0.516	I	A 80 20 130	—
		0.984	0.984	0.583	I	A 80 25 150	—
		0.984	0.984	0.984	I	A 80 25 251	—
		1.189	0.793	0.594	I	A 80 30 150	A 81 30 200
		1.594	0.543	0.634	I	A 80 40 160	A 81 40 130
		1.583	13.55	0.984	I	A 80 40 250	A 81 40 130
		1.575	1.575	0.504	I	A 80 40 130	A 81 40 400
		1.583	1.583	0.787	I	A 80 40 200	A 81 40 400
		1.776	1.185	0.591	I	A 80 45 150	A 81 45 300
		1.776	1.181	0.980	I	A 80 45 250	A 81 45 300
		1.965	0.516	0.591	I	A 80 50 150	—
		1.974	1.974	0.594	I	A 80 50 160	A 81 50 500
		1.972	1.972	0.988	I	A 80 50 250	A 81 50 500
		1.996	1.996	1.957	I	A 80 50 500	A 81 50 500
		2.756	1.984	0.787	I	A 80 70 200	A 81 70 500
		2.780	1.984	1.378	I	A 80 70 350	A 81 70 500
		3.555	2.374	0.787	I	A 80 90 200	—
		3.941	1.976	0.976	I	A 80 10 250	—
		3.937	3.937	1.575	I	A 80 10 400	—
case							
PA 6.6	PA 6.6	0.551	0.551	0.453	II	A 80 14 118	
		0.685	0.591	0.413	III	A 80 17 108	
		0.685	0.591	0.602	II	A 80 17 158	
		0.732	0.732	0.539	III	A 80 18 138	
		0.819	0.819	0.496	III	A 80 20 128	
		0.839	0.524	0.697	III	A 80 21 178	
		0.882	0.882	0.551	III	A 80 22 148	
		1.039	1.039	1.386	III	A 80 26 358	
		1.142	1.142	0.756	III	A 80 29 198	
		1.193	1.193	1.980	III	A 80 30 508	
		1.276	1.276	0.787	III	A 80 32 208	
		1.528	1.528	1.047	II	A 80 39 268	
		1.531	1.531	1.528	II	A 80 39 398	
		1.575	0.394	0.795	II	A 80 40 208	
		1.819	1.819	1.606	III	A 80 46 408	
ABS	ABS	0.484	0.484	0.602	III	A 80 12 159	
		0.835	0.835	0.476	III	A 80 21 129	
		0.996	0.996	0.598	III	A 80 25 159	
		1.508	0.803	0.795	III	A 80 38 209	
		1.791	1.201	0.618	III	A 80 45 169	
		2.657	1.409	1.823	III	A 80 67 469	

*1 cases supplied bulk packed

