# International

- Advanced Process Technology
- Dynamic dv/dt Rating
- 175°C Operating Temperature
- Fast Switching
- Fully Avalanche Rated
- Lead-Free

## IRFZ44EPbF

PD - 94822

HEXFET<sup>®</sup> Power MOSFET



#### Description

Fifth Generation HEXFETs from International Rectifier utilize advanced processing techniques to achieve extremely low on-resistance per silicon area. This benefit, combined with the fast switching speed and ruggedized device design that HEXFET Power MOSFETs are well known for, provides the designer with an extremely efficient and reliable device for use in a wide variety of applications.

The TO-220 package is universally preferred for all commercial-industrial applications at power dissipation levels to approximately 50 watts. The low thermal resistance and low package cost of the TO-220 contribute to its wide acceptance throughout the industry.



#### **Absolute Maximum Ratings**

	Parameter	Max.	Units
I <sub>D</sub> @ T <sub>C</sub> = 25°C	Continuous Drain Current, V <sub>GS</sub> @ 10V	48	
I <sub>D</sub> @ T <sub>C</sub> = 100°C	Continuous Drain Current, V <sub>GS</sub> @ 10V	34	A
I <sub>DM</sub>	Pulsed Drain Current ①⑤	192	
$P_{D} @ T_{C} = 25^{\circ}C$	Power Dissipation	110	W
	Linear Derating Factor	0.71	W/°C
V <sub>GS</sub>	Gate-to-Source Voltage	± 20	V
E <sub>AS</sub>	Single Pulse Avalanche Energy <sup>®</sup>	220	mJ
I <sub>AR</sub>	Avalanche Current①	29	A
E <sub>AR</sub>	Repetitive Avalanche Energy <sup>①</sup>	11	mJ
dv/dt	Peak Diode Recovery dv/dt ③	5.0	V/ns
TJ	Operating Junction and	-55 to + 175	
T <sub>STG</sub>	Storage Temperature Range		°C
	Soldering Temperature, for 10 seconds	300 (1.6mm from case )	
	Mounting torque, 6-32 or M3 srew	10 lbf•in (1.1N•m)	

#### **Thermal Resistance**

	Parameter	Тур.	Max.	Units
R <sub>0JC</sub>	Junction-to-Case		1.4	
R <sub>0CS</sub>	Case-to-Sink, Flat, Greased Surface	0.50		°C/W
R <sub>0JA</sub>	Junction-to-Ambient		62	

1

### IRFZ44EPbF

# International

#### Electrical Characteristics @ $T_J = 25^{\circ}C$ (unless otherwise specified)

	Parameter	Min.	Тур.	Max.	Units	Conditions
V <sub>(BR)DSS</sub>	Drain-to-Source Breakdown Voltage	60			V	$V_{GS} = 0V, I_D = 250\mu A$
$\Delta V_{(BR)DSS}/\Delta T_J$	Breakdown Voltage Temp. Coefficient		0.063		V/°C	Reference to 25°C, I <sub>D</sub> = 1mA
R <sub>DS(on)</sub>	Static Drain-to-Source On-Resistance			0.023	Ω	$V_{GS} = 10V, I_D = 29A$ ④
V <sub>GS(th)</sub>	Gate Threshold Voltage	2.0		4.0	V	$V_{DS} = V_{GS}, I_D = 250 \mu A$
9 <sub>fs</sub>	Forward Transconductance	15			S	V <sub>DS</sub> = 30V, I <sub>D</sub> = 29A <sup>®</sup>
I <sub>DSS</sub>	Drain-to-Source Leakage Current			25	Δ	$V_{\text{DS}} = 60 \text{V}, \text{ V}_{\text{GS}} = 0 \text{V}$
				250	μ <del>Λ</del>	$V_{DS} = 48V, V_{GS} = 0V, T_{J} = 150^{\circ}C$
1	Gate-to-Source Forward Leakage			100		$V_{GS} = 20V$
GSS	Gate-to-Source Reverse Leakage			-100		$V_{GS} = -20V$
Qg	Total Gate Charge			60		I <sub>D</sub> = 29A
Q <sub>gs</sub>	Gate-to-Source Charge			13	nC	$V_{DS} = 48V$
Q <sub>gd</sub>	Gate-to-Drain ("Miller") Charge			23		$V_{GS}$ = 10V, See Fig. 6 and 13 $\circledast$
t <sub>d(on)</sub>	Turn-On Delay Time		12			V <sub>DD</sub> = 30V
tr	Rise Time		60			I <sub>D</sub> = 29A
t <sub>d(off)</sub>	Turn-Off Delay Time		70		115	R <sub>G</sub> = 15Ω
t <sub>f</sub>	Fall Time		70			R <sub>D</sub> = 1.1Ω, See Fig. 10 ⊕
LD	Internal Drain Inductance		4.5		- mLl	Between lead,
						6mm (0.25in.)
L <sub>S</sub>	Internal Source Inductance		7.5	—	_	from package
						and center of die contact
Ciss	Input Capacitance		1360			V <sub>GS</sub> = 0V
C <sub>oss</sub>	Output Capacitance		420			$V_{DS} = 25V$
C <sub>rss</sub>	Reverse Transfer Capacitance		160		pF	f = 1.0MHz, See Fig. 5

#### **Source-Drain Ratings and Characteristics**

	Parameter	Min.	Тур.	Max.	Units	Conditions
Is	Continuous Source Current			18		MOSFET symbol
	(Body Diode)			40	Δ	showing the
ISM	Pulsed Source Current			192	1 ``	integral reverse
	(Body Diode)①					p-n junction diode.
V <sub>SD</sub>	Diode Forward Voltage			1.3	V	$T_J=25^\circ C,\ I_S=29A,\ V_{GS}=0V\ \textcircled{0}$
t <sub>rr</sub>	Reverse Recovery Time		69	104	ns	$T_J = 25^{\circ}C, I_F = 29A$
Q <sub>rr</sub>	Reverse Recovery Charge		177	266	nC	di/dt = 100A/µs ④
t <sub>on</sub>	Forward Turn-On Time	Intrinsic turn-on time is negligible (turn-on is dominated by $L_{S}+L_{D}$ )				

Notes:

- ① Repetitive rating; pulse width limited by max. junction temperature. ( See fig. 11 )
- 3 I\_{SD}  $\leq$  29A, di/dt  $\leq$  320A/µs, V\_{DD}  $\leq$  V\_{(BR)DSS}, T\_J  $\leq$  175°C
- ④ Pulse width  $\leq$  300µs; duty cycle  $\leq$  2%.

### **IRFZ44EPbF**

#### International **TOR** Rectifier

#### **TO-220AB** Package Outline

Dimensions are shown in millimeters (inches)





1 DIMENSIONING & TOLERANCING PER ANSI Y14.5M, 1982. 2 CONTROLLING DIMENSION : INCH

3 OUTLINE CONFORMS TO JEDEC OUTLINE TO-220AB. 4 HEATSINK & LEAD MEASUREMENTS DO NOT INCLUDE BURRS.

#### **TO-220AB Part Marking Information**



Data and specifications subject to change without notice.

International **ICR** Rectifier