International Rectifier


Advanced Process Technology

- Ultra Low On-Resistance
- Dynamic dv/dt Rating
- 175°C Operating Temperature
- Fast Switching
- Fully Avalanche Rated
- Optimized for SMPS Applications
- Lead-Free

Description

Advanced HEXFET® Power MOSFETs from International Rectifier utilize advanced processing techniques to achieve extremely low on-resistance per silicon area. This benefit, combined with the fast switching speed and ruggedized device design that HEXFET power MOSFETs are well known for, provides the designer with an extremely efficient and reliable device for use in a wide variety of applications.

The TO-220 package is universally preferred for all commercial-industrial applications at power dissipation levels to approximately 50 watts. The low thermal resistance and low package cost of the TO-220 contribute to its wide acceptance throughout the industry.



$V_{DSS} = 60V$

IRFZ44VPbF

HEXFET® Power MOSFET

 $R_{DS(on)} = 16.5 m\Omega$

 $I_{D} = 55A$



Absolute Maximum Ratings

	Parameter	Max.	Units	
I _D @ T _C = 25°C	Continuous Drain Current, V _{GS} @ 10V	55		
I _D @ T _C = 100°C	Continuous Drain Current, V _{GS} @ 10V	39	A	
I _{DM}	Pulsed Drain Current ①	220		
P _D @T _C = 25°C	Power Dissipation	115	W	
	Linear Derating Factor	0.77	W/°C	
V _{GS}	Gate-to-Source Voltage	± 20	V	
E _{AS}	Single Pulse Avalanche Energy ^②	115	mJ	
I _{AR}	Avalanche Current①	55	А	
E _{AR}	Repetitive Avalanche Energy①	11	mJ	
dv/dt	Peak Diode Recovery dv/dt ③	4.5	V/ns	
TJ	Operating Junction and	-55 to + 175		
T _{STG}	Storage Temperature Range		°C	
	Soldering Temperature, for 10 seconds	300 (1.6mm from case)		
	Mounting torque, 6-32 or M3 srew	10 lbf•in (1.1N•m)		

Thermal Resistance

	Parameter	Тур.	Max.	Units
R _θ JC	Junction-to-Case		1.3	
R _{θCS}	Case-to-Sink, Flat, Greased Surface	0.50		°C/W
$R_{\theta JA}$	Junction-to-Ambient		62	

IRFZ44VPbF



Electrical Characteristics @ T_J = 25°C (unless otherwise specified)

	Parameter	Min.	Тур.	Max.	Units	Conditions
V _{(BR)DSS}	Drain-to-Source Breakdown Voltage	60			V	$V_{GS} = 0V, I_D = 250\mu A$
$\Delta V_{(BR)DSS}/\Delta T_J$	Breakdown Voltage Temp. Coefficient		0.062		V/°C	Reference to 25°C, I _D = 1mA
R _{DS(on)}	Static Drain-to-Source On-Resistance			16.5	mΩ	V _{GS} = 10V, I _D = 31A ④
V _{GS(th)}	Gate Threshold Voltage	2.0		4.0	V	$V_{DS} = V_{GS}$, $I_D = 250\mu A$
9fs	Forward Transconductance	24			S	V _{DS} = 25V, I _D = 31A⊕
	Drain-to-Source Leakage Current			25	uА	$V_{DS} = 60V, V_{GS} = 0V$
I _{DSS}	Diali-10-30dice Leakage Odiferit			250	μΑ	V _{DS} = 48V, V _{GS} = 0V, T _J = 150°C
1	Gate-to-Source Forward Leakage			100	nA	V _{GS} = 20V
I _{GSS}	Gate-to-Source Reverse Leakage			-100	na ·	V _{GS} = -20V
Qg	Total Gate Charge			67		I _D = 51A
Q_{gs}	Gate-to-Source Charge			18	nC	$V_{DS} = 48V$
Q _{gd}	Gate-to-Drain ("Miller") Charge			25		V _{GS} = 10V, See Fig. 6 and 13 ④
t _{d(on)}	Turn-On Delay Time		13			$V_{DD} = 30V$
t _r	Rise Time		97			$I_D = 51A$
t _{d(off)}	Turn-Off Delay Time		40		ns	$R_G = 9.1\Omega$
t _f	Fall Time		57			$R_D = 0.6\Omega$, See Fig. 10 \oplus
L _D	Internal Drain Inductance		4.5			Between lead, 6mm (0.25in.)
L _S	Internal Source Inductance		7.5		hH	from package and center of die contact
C _{iss}	Input Capacitance		1812			V _{GS} = 0V
C _{oss}	Output Capacitance		393			$V_{DS} = 25V$
C _{rss}	Reverse Transfer Capacitance		103		pF	f = 1.0MHz, See Fig. 5

Source-Drain Ratings and Characteristics

	Parameter	Min.	Тур.	Max.	Units	Conditions
Is	Continuous Source Current			55		MOSFET symbol
	(Body Diode)		- 35	' A	showing the	
I _{SM}	Pulsed Source Current			000		integral reverse
	(Body Diode)①		220		p-n junction diode.	
V _{SD}	Diode Forward Voltage			2.5	V	$T_J = 25^{\circ}C$, $I_S = 51A$, $V_{GS} = 0V$ ④
t _{rr}	Reverse Recovery Time		70	105	ns	$T_J = 25^{\circ}C, I_F = 51A$
Q _{rr}	Reverse Recovery Charge		146	219	nC	di/dt = 100A/µs ④
t _{on}	Forward Turn-On Time	Intrinsic turn-on time is negligible (turn-on is dominated by L _S +L _D)				

Notes:


- ① Repetitive rating; pulse width limited by max. junction temperature. (See fig. 11)
- $\label{eq:loss} \begin{array}{l} \text{ } \exists \ \ I_{SD} \leq 51\text{A}, \ di/dt \leq 227\text{A}/\mu\text{s}, \ V_{DD} \leq V_{(BR)DSS}, \\ T_{J} \leq 175^{\circ}\text{C} \end{array}$
- 4 Pulse width $\leq 300 \mu s$; duty cycle $\leq 2\%$.

2 www.irf.com


IRFZ44VPbF

TO-220AB Package Outline

Dimensions are shown in millimeters (inches)



TO-220AB Part Marking Information



Data and specifications subject to change without notice. This product has been designed and qualified for the Automotive [Q101] market.

