




A Unit of Teledyne Electronics and Communications

HIGH REPEATABILITY BROADBAND TO-5 RELAYS DPDT

SERIES DESIGNATION	RELAY TYPE		
RF300	Repeatable RF relay		
RF303	Sensitive, repeatable RF relay		

INTERNAL CONSTRUCTION



PERFORMANCE FEATURES

The ultraminiature RF300 and RF303 relays are designed to provide improved RF signal repeatability over the frequency range. These relays are highly suitable for use in attenuator and other RF circuits, the RF 300 and RF303 feature:

- · High repeatability.
- Broader bandwidth.
- Metal enclosure for EMI shielding.
- Ground pin option to improve case grounding.
- High isolation between control and signal paths.
- Highly resistant to ESD.

CONSTRUCTION FEATURES

The following unique construction features and manufacturing techniques provide excellent resistance to environmental extremes and overall high reliability.

- Uni-frame motor design provides high magnetic efficiency and mechanical rigidity.
- Minimum mass components and welded construction provide maximum resistance to shock and vibration.
- Advanced cleaning techniques provide maximum assurance of internal cleanliness.
- · Gold-plated precious metal alloy contacts ensure reliable switching.
- · Hermetically sealed.
- Solderable leads.

ENVIRONMENTAL AND PHYSICAL SPECIFICATIONS						
Temperature	Storage	–65°C to +125°C				
(Ambient)	Operating	–55°C to +85°C				
Vibration (General Note 1	1)	10 g's to 500 Hz				
Shock (General Note 1	1)	30 g's, 6 msec, half-sine				
Enclosure		Hermetically sealed				
Weight	RF300	0.09 oz. (2.55g) ma				
weight	RF303	0.16 oz. (4.5g) max.				

SERIES

RF300


RF303

SERIES RF300 AND RF303 GENERAL ELECTRICAL SPECIFICATIONS (@25°C)

Contact arrangement		2 Form C (DPDT)		
Rated duty		Continuous		
Contact resistance		0.15 ohm max. initial (measured 1/8" from the header)		
Contact load rating		Resistive: 1Amp/28Vdc Low level: 10 to 50 μA, 10 to 50 mV		
Contact life rating		10,000,000 cycles typical at low level		
Coil operating power		RF300: 450 mW typical @ nominal rated voltage RF303: 200 mW typical @ nominal rated voltage		
Operate time	RF300	4.0 ms. max.		
Operate time	RF303	6.0 ms. max.		
Release time	RF300	3.0 ms. max.		
Release time	RF303	3.0 ms. max.		
Intercontact capacitance		0.4 pF typical		
Insulation resistance		1,000 M Ω min. (between mutually isolated terminals)		
Dielectric strength		350 VRMS / 60 Hz @ atmospheric pressure		

DETAILED ELECTRICAL SPECIFICATIONS (@25°C)

BASE PART NUMBERS	RF300-5 RF303-5	RF300-12 RF303-12	
Coil voltage, nominal, VDC		5.0	12.0
Coil resistance, ohms ± 20%	RF300	50	390
	RF303	100	850
Pick-up voltage max, VDC	3.6	9.0	



GENERAL NOTES

TO THE PART NUMBER FOR POSITION 10.

EXAMPLE: RF300Y-COIL VOLTAGE

1. Relays will exhibit no contact chatter in excess of 10 µsec or transfer in excess of 1 µsec.