



Lacing Tape and Twine
MILITARY GRADE NYLON LACING CORD
 *MIL-T-713EB, TYPE P

DESCRIPTION

Construction: Twisted nylon cord manufactured from high tenacity continuous filament yarn.

CHARACTERISTICS

Temperature Range: -55 to +121C.

FEATURES & APPLICATIONS

For use in bundling military or commercial wire harnesses. *Nylon has excellent tensile strength and resists acids, abrasion, flame and fungus.

APPROVALS

MIL-T-713EB, Type P.

Part Number	Mil Spec Class	Strength (Min.)	Color	Mil Spec Finish	Yards per Pound	Standard Spool
807010W	1	70 lbs.	Natural	A	650	1 lb.
807010B	1	70 lbs.	Black	A	650	1 lb.
807013W	1	70 lbs.	Natural	B	500	1 lb.
807013B	1	70 lbs.	Black	B	500	1 lb.
804812W	2	48 lbs.	Natural	A	950	1 lb.
Part Number	Mil Spec Class	Strength (Min.)	Color	Mil Spec Finish	Yards per Pound	Standard Spool
804812B	2	48 lbs.	Black	A	950	1 lb.
804814W	2	48 lbs.	Natural	B	750	1 lb.
804814B	2	48 lbs.	Black	B	750	1 lb.
803212W	3	32 lbs.	Natural	A	1400	1 lb.
803212B	3	32 lbs.	Black	A	1400	1 lb.
Part Number	Mil Spec Class	Strength (Min.)	Color	Mil Spec Finish	Yards per Pound	Standard Spool
803215W	3	32 lbs.	Natural	B	1100	1 lb.
803215B	3	32 lbs.	Black	B	1100	1 lb.

Standard Color: Natural with a tracer. Finishes and Coatings: A-Natural Finish* B-Wax *No additional coating.