PV180KB Universal 15.4 Watt (Compliant)

SSL POWER ELECTRONICS

PoE/SMPS

3 Year Warranty

- Power over Ethernet (PoE)
- PoE Injector and Power Supply in One Unit
- Universal Input 100 to 250VAC
- Desktop Style-Single Output
- Ideal for Midspan Applications
- Meets IEEE802.3af Requirements
- Regulated Output with Low Ripple
- Meets Safety Agency Requirements
- Complies with EMI/RFI Regulations
- CE Compliant
- Impact Resistant Polycarbonate Enclosure
- Private Label Marking Available
- Modified and Custom Designs Also Available





International Safety Standard Approvals



Specifications

Output Specifications		
Voltage		+48VDC Typical, 44V to 57V
Load Regulation		+/-4%, 44V to 57V
Ripple and Noise	f < 500kHz 500Hz-150kHz 150kHz-500kHz 500kHz-1MHz	500mVp-p 150mVp-p 150mVp-p 100mVp-p
Transient Response		0.5ms for 50% Load change Typical
Pin Assignment		(see page 2)

Input Specifications	S	
Voltage		100-250VAC -10%, +6%
Line Frequency		47-63Hz
Input Current	90VAC Input	0.5A max.
Protection		Internal Primary Current Fuse, Inrush Limiting

LED Indicator		
Power Mode LED (Two colors)	Amber -	Power ON / Detection Mode
	Green -	Injecting Full Power / Power Up Mode

General Specifications	
Topology	Switching-Fixed Frequency Flyback
Dielectric Withstand	3,000VAC or 4,250VDC Primary-Secondary
Output Current	350mAdc min.
Inrush Current	450mAdc max.
Overload Current Detection	(15.4W/Vport)min. / 400mA max.
Overload Time Limit	50-75ms
Short Circuit Protection	400-450mA max.
Continuous Output Power	15.4W min. Average over 1 second.
Approvals and Safety Standards	UL60950-1, IEC/EN60950-1 EMC: EN55022 / 55024 / 61000
Weight	5.95 ounces, 170 Grams
Leakage Current	Less than 0.75mA at 265VAC 50Hz
Spacing	6.4mm Primary-Secondary
Case and Dimension	Desktop Style 3.98L x 2.40W x 1.35H (in) 101.0L x 61.5W x 34.2H (mm)
Case Material	Black 94V0 Polycarbonate
Cord and Connectors	Dual RJ45 Jacks built into the enclosure.

PV180KB Universal 15.4 Watt (Compliant)

PoE / SMPS

For the most current data and application support visit www.slpower.com

	Output		Output Currents		Ripple
Ault Part Number	Voltage	Min	Max	Watts	Vp-p max.
PW180KB4800_01	48 V	0.00 A	0.35 A	15.4 W	480 mV

Ault Part Nui	ult Part Number Key					
PW180	К	В	48	00	=	01
Product Family Name	Manufacturing Location	Design Revision Changes	Voltage DC	Connector Number	Input Configuration/ Model Type	Standard (no modifications or special packaging)





