AULT SPECIFICATION **PW300 Universal Series**

INPUT

100-250VAC -10%, +6% Voltage **Line Frequency**

47-63 Hz

Current 1.3A Max. at 100VAC Input

Internal primary current fuse, Inrush limiting **Protection**

Overcurrent and short circuit protected

In Case IEC320 with Ground Configuration

OUTPUT

Model	Voltage	Min. Current	Max. Current	Max.Watts	Max. Power
PW300KA0012F01	+5VDC	0 A	5.0A	25.0	50 Watts
	+12VDC	0 A	4.0A	24.0	
	-12VDC	0A	0.5A	6.0	

+5VDC: +1% Combined +5,+12 Output of >0.6A Combined Line and Load +12VDC: +5% -5% Combined +5, +12 Output of >0.6A **Voltage Regulation Excluding Cord** -12VDC: +6% Combined +5, +12 Output of >0.6A

Ripple +5: 50mV p-p Max combined +5, +12 Output >0.6A

> +12: 100mV p-p Max combined +5, +12 Output >0.6A -12: 100mV p-p Max combined +5, +12 Output >0.6A

0.5mSec for 50% load change typical **Transient Response** 20mSec @ 120VAC; 120mSec @ 240VAC **Holdup Time Protection** Foldback overcurrent protection on all outputs

Short circuit protection on all outputs

OVP 6.8V Max on +5VDC

3 ft., 5 Conductor, 18 AWG, Ault #12 Connector **Cord and Connectors**

Other Connectors are also available

ELECTRICAL

Switching - Fixed Frequency Flyback **Topology Dielectric Withstand** 3000VAC, 4250VDC Primary - Secondary 1500VAC, 2150VDC Primary - Ground

> 500VDC, Secondary - Ground 8mm Primary - Secondary

Safety Spacings **Leakage Current** Less than 0.75mA at 265VAC 50Hz

Efficiency Up to 75%

EMI Complies with EMC Directives

CE Compliant CE

SAFETY APPROVALS UL1950, CSA950, TUV/IEC950

ENVIRONMENTAL

Operating Temperature 0° - 50° C with no derating

Storage Temperature -30° C to +85° C

Relative Humidity 5% to 95% Non-condensing

0 - 10,000 Feet Altitude

Cooling Convectional non-vented case

MECHANICAL

LP8 - Desktop **Case and Dimensions**

5.87 L x 3.34 W x 2.0 H (in) 149 L x 86 W x 51 H (mm)

Black 94V0 Polycarbonate **Case Material**

16 Ounces, 454 grams (excluding cords) Weight

WARRANTY 3 Years