

Vishay Siliconix


# N-Channel 20-V (D-S) MOSFET

PRODUCT SUMMARY					
V <sub>DS</sub> (V)	<b>R<sub>DS(on)</sub> (</b> Ω)	I <sub>D</sub> (A)	Q <sub>g</sub> (Typ.)		
	0.031 at V <sub>GS</sub> = 4.5 V	5.0			
20	0.037 at V <sub>GS</sub> = 2.5 V	4.6	7.5		
	0.047 at V <sub>GS</sub> = 1.8 V	4.1			

## **FEATURES**

- Halogen-free Option Available
  TrenchFET<sup>®</sup> Power MOSFET
- 100 % R<sub>g</sub> Tested





\* Marking Code

Ordering Information: Si2312BDS-T1-E3 (Lead (Pb)-free) Si2312BDS-T1-GE3 (Lead (Pb)-free and Halogen-free)

ABSOLUTE MAXIMUM RATINGS	T <sub>A</sub> = 25 °C, unle	ss otherwise r	noted		
Parameter		Symbol	5 s	Steady State	Unit
Drain-Source Voltage		V <sub>DS</sub>	20		V
Gate-Source Voltage		V <sub>GS</sub>	± 8		
	T <sub>A</sub> = 25 °C	- I <sub>D</sub>	5.0	3.9	
Continuous Drain Current $(T_J = 150 \ ^{\circ}C)^a$	T <sub>A</sub> = 70 °C		4.0	3.1	
Pulsed Drain Current <sup>b</sup>		I <sub>DM</sub>	15		A
Avalanche Current <sup>b</sup>	L = 0.1 mH	1 mll	13		
Single Avalanche Energy		E <sub>AS</sub>	8.	45	mJ
Continuous Source Current (Diode Conduction) <sup>a</sup>	1	۱ <sub>S</sub>	1.0	0.63	А
	T <sub>A</sub> = 25 °C	P <sub>D</sub>	P. 1.25	0.75	W
Power Dissipation <sup>a</sup>	T <sub>A</sub> = 70 °C		0.80	0.48	
Operating Junction and Storage Temperature Range		T <sub>J</sub> , T <sub>stg</sub>	- 55 to 150		°C

THERMAL RESISTANCE RATINGS					
Parameter		Symbol	Typical	Maximum	Unit
	t ≤ 5 s	R <sub>thJA</sub>	80	100	
Maximum Junction-to-Ambient <sup>a</sup>	Steady State		120	166	°C/W
Maximum Junction-to-Foot	Steady State	R <sub>thJF</sub>	50	60	

Notes:

a. Surface Mounted on 1" x 1" FR4 board.

b. Pulse width limited by maximum junction temperature.

## Vishay Siliconix



	Symbol		Limits				
Parameter		Test Conditions	Min.	Тур.	Max.	Unit	
Static							
Drain-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS}$ = 0 V, I <sub>D</sub> = 250 µA	20	)		v	
Gate-Threshold Voltage	V <sub>GS(th)</sub>	$V_{DS} = V_{GS}, I_D = 250 \ \mu A$	0.45		0.85	v	
Gate-Body Leakage	I <sub>GSS</sub>	$V_{DS} = 0 V$ , $V_{GS} = \pm 8 V$			± 100	nA	
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$V_{DS} = 20 \text{ V}, V_{GS} = 0 \text{ V}$			1	μΑ	
		$V_{DS}$ = 20 V, $V_{GS}$ = 0 V, $T_{J}$ = 70 °C			75		
On-State Drain Current <sup>a</sup>	I <sub>D(on)</sub>	$V_{DS} \ge 10$ V, $V_{GS} = 4.5$ V	15			А	
		$V_{GS} = 4.5 \text{ V}, I_{D} = 5.0 \text{ A}$		0.025	0.031		
Drain-Source On-Resistance <sup>a</sup>	R <sub>DS(on)</sub>	$V_{GS} = 2.5 \text{ V}, I_D = 4.6 \text{ A}$		0.030	0.037	Ω	
		V <sub>GS</sub> = 1.8 V, I <sub>D</sub> = 4.1 A		0.036	0.047		
Forward Transconductance <sup>a</sup>	9 <sub>fs</sub>	$V_{DS} = 15 \text{ V}, \text{ I}_{D} = 5.0 \text{ A}$		30		S	
Diode Forward Voltage	V <sub>SD</sub>	I <sub>S</sub> = 1.0 A, V <sub>GS</sub> = 0 V		0.8	1.2	V	
Dynamic <sup>b</sup>	<u> </u>				<u> </u>		
Total Gate Charge	Qg			7.5	12	nC	
Gate-Source Charge	Q <sub>gs</sub>	$V_{DS} = 10 \text{ V}, \text{ V}_{GS} = 4.5 \text{ V}, \text{ I}_{D} = 5.0 \text{ A}$		1.4			
Gate-Drain Charge	Q <sub>gd</sub>			1.2			
Gate Resistance	R <sub>g</sub>	f = 1.0 MHz	1.1	2.2	3.3	Ω	
Switching							
Turn-On Delay Time	t <sub>d(on)</sub>			9	15		
Rise Time	t <sub>r</sub>	$V_{DD}$ = 10 V, $R_L$ = 10 $\Omega$		30	45	]	
Turn-Off Delay Time	t <sub>d(off)</sub>	$t_{d(off)}$ I <sub>D</sub> $\cong$ 1.0 A, V <sub>GEN</sub> = 4.5 V, R <sub>g</sub> = 6 $\Omega$		35	55	ns	
Fall Time	t <sub>f</sub>			10	15		
Source-Drain Reverse Recovery Time	t <sub>rr</sub>			13	25		
Body Diode Reverse Recovery Charge	Q <sub>rr</sub>	I <sub>F</sub> = 1.0 A, di/dt = 100 A/μs		4.5	7	nC	


Notes:


a. Pulse test: Pulse width  $\leq$  300 µs, duty cycle  $\leq$  2 %.


b. Guaranteed by design, not subject to production testing.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

### TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted








**Si2312BDS** 

# Si2312BDS

## **Vishay Siliconix**



## TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted



Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see http://www.vishay.com/ppg?73235.



Vishay

# Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.