

## 3-phase filters **FN 3025 / FN 3026**

# Advanced EMC/RFI filter concept with minimum leakage current





- Compact state-of-the-art filter concept
- Light weight plastic enclosure design
- Minimized filter leakage current
- Hinged safety covers
- Revolutionary embedded filter terminals
- Chassis or DIN-rail mounting option
- Selectable performance level
- Environmental friendly design without potting compound

#### **Approvals**










#### **Technical specifications**

Maximum continuous operating voltage:	3x 520/300VAC		
Operating frequency:	dc to 60Hz		
Rated currents:	10 to 50A @ 50°C		
High potential test voltage:	P -> E 2000VAC for 2 sec (HL types)		
	P -> E 3000VDC for 2 sec (HP types)		
	P -> P 2250VDC for 2 sec		
Protection category:	IP00 (protection according to VBG 4)		
Overload capability:	4x rated current at switch on,		
	1.5x rated current for 1 minute, once per hour		
Temperature range (operation and storage):	-25°C to +100°C (25/100/21)		
Flammability corresponding to:	UL 94V-2 or better		
Design corresponding to:	UL 1283, CSA 22.2 No. 8 1986, IEC/EN 60939		
MTBF @ 50°C/400V (Mil-HB-217F):	>200,000 hours		

#### Typical electrical schematic



#### Features and benefits

- FN 3025 filters are designed for traditional chassis mounting.
- For extra fast installation, FN 3026 filters can comfortably be snapped-in on TS 35 DIN-rails.
- Two different performance levels are offered (L types, P types). The suitable filter can be selected by choosing the required performance level, the admissible leakage current and the preferred installation style.
- A plastic housing and a metal ground plate are cleverly combined to get the lowest possible product weight without compromizing EMC behavior.

- The embedded jump-terminal system from Schaffner guarantees user-friendly handling as well as fast and reliable electrical connection.
- Captive hinged protective covers contribute to overall safety by offering protection against unintended contact with life conductors. They are included in the standard delivery package without causing extra
- Very low leakage current values make these filter ranges ideally suitable for use in Japanese electricity networks as well as in applications which set value on safety and reliability.

#### Typical applications

- Applications with the requirement for extremely compact filter solutions
- Applications with tough leakage current requirements or sensitive earth leakage detectors
- Applications with insufficient internal filtering or moderate interference levels
- Automation equipment
- Motor drives and servo drives with short motor cables
- Applications including stepping motors
- Semiconductor manufacturing equipment
- Electrical cabinets
- Three-phase power supplies
- Medical equipment (not patient-coupled)


#### Filter selection table


Filter	Rated current @ 50°C (40°C)	Typical drive power rating*	Leakage current** @ 480VAC/50Hz	Power loss @ 25°C/50Hz	Input/Output connections	Weight
	[A]	[kW]	[mA]	[w]		[kg]
FN 3025HL-10-71	10 (10.7)	5.5	0.4	4.8	-71	0.52
FN 3025HL-20-71	20 (21.4)	11	0.4	6.2	-71	0.52
FN 3025HL-30-71	30 (32.1)	18.5	0.4	7.0	-71	0.54
FN 3025HL-50-72	50 (53.5)	30	0.4	10.5	-72	0.93
FN 3025HP-10-71	10 (10.7)	5.5	2.5	4.8	-71	0.52
FN 3025HP-20-71	20 (21.4)	11	2.5	6.2	-71	0.52
FN 3025HP-30-71	30 (32.1)	18.5	2.5	7.0	-71	0.54
FN 3025HP-50-72	50 (53.5)	30	2.5	10.5	-72	0.93
FN 3026HL-10-71	10 (10.7)	5.5	0.4	4.8	-71	0.56
FN 3026HL-20-71	20 (21.4)	11	0.4	6.2	-71	0.56
FN 3026HL-30-71	30 (32.1)	18.5	0.4	7.0	-71	0.58
FN 3026HL-50-72	50 (53.5)	30	0.4	10.5	-72	0.98
FN 3026HP-10-71	10 (10.7)	5.5	2.5	4.8	-71	0.56
FN 3026HP-20-71	20 (21.4)	11	2.5	6.2	-71	0.56
FN 3026HP-30-71	30 (32.1)	18.5	2.5	7.0	-71	0.58
FN 3026HP-50-72	50 (53.5)	30	2.5	10.5	-72	0.98


- \* Calculated at rated current, 480VAC and cos phi = 0.8. The exact value depends upon the efficiency of the drive, the motor and the entire application.
- \*\* Maximum leakage under normal operating conditions. Note: if two phases are interrupted, worst case leakage could reach up to 10 times higher levels (at 520VAC/60Hz).


#### Typical filter attenuation

Per CISPR 17; A =  $50\Omega/50\Omega$  sym; B =  $50\Omega/50\Omega$  asym; C =  $0.1\Omega/100\Omega$  sym; D =  $100\Omega/0.1\Omega$  sym










### Installation






FN 5025/FN 3026 are delivered with closed plastic covers and unfastened terminals. To install the filter please proceed as follows:


- Mount the filter on a metal surface with four screws or snap it onto a TS 35 DINrail.
- First connect the green/yellow wire to the earth stud of the filter.
- Gently lift the two hinged plastic covers.
- Connect phase wires with cable lugs by pushing down and tightening the screws.
- Please note the torque recommendation on top of the filter.
- Push the covers back into their locked position to finish the filter installation.

## Mechanical data

FN 3025







## **Dimensions**

	FN 3025 10A	20A	30A	50A	FN 3026 10A	20A	30A	50A
A	150	150	150	177	150	150	150	177
В	50	50	50	65	50	50	50	65
С	78	78	78	84	78	78	78	84
E	140	140	140	162				
F	32	32	32	44				
G	4.3 x 5.5	4.3 x 5.5	4.3 x 5.5	5.3 x 6.5				
Н	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
J	M4	M4	M4	M5	M4	M4	M4	M5
Х					9.7	9.7	9.7	9.7

All dimensions in mm; 1 inch = 25.4mm Tolerances according: ISO 2768-m / EN 22768-m

## Filter input/output connector cross sections

	-71 (10A)	-71 (20A)	-71 (30A)	-72 (50A)	
Flex wire	1.3 - 2.5mm <sup>2</sup>	4 - 6mm <sup>2</sup>	8 - 10mm <sup>2</sup>	16 - 20mm²	
AWG type wire	AWG 16 - AWG 13	AWG 12 - AWG 10	AWG 8 - AWG 7	AWG 5 - AWG 4	
Ring/fork lug (W/d)*	max. 11mm (9.5mm)/	max. 11mm (9.5mm)/	max. 11mm (9.5mm)/	max. 16.5mm (15mm)/	
	min. Ø4.3mm**	min. Ø4.3mm**	min. Ø4.3mm**	min. Ø5.3mm**	
Recommended torque	2 1.0 - 1.2Nm	1.0 - 1.2Nm	1.0 - 1.2Nm	1.9 - 2.2Nm	

<sup>\*</sup> Schaffner recommends the use of insulated and UL-recognized ring lugs or fork lugs of the appropriate size.

Please visit www.schaffner.com to find more details on filter connectors.



<sup>\*\*</sup> Specification in () relates to earth connector.