

# CAT 5E CABLE

High Reliability Cat 5e Ethernet Cable & Cordsets



### Applications

- Robotics
- Motion Control
- Railways
- CNC Machines
- Battlefield communication
- Industrial Process Control

### General Construction

A 4 pair, 24 AWG, 100 Ohm SFTP round patch cable, designed to the ISO / IEC 11801 Category 5e requirements (cat 5e on 76m).

The cable contains 4 twisted pairs, cabled, double shielded with kevlar reinforcement strands, jacketed in black UV resistant Polyurethane HFFR.

Designed for fixed or portable applications in harsh environments.

### HFFR: Halogen Free Flame Retardant

Jacket Compound Specification:

- Halogen Free Flame Retardant Polyether-based Polyurethane
- Excellent hydrolysis resistance
- High microbial resistance
- Glossy finish
- UV resistant
- High flexibility

Datas for the cable alone only (without RJ45 plug)

### Physical characteristics

|  |   |
|--|---|
| <b>CONDUCTORS</b>                            | 24 AWG (0,25 mm <sup>2</sup> ) tinned copper, 7x0.20 mm                         |
| <b>INSULATION</b>                            | Color coded 568-B, Linear Low Density Polyethylene, Nom. Dia. 0,039" (1mm)      |
| <b>ASSEMBLY</b>                              | Pairs cabled with Kevlar strength members and separation tape wrapped           |
| <b>SHIELDS</b>                               | Inner: Aluminium mylar 100% coverage<br>Outer: Tinned copper braid 80% coverage |
| <b>JACKET</b>                                | Black, special PUR compound   |
| <b>WEIGHT</b>                                | 40 lbs / mft (59 kg/km)   |
| <b>OUTSIDE DIAM.</b>                         | 0.28" (7.1 mm) nom.   |
| <b>MIN BEND RADIUS (During installation)</b> | 67.5mm (9x O. D.)   |
| <b>MIN BEND RADIUS (During operation)</b>    | 37.5mm (5 x O.D.)   |
| <b>MIN FLEXES TO FAILURE</b>                 | Passes IEC 61156-6 requirements   |
| <b>TEMPERATURE</b>                           | Plus 85°C, minus 40°C   |

### Cordsets with a RJ45 plug overmolded on each end

| Length (m/ft)       | Part Number      |
|---------------------|------------------|
| 0,76 m / 2,5 ft     | RJF SFTP 5E 0076 |
| 1,00 m / 3.28 ft    | RJF SFTP 5E 0100 |
| 1,52 m / 5 ft       | RJF SFTP 5E 0152 |
| 3,05 m / 10 ft      | RJF SFTP 5E 0305 |
| 4,57 m / 15 ft      | RJF SFTP 5E 0457 |
| 5,00 m / 16.4 ft    | RJF SFTP 5E 0500 |
| 6,00 m / 19.68 ft   | RJF SFTP 5E 0600 |
| 6,24 m / 20.46 ft   | RJF SFTP 5E 0624 |
| 7,62 m / 25 ft      | RJF SFTP 5E 0762 |
| 8,00 m / 26.24 ft   | RJF SFTP 5E 0800 |
| 10,00 m / 32.78 ft  | RJF SFTP 5E 1000 |
| 14,00 m / 45.92 ft  | RJF SFTP 5E 1400 |
| 15,25 m / 50 ft     | RJF SFTP 5E 1525 |
| 22,87 m / 75 ft     | RJF SFTP 5E 2287 |
| 30,5 m / 100 ft     | RJF SFTP 5E 3050 |
| 45,75 m / 150 ft    | RJF SFTP 5E 4575 |
| 50,00 m / 164 ft    | RJF SFTP 5E 5000 |
| 61,00 m / 200.08 ft | RJF SFTP 5E 6100 |

### Electrical characteristics

|  |                                       |
|--|---------------------------------------|
| <b>DC Resistance</b>                         | 96 Ohms/Km @ 20°C                     |
| <b>Impedance</b>                             | 100 +/- 15 Ohms 1-100 MHz             |
| <b>Attenuation</b>                           |                                       |
| 772 KHz                                      | 2.70 db/100m nom.                     |
| 1 MHz  | 3.15 db/100m nom.                     |
| 4 MHz  | 6.45 db/100m nom.                     |
| 10 MHz                                       | 9.90 db/100m nom.                     |
| 16 MHz                                       | 12.3 db/100m nom.                     |
| 20 MHz                                       | 13.8 db/100m nom.                     |
| 31.25 MHz                                    | 17.7 db/100m nom.                     |
| 62.5 MHz                                     | 25.6 db/100m nom.                     |
| 100 MHz                                      | 33 db/100m nom.                       |
| <b>N.E.X.T. (Near-End Crosstalk Loss)</b>    |                                       |
| 772 KHz                                      | 64 db min.                            |
| 1 MHz  | 62 db min.                            |
| 4 MHz  | 53 db min.                            |
| 10 MHz                                       | 47 db min.                            |
| 16 MHz                                       | 44 db min.                            |
| 20 MHz                                       | 42 db min.                            |
| 31.25 MHz                                    | 40 db min.                            |
| 62.5 MHz                                     | 35 db min.                            |
| 100 MHz                                      | 32 db min.                            |
| <b>Capacitance</b>                           | 46pF/m nom. @ 1KHz                    |
| <b>LCL</b>                                   | 43 dB min. @ 64 KHz                   |
| <b>Capacitance Unbalance</b>                 | 3.4 pF/m max. @ 1KHz (wire to ground) |
| <b>Insulation Resistance</b>                 | 150 M Ohm min.                        |
| <b>Voltage Rating</b>                        | 230 VMS                               |
| <b>Dielectric Strength</b>                   | VAC/1 min - 700 V/Min                 |
| <b>Propagation Delay (100 MHz)</b>           | 5.2 ns/m max. @ 100 MHz               |
| <b>Delay Skew</b>                            | 20 ns/100m max. @ 1-100 MHz           |
| <b>Resistance Unbalance</b>                  | 3% max. @ 20°C                        |
| <b>Structural Return Loss (100 MHz)</b>      | 23db/100m min. @ 1-20 MHz             |
| <b>Spark test (tested during production)</b> | 3 KV                                  |
| <b>Velocity of propagation</b>               | 67% nom.                              |

### Reel of cable (without RJ45 plug on ends)

| Length (m / ft) | Part Number   |
|-----------------|---------------|
| 100 m / ~328 ft | 190-038045-00 |
| 300 m / ~984 ft | 190-038045-01 |