Amphenol Connex

A New Kind of RF Solution

Products | Site Tools | RF Made Simple | Distributors | About Us | News Room | Contact Us | Login 📜 Shopping Cart

Our Products

<u>7/16</u> **BNC**

D-Sub

FME

MCX

MMCX

<u>SMA</u>

<u>SMB</u>

SMC

TNC

Twin BNC

Type F

Type N

<u>UHF</u>

Between-Series Adapters

Shielded Terminations

Strain-Relief Boots

Tools

View All Products

Search Results for: Right Angle Crimp/Solder Plug - Miniature Cable

Please note: Images are for reference only



Part Number: 112588

Family/Series: BNC Coaxial Connectors Product Type: RIGHT ANGLE PLUG CRIMP ATTACHMENTS FOR FLEXIBLE

CABLE

Description: Right Angle Crimp/Solder

Plug - Miniature Cable

Brass Shell

Cable: 180/195/122/B8218/B1865A/

B1855 **


Add to Cart | Product Specs | Customer Drawing

Cable Group: 16 Finish: Nickel Insulation: Delrin Impedance: 75 ohms

Crimp Tool: B

Remark: Cable Center Conductor

Solder to pin directly





Products Site Tools RF Made Simple Distributors

About Us News Room Contact Us Login

Shopping Cart

Our Products

7/16 **BNC**

D-Sub

FME

MCX

MMCX

<u>SMA</u>

<u>SMB</u>

SMC

TNC

Twin BNC

Type F

Type N

UHF

Between-Series Adapters

Shielded Terminations Strain-Relief Boots

Tools

View All Products

BNC connector series

Features & Benefits | Applications | 50 Ω BNC Specs | 75 Ω BNC Specs | Reverse Polarity Specs | Assembly Instructions

Developed in the late 1940's as a miniature version of the Type C connector, BNC stands for Bayonet Neill Concelman and is named after Amphenol engineer Carl Concelman. The BNC product line is a miniature quick connect/disconnect RF connector. It features two bayonet lugs on the female connector; mating is achieved with only a quarter turn of the coupling nut. BNC's are ideally suited for cable termination for miniature to subminiature coaxial cable (RG-58, 59, to RG-179, RG-316, etc.)



Amphenol 50 Ω BNC connectors are miniature, lightweight units designed to operate up to 11 GHz and typically yield low reflection through 4 GHz.

Designed to accommodate a large variety of RG and industry standard cables, BNC connectors are available in crimp/crimp, clamp/solder, SURETWIST®, and field serviceable termination styles. A full line of printed circuit board receptacles, bulkhead receptacles, resistor terminations, and other accessories complement the product offering.

A variety of our 50 Ω BNC connectors are recognized under the Component program of Underwriter's Laboratories, Inc. These connectors are ideal for use with medical equipment and test instrumentation where safety cannot be compromised.

Amphenol also offers a full line of 75 Ω BNC connectors to meet the needs for higher performance impedance-matched cable interconnections. These connectors can be used in a variety of applications where true 75 Ω performance is needed to insure low signal distortion. Designed for the most popular 75 Ω cables used in broadcast and CATV applications as well as for plenum and other cables, these connectors feature crimp-crimp cable affixment for quick and reliable installation.

Two distinct types of 75 Ω BNCs are available, and both mate with each other and with 50 Ω BNCs. Type 1 is designated 75 Ω BNC-T1 and provides constant 75 Ω performance with low VSWR DC – 4 GHz. Type 2 is designated 75 Ω BNC-T2 and is usable with low reflection DC - 1 GHz. For applications above 1 GHz, Type 1 is recommended.

Part numbers that are listed with the appropriate M39012 number are military grade connectors produced in accordance with and actively qualified to the military specification MIL-C-39012. Connectors not listed with the M39012 number constitute the industrial grade product offering. These connectors provide comparable performance and generally feature nickel-plated brass bodies, Teflon insulators, and either gold or silver-plated center contacts. Amphenol's commercial grade connector offering carries the part number designation "RFX" for easy recognition. These low-cost connectors typically utilize die cast and molded components. While performance will not be equal to the industrial or military grade products, these connectors are ideal for use on a variety of commercial applications.

Reverse Polarity BNCs are also available. Reverse polarity is a keying system accomplished with a reverse interface, and ensures that reverse polarity interface connectors do not mate with standard interface connectors. Amphenol accomplishes this by inserting female contacts into plugs and male contacts into jacks. Other manufacturers may use reverse threading to accomplish reverse polarity keying.

BNC Coaxial Connectors

PLUG CRIMP ATTACHMENTS FOR FLEXIBLE CABLE

Straight Crimp Plug - Captive Contact - Standard Cable

Straight Solder Plug - Semi-Rigid Cable

Straight Crimp Plug - Captive Contact - Miniature Cable

Straight Crimp Plug - Captive Contact - Plenum Cable

Straight Crimp Plug - Pin-In-Pin - Miniature Cable

Straight Crimp Plug - Miniature Cable

Straight Crimp Plug - Single Crimp

RIGHT ANGLE PLUG CRIMP ATTACHMENTS FOR FLEXIBLE CABLE

Right Angle Crimp/Solder Plug - Standard Cable

Right Angle Crimp/Solder Plug -Plenum Cable

Right Angle Crimp/Solder Plug - Miniature Cable

Straight PCB Mount Jack - Three Legs

Straight PCB Mount Jack

Straight PCB Mount Jack

Straight PCB Mount Jack

Straight PCB Edge Mount Jack - End Launch

Bulkhead Vertical PCB Receptacle - End Launch

Commercial Straight PCB Mount Jack

Commercial Straight PCB Mount Jack — Metal Body

Commercial Right Angle PCB Mount Jack

<u>Commercial Right Angle PCB Mount Jack — Metal Body</u>

BULKHEAD FEEDTHROUGH ADAPTERS

Jack-To-Jack Bulkhead Adapter

Jack-To-Jack Bulkhead Adapter

Jack-To-Jack Bulkhead Adapter

Jack-To-Plug Bulkhead Adapter - Push-On

BULKHEAD ISOLATED GROUND ADAPTERS

Jack-To-Jack Bulkhead - Isolated Adapter

Jack-To-Jack Bulkhead - Isolated Adapter

ADAPTERS

Jack-To-Jack Adapter

Plug-To-Plug Adapter

Right Angle Adapter - Plug-To-Jack

TEE ADAPTERS

Tee Adapter - Jack-To-Jack-To-Jack

Tee Adapter - Jack-To-Plug-To-Jack

Tee Adapter - Jack-To-Plug-To-Jack

Tee Adapter - Jack-To-Jack-To-Plug

TERMINATORS

BNC Terminator Plug

BNC Terminator Jack

ACCESSORIES

BNC Male Cap & Chain

BNC Male Shorting Cap

Features & Benefits

- Bayonet coupling mechanism provides quick mating and unmating
- 50 Ω and 75 Ω impedance designs allow customers to match impedance to system requirements
- 50 Ω and 75 Ω connectors are intermateable to ensure non-destructive mating
- Three grades of connectors are available for military, industrial and commercial applications

Applications

- Antennas
- Broadcast (75 Ω)
- Components
- Oscilloscopes
- Radios
- Telecom

- Automotive
- Cable Assemblies
- Computers/LANs
- Medical Equipment
- Satcom

- Base Stations
- Cable Modems
- Instrumentation
- Mil-Aero
- Surge Protection

50 Ω BNC Specifications

Electrical	
Impedance	50 Ω nominal
Frequency Range	0-4 GHz with low reflection
Voltage Rating	500 volts peak

Dielectric Withstanding Voltage	1,500 volts rms
VSWR	M39012 straight connectors: 1.3 max 0-4 GHz M39012 right angle connectores: 1.35 max 0-4 GHz
MIL-C-39012 Contact Resistance	Center contact: 1.5 m Ω ; Outer contact: 0.2 m Ω
MIL-C-39012 Insulation Resistance	5,000 ΜΩ
MIL-C 39012 Braid to Body	0.1 milliohm
MIL-C-39012 RF Leakage	-55 dB min at 3 GHz
MIL-C-39012 Insertion Loss	0.2 dB min at 3 GHz
Mechanical	
Mating	2-stud bayonet coupling per M39012
Braid/Jacket Cable Affixment	All crimps are hex braid; clamps are screw-thread net and braid clamp
Center Conductor Cable Affixment	Crimps are crimp or solder; all other are solder only
Captivated Contacts	All crimps unless specified otherwise
Cable Retention	Crimps: 20-100 lbs; All others: 30-70 lbs
Material	
Male Contact	Brass
Female Contact	Beryllium copper or phosphorous bronze, silver or gold-plated
Other Metal Parts	Brass, nickel finish; M39012 is silver finish
Insulator	TFE, copolymer of styrene, glass-TFE (hermetically sealed)
Crimp Ferrule	Copper/brass
Environmental	
Temperature Range	TFE insulators: - 65°C to + 165 °C Copolymer of Styrene: - 55°C to + 85°C
Weatherproof	Clamps with clamp gaskets; crimps with heat-shrink tubing
Mermetic Seals	Pass helium leak test of 2x10 ⁻⁸ cc/second
Shock	MIL-STD-202 method 202
Vibration	MIL-STD-202 method 202, test condition D
Moisture Resistance	MIL-STD-202 method 106
Corrosion	MIL-STD-202 method 101, test condition B
Temperature Cycling	MIL-STD-202 method 102, test condition D
Altitude	MIL-STD-202 method 105, test condition C
Military	
MIL-C-39012	Where applicable
Note: Those characteristics are typic	cal but may not apply to all connectors

Note: These characteristics are typical but may not apply to all connectors.

75 Ω BNC Specifications

·		
Electrical		
Impedance	75Ω nominal	
Frequency Range	0-4 GHz	
Voltage Rating	500 volts rms	
Dielectric Withstanding Voltage	1,500 volts rms	
VSWR	Type 1: 1.5+0.1 f(GHz) DC to 4 GHz Type 2: 1.00+0.25 f(GHz) DC to 1 GHz	
Mechanical		
Mating	2-stud bayonet lock	
Cable Affixment	Crimp-crimp	
Material		
Body, Coupling Sleeve, Male Contact	Brass	
Female Contact	Beryllium copper or phosphorous bronze	
Crimp Ferrule	Copper alloy	
Contact Plating	Gold	
Insulator	TFE, copolymer of styrene, glass-TFE (hermetically sealed)	

Other Metal Parts Plating	Nickel
Environmental	
Temperature Range	TFE insulators: - 65°C to + 165 °C Copolymer of Styrene: - 55°C to + 85°C
Weatherproof	Clamps with clamp gaskets; crimps with heat-shrink tubing
Mermetic Seals	Pass helium leak test of 2x10 ¹⁰⁻⁸ cc/second
Shock	MIL-STD-202 method 202
Vibration	MIL-STD-202 method 204, test condition D
Moisture Resistance	MIL-STD-202 method 106
Corrosion	MIL-STD-202 method 101, test condition B
Temperature Cycling	MIL-STD-202 method 102, test condition D
Altitude	MIL-STD-202 method 105, test condition C

Note: These characteristics are typical but may not apply to all connectors.

Reverse Polarity BNC Specifications

Electrical	
Impedance	50 Ω
Frequency Range	0-4 GHz
Voltage Rating	500 volts peak
Dielectric Withstanding Voltage	1,500 volts rms
VSWR	M39012 straight connectors: 1.3 max @ 0-4 GHz M39012 right angle connectors: 1.35 max @ 0-4 GHz
Insertion Loss	0.18 dB @ 9 GHz
Insulation Resistance	≥ 5,000 MΩ
Mechanical	
Mating	Bayonet coupling
Braid/Jacket Cable Affixment	Hex crimp
Center Conductor Cable Affixment	Hex crimp or solder
Captivated Contact	Except as noted
Cable Retention	20-100 lbs depending on cable
Material	
Male Cetner Contact	Brass, gold plated
Female Center Contact	Beryllium copper or phosphorous bronze, gold plated
Other Metal Parts	Brass with bright nickel finish
Insulators	TFE
Weatherproof Gaskets	Silicone rubber
Environmental	
Temperature Range	- 65°C to + 165 °C
Weatherproof	When mated with other Amphenol RP-BNC connectors
Corrosion	MIL-STD-202, method 101, test condition B

Note: These characteristics are typical but may not apply to all connectors.