

A New Kind of RF Solution

Products Site Tools RF Made Simple Distributors About Us News Room Contact Us Login Shopping Cart

Our Products
Search Results for: Bulkhead Crimp Jack

7/16
BNC
D-Sub



Part Number: 182318
Family/Series: UHF/Mini-UHF Coaxial

Connectors

Product Type: MINI-UHF SERIES **Description:** Bulkhead Crimp Jack **Cable:** 58/58A/58C/141/303/LMR195/

Add to Cart | Product Specs | Customer Drawing

B7806A **

Between-Series Adapters

Shielded Terminations

Strain-Relief Boots

Tools

FME

MCX

<u>SMA</u>

SMB

SMC

TNC Twin BNC

Type F
Type N
UHF

MMCX

View All Products

Copyright @ 2001 - 2008 Amphenol Connex. All rights reserved.

Copyright | Terms & Conditions | Contact Us | Amphenol.com

Cable Group: 01

Insulation: Teflon

Impedance: 50 ohms

Finish: Nickel

Crimp Tool: A

Products Site Tools RF Made Simple Distributors About Us News Room Contact Us Login 🚍 Shopping Cart

Our Products

7/16

BNC D-Sub

FME

<u>MCX</u>

MMCX

<u>SMA</u>

SMB

SMC TNC

Twin BNC

Type F

Type N UHF

Between-Series Adapters

Shielded Terminations

Strain-Relief Boots

Tools


View All Products

UHF connector series

Features & Benefits | Applications | Specs | Assembly Instructions

Invented in the 1930's by an Amphenol engineer named E. Clark Quackenbush, UHF coaxial connectors are general purpose units developed for use in low frequency systems from 0.6 - 300 MHz. Invented for use in the radio industry, UHF is an acronym for Ultra High Frequency because at the time 300 MHz was considered high frequency.

UHF connectors feature a threaded coupling. Because these connectors are low-cost, the impedance is variable.



UHF/Mini-UHF Coaxial Connectors

UHF SERIES

Straight Crimp Plug

Straight FCP Plug

Straight Solder Plug - Ug Standard, PL-259 Type

Reducing Adapter

Straight Crimp Jack

Panel Crimp Jack

Panel Receptacle

Bulkhead Receptacle

Jack-To-Jack Adapter

Jack-To-Jack Adapter

MINI-UHF SERIES

Mini-UHF Terminator Plug

Right Angle 2-Piece Crimp Plug

Straight 3-Piece Crimp Plug - Captive Contact

Straight 3-Piece Crimp Jack

Bulkhead Crimp Jack

Bulkhead Receptacle Jack - Rear Mount

Features & Benefits

- Optional reducing adapters accommodate a wide range of popular coaxial cables
- Solder termination types require no special assembly tools
- Crimp termination types provide a lower cost installation method
- Large-size threaded coupling is rugged design
- Non-demanding specifications and low cost

Applications

Antennas

- Cable Assembly
- Low Frequency Applications

- Public Address Systems
- CB Radios

UHF Specifications

Electrical	
Impedance	Non-constant
Frequency Range	0 - 300 MHz
Voltage Rating	500 volts peak
Mechanical	
Mating	5/8-24 threaded coupling
Cable Affixment	Braid solder, set screw, clamp and crimp

Material	
Male Contact	Brass with silver plating
Female Contact	Beryllium copper with silver plating
Bodies	Brass and die cast zinc
Other Metal Parts	Brass
Plating	Nickel and silver
	TFE, copolymer of styrene, polystyrene, mica-filled phenolic and PBT polyester or equivalent
Environmental	
	Mica-filled phenolic insulators: -55°C to +149°CCopolymer of styrene and polystyrene: -55°C to +85°CTFE insulators: -65°C to +165°C
Weatherproof	Except as noted, all UHF series are non-weatherproof

Note: These characteristics are typical but may not apply to all connectors.



Copyright © 2001 - 2008 Amphenol Connex. All rights reserved.

Copyright | Terms & Conditions | Contact Us | Amphenol.com