

Conforms to EN1088, EN292, EN60204-1 CSA approved



# MA Series

## **Magnetically Actuated Safety Interlock Switches**

- Large selection—choose from a large selection of contact configurations housed in plastic to satisfy most application requirements
- NEMA 6 enclosure enables the MA Series switches to satisfy most application requirements (MA 3, 4, 5 are NEMA 4)
- Misalignment tolerant—the non-contact actuation of the MA Series switches makes them very tolerant to misalignment of up to 10 mm (0.39 in.)
- Variety of terminations—select from various cable lengths or terminal strip termination for easy installation. Cable connector available on selected models.
- Long life—the MA Series safety interlock switches are designed for a minimum of one million actuations



**Go to the Engineering Guide** For in-depth information on

safety standards and use.



For More Guarding Products See Section N for safeguarding cutting and turning machines





## Actual Size










## Applications

Typical applications are on sliding guard doors or swinging guard doors.






## Operation

## **Operating Principle**





Encapsulated in the MA Series is a unique high-power industrial reed which is de-rated by a non-resetable overload protection circuit depending on switch type. On presenting the actuator to the switch, the high intensity magnetic field from the actuator causes the contacts to close. On removing the actuator (opening the door), the safety contacts open, isolating the machine.




It is advisable, where possible, to mount the switch and actuator on non-ferrous materials otherwise it may affect the operating distances.

## **Mounting Examples**





#### **Contact Arrangement**







Wherever possible the units should be mounted so that no access can be obtained to the switch when the guard door is open, thus preventing attempts to defeat the safety system.



**Go to the Engineering Guide**For in-depth information on safety standards and use.



For More Guarding Products See Section N for safeguarding cutting and turning machines



Universal Mounting Brackets can be used with this product. See page G241 for details.





## Specifications

Floatrical	All Madala Uniona Indicated		
Electrical	All Models Unless Indicated  AC models	MA-1 thru 6, 10, 11, 12, 13, 16 — 1 N/C	MA 11 10 10 01 0 N/O
Safety Contacts:	DC models		MA-11, 13, 16, 21 — 2 N/C
Cofety Contest Operating Distance	DC models	MA-9, 11, 12, 13, 14, 16 — 1 N/C	MA-11, 13, 15, 16, 20, 21 — 2 N/C
Safety Contact Operating Distance:	MA-2, 4, 11, 12, 13, 14, 15, 16, 21	Make 7-12 mm (0.28-0.47in.); Break 1	2-25 111111 (0.47-0.98 111.)
Auxiliary Contacts:	MA-3	1 N/O 1 N/C	
Avv. Contact Operating Distance	MA-2, 4, 16, 21	Make 8-13 mm (0.39-0.51 in.); Break 8	2.10 mm (0.21.0.20 in )
Aux. Contact Operating Distance:	MA-3	· ·	•
Cofety Dated Valters	AC models: All except MA-10	Make 21 mm (0.83 in.); Break 24 mm 230 VAC	(0.94 III.)
Safety Rated Voltage:	AC models: All except MA-10  AC model: MA-10	110 VAC	
	DC models	30 VDC	
Cofaty Dated Currents	AC models: All except MA-3	2 A, fuse externally 1.6 A quick acting	
Safety Rated Current:	AC model: MA-3		
		3 A, fuse externally 2.5 A quick acting 1 A, fuse externally 800 mA quick actin	0.00
	DC models: All except MA-15 DC model: MA-15	0.3 A max., fuse externally 0.2 A quick	=
Internal Fuse	AC models	2 A fast acting	acting
internal ruse	DC models	1 A fast acting	
External Fuse (Customer Supplied)	AC models	1.6 A fast acting	
External Fuse (Gustomer Supplieu)	DC models: All except MA-15	0.8 A fast acting	
Electrical Life:	DC IIIodeis. All except MA-13	1 x 10 <sup>6</sup>	
Mechanical—Special Safety Reed		Safety	Aux.
Closing Time:		3.0 mS	0.5 mS
Drop-Out Time:		2.1 mS	0.3 mS
Bounce Time:		0.7 mS	0.7 mS
Shock:		10 G	10 G
Vibration:		10 G, 50 to 100 Hz	10 0
Mechanical		10 4, 00 10 100 112	
Mounting:		Any position	
Case Material:		Molded ABS	
Actuator Material:		Molded ABS	
Wiring Connection:		Various lengths or male M12 micro co	nnector
Weight:		384 g (14 oz.)	
Color:		Red	
Mechanical Life:		10 x 10 <sup>6</sup>	
Environmental			
Protection:	MA-3, 4, 5	IP65 (NEMA 4)	
	All models except MA-3, 4, 5	IP67 (NEMA 6)	
Operating Temperature:	MA-11, 12, 13, 14, 15, 16	-10 to 55°C (14 to 131°F)	
	All models except:	,	
	MA-11, 12, 13, 14, 15	-10 to 65°C (14 to 149°F)	
Compliance			
Standards:	EN1088, EN292, EN60204-1		
Approvals/Listings:			
	MA-1, 2, 3, 4, 5, 6, 9, 10, 20, 21	cCSAus (UL and C-UL pending)	
	MA-11, 12, 13, 14, 15, 16	(UL and C-UL pending)	

Specifications are subject to change without notice.


Note: The safety contacts of the Omron STI switches are described as normally closed (N/C)—i.e., with the guard closed, actuator in place, and the machine able to be started.





## **■ Application Diagram**

## Typical Application of MA Series with a Safety Monitoring Relay



For a full explanation of the circuit operating principle and fault detection, see "Common Circuit Examples" in the Engineering Section of this catalog.

#### **Pin Assignments with Connector Option**

MA-2	
Pin 1 same as Red lead	N/C Safety
Pin 3 same as Blue lead	N/C Safety
Pin 2 same as Green lead	N/O Auxiliary
Pin 4 same as Yellow lead	N/O Auxiliary
MA-6 and MA-9	
Pin 1 same as Brown lead	N/C Safety
Pin 3 same as Blue lead	N/C Safety
Pins 2 & 4 not used	

MA-15, 21	
Pin 1 same as Red/Blue lead	N/C Safety
Pin 3 same as Red lead	N/C Safety
Pin 2 same as Red/Black lead	N/C Safety
Pin 4 same as Red/White lead	N/C Safety
Pin 5 same as Red/Yellow lead	N/O Auxiliary
Pin 6 same as Green lead	N/O Auxiliary

MA-20	
Pin 1 same as Brown lead	N/C Safety
Pin 3 same as Blue lead	N/C Safety
Pin 2 same as White lead	N/C Safety
Pin 4 same as Black lead	N/C Safety



## Go to the Engineering Guide

For in-depth information on safety standards and use.



## For More Guarding Products


See Section N for safeguarding cutting and turning machines






#### ■ Dimensions — mm/in.

MA-1, 2, 20, 21






MA-3, 4, & 5

2 HOLES  $\begin{array}{c} 50 \\ 4 \text{ THRU} \\ \hline \\ 38.5 \\ \hline \\ 1.52 \\ \end{array}$   $\begin{array}{c} 60 \\ \hline \\ 2.72 \\ \hline \end{array}$   $\begin{array}{c} 0.25 \\ \hline \\ \hline \\ \hline \\ \hline \\ \hline \end{array}$   $\begin{array}{c} 60 \\ \hline \\ \hline \\ \hline \\ \hline \\ \hline \end{array}$   $\begin{array}{c} 760 \\ \hline \\ \hline \\ \hline \\ \hline \end{array}$ 


**ACTUATOR** 




MA-6, 9, 10, 16

**SWITCH** 

6 0.25



MA-14 / MA-15





Model	Contacts	Wiring Entry	Part No.
DC ONLY			
MA-2DPC4	1 N/C + 1 N/O	4 m cable, pre-wired	44507-0390
MA-2DPC10	1 N/C + 1 N/O	10 m cable, pre-wired	44507-0380
MA-2DPC15	1 N/C + 1 N/O	15 m cable, pre-wired	44507-0370
MA-2DPCC	1 N/C + 1 N/O	Connector, Brad Harrison	44507-0650
MA-9DPC2 (24 VDC only)	1 N/C	2 m cable, pre-wired	44507-0100
MA-9DPC4 (24 VDC only)	1 N/C	4 m cable, pre-wired	44507-0200
MA-9DPC6 (24 VDC only)	1 N/C	6 m cable, pre-wired	44507-0320
MA-9DPC10 (24 VDC only)	1 N/C	10 m cable, pre-wired	44507-0220
MA-9DPCC (24 VDC only)	1 N/C	Connector, Brad Harrison	44507-0620
MA-11DP10C3	1 N/C	3 m cable, pre-wired	44507-1110
MA-11DP11C3	1 N/C + 1 N/O	3 m cable, pre-wired	44507-1120
MA-11DP20C3	2 N/C	3 m cable, pre-wired	44507-1130
MA-11DP20C5	2 N/C	5 m cable, pre-wired	44507-1131
MA-11DP21C3	2 N/C + 1 N/O	3 m cable, pre-wired	44507-1140
MA-12DP10C3	1 N/C	3 m cable, pre-wired	44507-1210
MA-12DP11C3	1 N/C + 1 N/O	3 m cable, pre-wired	44507-1220
MA-13DP10C3	1 N/C	3 m cable, pre-wired	44507-1310
MA-13DP11C3	1 N/C + 1 N/O	3 m cable, pre-wired	44507-1320
MA-13DP20C3	2 N/C	3 m cable, pre-wired	44507-1330
MA-13DP21C3	2 N/C + 1 N/O	3 m cable, pre-wired	44507-1340
MA-13DP21C10	2 N/C + 1 N/O	10 m cable, pre-wired	44507-1341
MA-14DP10C3	1 N/C	3 m cable, pre-wired	44507-1410
MA-14DP11C3	1 N/C + 1 N/O	3 m cable, pre-wired	44507-1420
MA-15DP21C3*	2 N/C + 1 N/O	3 m cable, pre-wired (300 mA max.)	44507-1540
MA-15DP21C5*	2 N/C + 1 N/O	5 m cable, pre-wired (300 mA max.)	44507-1541
MA-15DP21CC*	2 N/C + 1 N/O	Connector, Brad Harrison	44507-1549
MA-16DP10C3 (DC only)	1 x N/C	3 m cable, pre-wired	44507-1610
MA-16DP10C6 (DC only)	1 x N/C	6 m cable, pre-wired	44507-1611
MA-16DP11C3 (DC only)	1 x N/C + 1 N/O	3 m cable, pre-wired	44507-1620
MA-16DP11C6 (DC only)	1 x N/C + 1 N/O	6 m cable, pre-wired	44507-1621
		· •	
MA-16DP20C3 (DC only)	2 x N/C 2 x N/C	3 m cable, pre-wired	44507-1630
MA-16DP20C6 (DC only) MA-16DP21C3 (DC only)		6 m cable, pre-wired	44507-1631
\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	2 N/C + 1 N/O	3 m cable, pre-wired	44507-1640
MA-16DP21C6 (DC only)	2 N/C + 1 N/O	6 m cable, pre-wired	44507-1641
MA-20DPC4 (24 VDC only)	2 N/C	4 m cable, pre-wired	44507-0340
MA-20DPCC (24 VDC only)	2 N/C	Connector, Brad Harrison	44507-0630
MA-21DPC2 (24 VDC only)	2 N/C + 1 N/O	2 m cable, pre-wired	44507-0270
MA-21DPC4 (24 VDC only)	2 N/C + 1 N/O	4 m cable, pre-wired	44507-0280
MA-21DPC6 (24 VDC only)	2 N/C + 1 N/O	6 m cable, pre-wired	44507-0290
MA-21DPC10 (24 VDC only)	2 N/C + 1 N/O	10 m cable, pre-wired	44507-0350
MA-21DPC15 (24 VDC only)	2 N/C + 1 N/O	15 m cable, pre-wired	44507-0360
MA-21DPCC	2 N/C + 1 N/O	Connector, Brad Harrison	44507-0670
pare Actuator (1–5 & 20, 21), Red ABS I			44507-0700
pare Actuator (6, 9 & 10), Red ABS Plas			44507-0710
Replacement Actuator for MA-11, Red AB			44507-0711
deplacement Actuator for MA-12, Red AB			44507-0712
leplacement Actuator for MA-13, Red AB			44507-0713
Replacement Actuator for MA-14, Red AB			44507-0714
Replacement Actuator for MA-15, Red AB			44507-0715
Replacement Actuator for MA-16, Red AB	S Plastic		44507-0716

<sup>\*</sup>MA-15 switches are not compatible with the following Omron STI safety relays: SR203M, SR203AM, SR208AD, SR209AD and all Legacy Relays.

= New product



