
## **★★★★★** 7000 Series Angulated Head Cutters

### Made in the USA

Edge hardened to 63/65 Rockwell "C" Stainless Steel Leaf Springs – Fine Cutting of Small Leads and Wires



### 7100 Series Angulated Head Cutters with Long Foam Cushion Grips

### \*\*\*\* 6" Miniature

**Angulated Head Cutter 7175E** Optimum Flush Cut

Cutting Capacity .001" – .018"

A B C D F G
.710" .275" .430" N/A 50° .160"

# 7200 Series Angulated Head Cutters with Ergonomic Molded Grips

### \*\*\*\* 5 1/4" Miniature

**Angulated Head Cutter** 

**7275E** Optimum Flush Cut
Cutting Capacity .001" – .018"

A B C D F G
.710" .275" .430" N/A 50° .160"



**7182E** Optimum Flush Cut
Cutting Capacity .003" – .025"

A B C D F G
.710" .275" .430" N/A 50° .220"



**7282E** Optimum Flush Cut Cutting Capacity .003" – .025" A B C D F G .710" .275" .430" N/A 50° .220"

### \*\*\*\* 6" Large Angulated Head Cutter

**7172E** Maximum Flush Cut
Cutting Capacity .005" – .032"

A B C D F G
.710" .275" .430" N/A 50° .310"



7272E Maximum Flush Cut
Cutting Capacity .005" - .032"

A B C D F G
.710" .275" .430" N/A 50° .310"

### \*\*\*\* 6" Large

**Angulated/Tapered Tip Cutter** 

7104E Maximum Flush Cut
Cutting Capacity .003" – .025"

A B C D F G
.500" .275" .430" .025" 50° .300"

### **★★★★★ 5** ¼" Large

**Angulated/Tapered Tip Cutter** 

**7204E** Maximum Flush Cut
Cutting Capacity .003" – .025"

A B C D F G
.500" .275" .430" .025" 50° .300"

