

Adjustable Range & Fixed-focus Reflective Photoelectric Sensor

The EQ-500 series of photoelectric sensors provides a long-range diffuse reflective solution that is suitable for applications where it is not feasible to get close to the sensing object. The sensor is impervious to changes in an object's angle, gloss, or even color, so you get an accurate detection every time. Built in an IP-67 rated enclosure, the EQ-500 series is also good for use in harsh environments. The sensing range is easily adjustable to a maximum of 2.5m (1m version also available). There are two main product types available:

Multi-Voltage Type

- Can be powered with 24-240VAC or 12-240VDC. This free ranging input allows for nearly any power source in the world to be
 used.
- 1 Form A relay output is used which is suitable for direct switching of a load up to 3A 250VAC (resistive) or 3A 30VDC (resistive).


DC-Voltage Type


- Powered by 12-24 VDC
- NPN and PNP transistor outputs are used.
- Equipped with Background and Foreground suppression to eliminate the effects of unwanted objects and provides more stability in your sensing operation.

All models are also available with a built-in ON or OFF delay timer function.

Model Name	Model Pic	Туре	Output Operation	Output Configuration	Emitting Element	Max. Range (mm)	Max. Range (in)
Sort 🔺 🔻		Sort 🔺 🔻	Sort 🔺 🔻	Sort 🔺 🔻	Sort 🔺 🔻	Sort 🔺 🔻	Sort 🔺 🔻
EQ-511T		DC-voltage Long sensing Adjustable Range, BGS/ FGS w/ Timer	Light-ON/Dark- ON	NPN/PNP	Infrared LED	2500	98.4
EQ-512		DC-voltage Long sensing Adjustable Range, BGS/ FGS	Light-ON/Dark- ON	NPN/PNP	Infrared LED	1000	39.4
EQ-512T		DC-voltage Long sensing Adjustable Range, BGS/ FGS w/ Timer	Light-ON/Dark- ON	NPN/PNP	Infrared LED	1000	39.4


EQ-501(T) EQ-502(T) EQ-511(T) EQ-512(T) Sensor






Notes: 1) The operation mode switch of the DC-voltage type is the DIP switch. 2) **EQ-5**□**T** does not incorporate those.

Assembly dimensions with sensor mounting bracket MS-EQ5-01 (Optional) (Foot angled mounting)





SPECIFICATIONS

_			Multi-v	/oltage		DC-voltage DC-voltage						
		Type		With timer		With timer		With timer		With timer		
Iten	1	Model No.	EQ-501	EQ-501T	EQ-502	EQ-502T	EQ-511	EQ-511T	EQ-512	EQ-512T		
Adju	stable range (Note 1) (Note 2)	0.2 to 2.5 m 0.	656 to 8.202 ft	0.2 to 1.0 m 0	0.2 to 1.0 m 0.656 to 3.281 ft		.656 to 8.202 ft	0.2 to 1.0 m 0	.656 to 3.281 ft		
Sensing range (at maximum setting distance) (Note 2)		0.1 to 2.5 m 0.	328 to 8.202 ft	0.1 to 1.0 m 0	.328 to 3.281 ft	0.1 to 2.5 m 0.328 to 8.202 ft						
Hys	teresis					10 % or less of o	peration distanc	e				
Supply voltage		24 to 240 V AC \pm 10 $\%$ or 12 to 240 V DC \pm 10 $\%$ Ripple P-P 10 $\%$ or less				12 to 24 V DC ± 10 % Ripple P-P 10 % or less						
Power / Current consumption		AC: 4 VA or less DC: 3 W or less	AC: 5 VA or less DC: 4 W or less	AC: 4 VA or less DC: 3 W or less	AC: 5 VA or less DC: 4 W or less							
Output		Relay contact 1a • Switching capacity: 250 V AC 3 A (resistive load) 30 V DC 3 A (resistive load) • Electrical life: 100,000 or more switching operations (switching frequency 1,200 operations/hour) • Mechanical life: 50 million or more switching operations (switching frequency 18,000 operations/hour)				NPN open-collector transistor • Maximum sink current: 100 mA • Applied voltage: 30 V DC or less (between output and 0 V) • Residual voltage: 1 V or less (at 100 mA sink current) 0.4 V or less (at 16 mA sink current) PNP open-collector transistor • Maximum source current: 100 mA • Applied voltage: 30 V DC or less (between output and + V) • Residual voltage: 1 V or less (at 100 mA source current) 0.4 V or less (at 16 mA source current)						
	Output opera	ation		Switchable either Detection-ON or Detection-OFF								
Short-circuit protection						Incorporated						
Res	ponse time		20 ms or less (For EQ-50 □ T depends on the setting timer period)				2 ms or less (For EQ-51 T depends on the setting timer period)					
Орє	ration indicat	tor	Orange LED (lights up when the output is ON)									
Stal	oility indicator	r			Green LED) (lights up under	stable operating	g condition)				
Dist	ance adjuste	r			2-tu	ırn mechanical a	djuster with indic	cator				
Sensing mode						Switchable either BGS or FGS function						
Timer function			Incorporated with variable (0.1 to 5 sec.) ON-delay / OFF-delay timer		Incorporated with variable (0.1 to 5 sec.) ON-delay / OFF-delay timer		Incorporated with variable (0.1 to 5 sec.) ON-delay / OFF-delay timer		Incorporated with variable (0.1 to 5 sec.) ON-delay / OFF-delay timer			
Autor	natic interference	prevention function		1	I	Incorporate	ed (Note 3)	1	I	1		
	Protection		IP67 (IEC)									
9			-20 to +55 °C −4 to +131 °F (No dew condensation or icing allowed), Storage: -30 to +70 °C −22 to +158 °F									
esistance	Ambient hui	midity	35 to 85 % RH, Storage: 35 to 85 % RH									
	Ambient illu	minance	Sunlight: 10,000 ℓx at the light-receiving face, Incandescent light: 3,000 ℓx at the light-receiving face									
enta	Voltage with	nstandability	2,000 V AC for one min. among supply terminals, non-supply metal parts and relay contact output terminals, 1,000 V AC for one min. between relay contacts									
ronm	Voltage withstandability Insulation resistance Vibration resistance		100 MΩ, or more, with 500 V DC megger among supply terminals, non-supply metal parts and relay contact output terminals as well as between relay contacts									
Envi	Vibration resistance		10 to 55 Hz frequency, 1.5 mm 0.059 in amplitude in X, Y and Z directions for two hours each									
Shock resistance		500 m/s² acceleration (50 G approx.) in X, Y and Z directions for three times each										
Emitting element		Infrared LED (modulated)										
Receiving element		2-segment photodiode										
Material			Encl	osure: ABS, Fro		•	cover: Polycarbo	onate				
Connection method		Enclosure: ABS, Front cover: Polycarbonate, Display cover: Polycarbonate Screw-on terminal connection										
Con	nection meth	Cable		Suitable for round cable ϕ 9 to ϕ 11 mm ϕ 0.354 to ϕ 0.433 in								
					Suitable for re	ound cable	φ11 mm φ0.35	4 to <i>ϕ</i> 0.433 in				
Cab				Extension		ound cable ϕ 9 to a 328.084 ft is po	· · · · · · · · · · · · · · · · · · ·		abtyre cable			
Cab	le le length						· · · · · · · · · · · · · · · · · · ·	nm ² , or more, ca	abtyre cable			