

CM Series

Compact Coded Magnetic Safety Interlock Switch and Control Units

- A fully monitored system that meets Category 3 when 1 to 30 plus switches are used with the **CM Control Units**
- External Device Monitoring (EDM) with monitored manual or automatic reset
- NEMA 6 switch enclosures satisfy most application requirements
- Magnetically coded switches are tamper resistant to common magnets
- Misalignment tolerance of (5 and 9 mm) reduces nuisance tripping

- Dual channel N/C E-stop input is monitored by the CM-S41 control in addition to four CM switches
- Mechanical interlock switches may be used with the CM-S4 control unit
- CM control units may replace a safety relay in most applications
- CM-S221 switches with 2 N/C safety contacts and 1 N/O auxiliary contact may be used with many other safety monitoring relays accepting 2 N/C safety inputs including the SR103AM; CM-S221 switches are not compatible with Legacy Relay products or the SR203M/AM, SR208AD or SR209AD







Conforms to EN292, EN60204-1, EN954-1, EN1088, EN60947-5-3, EN947-5-3, EN50081, EN50082, EN61000-6-2 UL and C-UL listed, TUV certified

Description

The CM switches are tamper resistant non-contact safety interlock switches that operate with their own control units except for the CM-S221 switch. The CM-S221 switch will work with many safety monitoring relays accepting 2 N/C safety inputs. The CM control units will monitor one to four CM switches to category 3 in accordance with EN954-1.

The CM-S4 controller is designed to work with with non-contact switches with dry contacts 1 N/C + 1 N/O. The CM-S21 and CM-S41 controllers and the CM-SE expansion module are designed to only accept CM-S11 and CM-S31 switches. These controllers sense voltage and current changes in the switch circuit when the actuator is presented to the switch.

The CM control units provide EDM (External Device Monitoring, also called MPCE monitoring) and an automatic reset function. This allows the CM control units to replace a safety relay in most applications.

The NEMA 6 encapsulated design of the CM Series switch makes it ideal for harsh environments.

Mechanical switches and CM Series switches may be used together with a single CM-S4 control unit for applications requiring both non-contact and mechanical safety interlock switches.

The CM Series switch and actuator are available in four sizes plus a stainless steel version to accommodate a variety of application requirements.









Actual Size

CM-S31 Read Head



CM-S2 and CM-S221 Read Heads




Universal Mounting Brackets can be used with this product. See page G241 for details.


Operation

Operating Principle for Coded Magnetic Switch with Conventional Dry Contacts

On presenting the actuator to the switch, the coded, high intensity magnetic field from the actuator causes the contacts to close. On removing the actuator (opening the door), the safety contacts open, isolating the machine.





Contact Arrangements




Note: The CM-S11 and CM-S31 switches are not conventional dry contacts.

Mounting Examples






NOTE: ACTUATOR MUST NOT STRIKE READ HEAD



Recommended gap between sensor and actuator.


Installation Alignments






Applications


Typical applications are on sliding guard doors or swinging guard doors.







In the illustration above, the guard door is open and the machine is stopped. Machine will start when the guard door is closed, and the reset button is pressed.



In the illustration above, all of the guard doors are open and the machine is stopped. Machine will start when all the guard doors are closed, and the reset button is pressed.



Go to the Engineering Guide

For in-depth information on safety standards and use.



For More Guarding Products

See Section N for safeguarding cutting and turning machines







■ Control Unit Specifications

Electrical	CM-S4	CM-S41, CM-S21 & CM-SE	
Power Supply:	24 VAC/DC ± 10%	CM-S41 — 24 VAC/DC, 110 VAC	
		CM-S21 & CM-SE — 24 VAC/DC	
Power Consumption:	2.4 VA typical	CM-S41 — 6 VA; CM-S21 & CM-SE — 3 VA	
External Fuse (Operating Voltage):	0.25 A quick acting	_	
Input Fuse (Supply Voltage):	_	500 mA resetable	
Safety Inputs:	1 N/O + 1 N/C	CM-S41 — 4 CM-S11 or CM-S31 switches	
		CM-S21 — 2 CM-S11 or CM-S31 switches	
		CM-SE — 5 CM-S11 or CM-S31 switches	
Max Cable Length:	_	100 m (328 ft.)	
Max Input Resistance:	Contact factory		
Min. Approach Speed:	Contact factory		
Relay Outputs:	1 N/O safety + 1 N/O aux.	CM-S41 & CM-S21 — 2 N/O; CM-SE — N/A	
Auxiliary Contact of Controls:	4 A, 24 VAC/DC	CM-S41 & CM-S21 — 1 N/C; CM-SE — N/A	
Max Switched Current/Voltage:	4 A / 24 VAC/DC	4 A / 230 VAC; 2 A / 24 VDC (resistive)	
Min Switched Current/Voltage:	4 mA / 12 V	10 V / 10 mA	
Impulse Withstand Voltage:	250 V		
Max Drop-Out Time:	18 ms	Deactivation by sensor 13 mS	
Max Output Fuse:	4 A quick acting	AC = 5 A; DC = 2.5 A; quick acting	
Reset Mode:	Automatic	Monitored manual or automatic	
External Device Monitoring:	N/C loop between Y1 and Y2	N/C loop between X1 and X2	
Mechanical			
Mounting:	35 mm (1.38 in.) DIN rail	35 mm (1.38 in.) DIN rail	
Case Material:	Polycarbonate	Polycarbonate	
Max Wire Size:	2 x 2.5 mm ² (12 AWG)	1 x 2.5 mm stranded, 1 x 4 mm solid	
Weight:	240 g (8.5 oz.)	CM-S41 — 575 g (20.3 oz.)	
		CM-S21 — 183 g (6.5 oz.)	
		CM-SE — 135 g (4.8 oz.)	
Color:	Gray	Red	
Indication:	U: Green = On	Power = Red	
	Outputs Open: Red = On	Outputs Closed: Green = On	
	Outputs Closed: Green = On	Outputs Open: No Light = Off	
	D11, D12, D21, D22: Green = Gate closed	Gate Closed: Yellow = On	
	D31, D32, D41, D42: Red = Gate open	Gate Open: No Light = Off	
Mechanical Life:	30 x 10 ⁶	10 x 10 ⁶	
Environmental			
Protection:	IP40 (NEMA 1)	Housing IP40, Terminals IP20	
Operating Temperature:	0 to 50°C (32 to 122°F)	10 to 55°C (50 to 131°F)	
Humidity:	95% RH at 55°C (131°F)	85% max	
Compliance			
Standards: EN292, EN60204-1, EN954-1,	EN1088, EN60947-5-3, EN947-5-3, EN50081, EN5008	82, EN61000-6-2	
Approvals/Listings: CE marked for all app	licable directives, UL and C-UL, TUV		
Safety Category: Cat 3 per EN954-1 (inter	nal operation)		
Considerations are cubicat to change without no			

Specifications are subject to change without notice.

Note: The safety contacts of the Omron STI switches are described as normally closed (N/C) i.e., with the guard closed, actuator in place, and the machine able to be started.







■ Switch Specifications

Electrical	CM-S1, CM-S2, CM-S3	CM-S221	CM-S11	CM-S31	
Safety Contacts:	1 N/C + 1 N/O	2 N/C + 1 N/O	Current Sensing Circuit	Current Sensing Circuit	
N/C Operating Distance:	CM-S1 —	On = 7 mm; Off = 12 mm	On = 5-7 mm; Off = 8-12 m	On = 5-7 mm; Off = 8-12 mm	
	On = 3 mm; Off = 8 mm				
	CM-S2 and CM-S3 —				
	On = 6 mm; Off = 13 mm				
Minimum Gap:		1 mm	1 mm	1 mm	
Max Switched Current/Voltage:	500 mA / 24 V	300 mA / 24 V			
Mechanical					
Mounting:	2 x M4 screws supplied				
Case Material:	Glass filled SPS	ABS	ABS	316 stainless steel	
Max Wire Size:	Pre-wired cable to 5 m	Pre-wired cable to 5 m	Pre-wired cable	Pre-wired cable	
			various lengths	various lengths	
Weight:	230 g (8.1 oz.)	230 g (8.1 oz.)	207 g (7.3 oz.)	265 g (9.3 oz.)	
Color:	Red	Red	Red	Stainless	
Mechanical Life:	100 x 10 ⁶	10 x 10 ⁶			
Environmental					
Protection:	IP67 (NEMA 6)	IP67 (NEMA 6)	IP67 (NEMA 6)	IP67 (NEMA 6)	
Operating Temperature:	-20 to 60°C (-4 to 140°F)	-10 to 55°C (14 to 131°F)	10 to 55°C (50 to 131°F)	10 to 55°C (50 to 131°F)	
Humidity:	95% RH at 55°C (131°F)				
Compliance					
Standards: EN292, EN60204-1, EN954-1, EN1088, EN60947-5-3, EN947-5-3, EN50081, EN50082, EN61000-6-2					
Approvals/Listings: CE marked for all applicable directives, UL and C-UL, TUV (TUV pending for CM-S221)					

Specifications are subject to change without notice.

Note: The safety contacts of the Omron STI switches are described as normally closed (N/C) i.e., with the guard closed, actuator in place, and the machine able to be started.




Go to the Engineering Guide

For in-depth information on safety standards and use.



For More Guarding Products











■ Dimensions — mm/in.


Control Units









CM-S41






CM-S21/SE



Canada Tel. 1/866/986-6766











■ Dimensions — mm/in. (continued)


Switches














N Se

See Section N for safeguarding cutting and turning machines







Ordering

Model	Contacts	Wiring Entry	Part No.
CONTROL UNITS			
CM-S4 (24 VAC/DC) (for S1, S2, S3 Switches Only)			44536-0040
CM-S41-24 (24 VAC/DC) (for S11, S31 Solid-State Switches Only)			44536-0140
CM-S41-110 (110 VAC) (for S11, S31 Solid-State Switches Only)			44536-0141
CM-S21-24 (24 VAC/DC) (for S11, S31 Solid-State Switches Only)			44536-0120
CM-SE-24 (24 VAC/DC) (for S11, S31 Solid-State Switches Only)			44536-0170
PLASTIC CASE SWITCHES			
Model 1			
CM-S1PC3	1 N/O + 1 N/C	3 m cable	44536-0100
CM-S1PC5	1 N/O + 1 N/C	5 m cable	44536-0105
CM-S11PC3	Current Sensing Circuit	3 m cable	44536-1100
CM-S11PC5	Current Sensing Circuit	5 m cable	44536-1105
CM-S11PC10	Current Sensing Circuit	10 m cable	44536-1110
CM-S11PCC5	Current Sensing Circuit	Connector + 5 m cable	44536-1159
Model 2			
CM-S2PC3	1 N/O + 1 N/C	3 m cable	44536-0200
CM-S2PC5	1 N/O + 1 N/C	5 m cable	44536-0205
CM-S221PC5 (not compatible with	2 N/C + 1 N/O	5 m cable	44536-0221
Legacy Relays or SR203M/AM, SR208AD or SR209AD)			
Model 3			
CM-S3PC3	1 N/O + 1 N/C	3 m cable	44536-0300
CM-S3PC5	1 N/O + 1 N/C	5 m cable	44536-0305
STAINLESS CASE SWITCHES			
Model 1			
CM-S31SC3	Current Sensing Circuit	3 m cable	44536-3100
CM-S31SC5	Current Sensing Circuit	5 m cable	44536-3105
CM-S31SCC5	Current Sensing Circuit	Connector + 5 m cable	44536-3159
Replacement Actuator for CM-S1, Red ABS Plastic			44536-0710
Replacement Actuator for CM-S2, Red ABS Plastic			44536-0720
Replacement Actuator for CM-S221, Red ABS Plastic			44536-0721
Replacement Actuator for CM-S3, Red ABS Plastic			44536-0730
Replacement Actuator for CM-S11, Red ABS Plastic			44536-0711
Replacement Actuator for CM-S31, Stainless Steel			44536-0731
Mounting Bracket for CM-S3			44536-0800
Accessories (see page G238)			
- New product	<u> </u>		

= New product



Universal Mounting Brackets can be used with this product. See page G241 for details.







Canada Tel. 1/866/986-6766