Safety Relay Unit

The G9SA Series Offers a Complete Line-up of Compact Units.

- Four kinds of 45-mm wide Units are available: A 3-pole model, a 5-pole model, and models with 3 poles and 2 OFF-delay poles, as well as a Two-hand Controller. Also available are 17.5-mm wide Expansion Units with 3 poles and 3 OFF-delay poles.
- Simple expansion connection.
- OFF-delay models have 15-step OFF-delay settings.
- Conforms to EN standards. (BG approval)
- Approved by UL and CSA.
- Both DIN track mounting and screw mounting are possible.

Ordering Information

Emergency-stop Units

Main contacts	Auxiliary contact	Number of input channels	Rated voltage	Model	Category
3PST-NO	SPST-NC	1 channel or 2 channels possible	24 VAC/VDC	G9SA-301	4
			100 to 240 VAC		
5PST-NO			24 VAC/VDC	G9SA-501	Ī
			100 to 240 VAC		

Emergency-stop OFF-delay Units

Main contacts	OFF-delay contacts	Auxiliary contact	Number of input channels	OFF-delay time	Rated voltage	Model	Category
3PST-NO	DPST-NO	SPST-NC	1 channel or 2	7.5 s	24 VAC/VDC	G9SA-321-T075	Main contacts:
			channels		100 to 240 VAC	4	1 OFE dolov
	possible	possible	15 s	24 VAC/VDC	G9SA-321-T15	contacts:	
					100 to 240 VAC		3
				30 s	24 VAC/VDC	G9SA-321-T30	
					100 to 240 VAC	1	

Note: The following 15-step OFF-delay time settings are available:

T075: 0.5, 1, 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7, and 7.5 s

T15: 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, and 15 s

T30: 2, 4, 6, 8, 10, 12, 14, 16, 18, 20, 22, 24, 26, 28, and 30 s

Two-hand Controller

Main contacts	Auxiliary contact	Number of input channels	Rated voltage	Model	Category
3PST-NO	SPST-NC	2 channels	24 VAC/VDC	G9SA-TH301	4
			100 to 240 VAC		

Expansion Unit

The Expansion Unit connects to a G9SA-301, G9SA-501, G9SA-321, or G9SA-TH301.

Main contacts	Auxiliary contact	Model	Category
3PST-NO	SPST-NC	G9SA-EX301	4



Expansion Units with OFF-delay Outputs

The Expansion Unit connects to a G9SA-301, G9SA-501, G9SA-321, or G9SA-TH301.

Main contact form	Auxiliary contact	OFF-delay time	Model	Category
3PST-NO	SPST-NC	7.5 s	G9SA-EX031-T075	3
		15 s	G9SA-EX031-T15	
		30 s	G9SA-EX031-T30	

Note: The following 15-step OFF-delay time settings are available:

T075: 0.5, 1, 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7, and 7.5 s

T15: 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, and 15 s

T30: 2, 4, 6, 8, 10, 12, 14, 16, 18, 20, 22, 24, 26, 28, and 30 s

Model Number Structure

Model Number Legend



- 1. Function
 - None: Emergency stop
 - EX: Expansion Unit
 - TH: Two-hand Controller
- 2. Contact Configuration (Safety Output)
 - 0: None
 - 3: 3PST-NO
 - 5: 5PST-NO
- 3. Contact Configuration (OFF-delay Output)
 - 0: None
 - 2: DPST-NO
 - 3: 3PST-NO
- 4. Contact Configuration (Auxiliary Output)
 - 0: None
 - 1: SPST-NC
- 5. Input Configuration (for G9SA-301/501/321)
 - None: 1-channel or 2-channel input possible
- 6. OFF-delay Time (Max. setting time)
 - None: No OFF-delay
 - T075: 7.5 seconds
 - T15: 15 seconds
 - T30: 30 seconds

Specifications

Ratings

Power Input

Item	G9SA-301/TH301	G9SA-501	G9SA-321-T	
Power supply voltage	24 VAC/VDC:24 VAC, 50/60 Hz, or 24 VDC 100 to 240 VAC:100 to 240 VAC, 50/60 Hz			
Operating voltage range	Operating voltage range 85% to 110% of rated power supply voltage			
Power consumption (See note.)	24 VAC/VDC: 1.8 VA/1.7 W max. 100 to 240 VAC: 9 VA max.	24 VAC/VDC: 2.8 VA/2.6 W max. 100 to 240 VAC: 11 VA max.	24 VAC/VDC: 3.5 VA/3.3 W max. 100 to 240 VAC: 12.5 VA max.	

Note: When an Expansion Unit is connected, the power consumption is increased by 2 VA/2 W max.

Inputs

Item	G9SA-301/321-T□/TH301	G9SA-501
Input current (See note.)	40 mA max.	60 mA max.

Note: When an Expansion Unit is connected, the input current is increased by 30 mA max.

Contacts

Item	G9SA-301/501/321-T□/TH301/EX301/EX031-T□	
	Resistive load	
Rated load	250 VAC, 5 A 30 VDC, 5 A	
Rated carry current	5 A	

■ Characteristics

ltem		G9SA-301/TH301	G9SA-501/321-T	G9SA-EX301/EX031-T		
Contact resistance (see note 1)		100 mΩ				
Operating time (see note 2)		30 ms max. (not including b	ounce time)			
Response time	e (see note 3)	10 ms max. (not including b	ounce time)			
Insulation resi	stance (see note 4)	100 MΩ min. (at 500 VDC)				
Dielectric	Between different outputs	2,500 VAC, 50/60 Hz for 1 m	nin			
strength	Between inputs and outputs					
	Between power inputs and outputs					
	Between power inputs and other inputs (only for 100 to 240-V models)					
Vibration resis	tance	10 to 55 to 10 Hz, 0.375-mm single amplitude (0.75-mm double amplitude)				
Shock	Destruction	300 m/s²				
resistance	Malfunction	100 m/s ²				
Durability	Mechanical	5,000,000 operations min. (at approx. 7,200 operations/hr)				
(see note 5)	Electrical	100,000 operations min. (at approx. 1,800 operations/hr)				
Minimum perm	nissible load (reference value)	5 VDC, 1 mA				
Ambient operating temperature		-25°C to 55°C (with no icing or condensation)				
Ambient operating humidity		35% to 85%				
Terminal tightening torque		0.98 N·m				
Weight (see note 6)		Approx. 210 g	Approx. 270 g	Approx. 130 g		

Note: 1. The contact resistance was measured with 1 A at 5 VDC using the voltage-drop method.

2. Includes bounce time.

4. The insulation resistance was measured with 500 VDC at the same places that the dielectric strength was checked.

^{3.} The response time is the time it takes for the main contact to open after the input is turned OFF.

^{5.} The durability is for an ambient temperature of 15°C to 35°C and an ambient humidity of 25% to 75%.

^{6.} Weight shown is for 24-VAC/VDC type. For 100 to 240-VAC type, add approximately 20 g.

G9SA-301 (100 to 240 VAC) with 2-channel Limit Switch Input/Auto-reset



<u>G9SA-301 (24 VAC/VDC) with 2-channel Emergency Stop Switch Input/Manual</u> Reset



Timing Chart Emergency stop switch S1 Reset switch S2 K1 and K2 (NC) K1 and K2 (NO) KM1 and KM2 (NC) KM1 and KM2 (NO) PC input PC output KM3 S1: Emergency stop switch with direct opening mechanism (A165E or A22E) ⊖ S2 Reset switch KM1 and KM2: Magnetic Contactor KM3: G3J Solid-state Contactor (G3J) M٠ 3-phase motor

M: 3-phase motor Note: This circuit achieves EN954-1 Safety Category 4. Safety Networks and Application Controllers

G9SA-321-T (24 VAC/VDC) with 2-channel Limit Switch Input/Manual Reset



ty Networks Application

<u>G9SA-321-T</u> (24 VAC/VDC) + G9SA-EX031-T with 2-channel Limit Switch Input/ Manual Reset



<u>G9SA-501 (24 VAC/VDC) and G9SA-EX301 with 2-channel Limit Switch Input/</u> Manual Reset



y Networks

Dimensions

Note: All units are in millimeters unless otherwise indicated. The diagrams are drawn in perspective.



3: Do not remove unless an Expansion Unit is being used.

ion G9SA



Installation

Internal Connections

G9SA-301 (24 VAC/VDC)



G9SA-501 (24 VAC/VDC)



G9SA-321-T (24 VAC/VDC)



G9SA-TH301 (24 VAC/VDC)



(See note 2.)



G9SA-EX031-T





G9SA-501 (100 to 240 VAC)



G9SA-321-T (100 to 240 VAC)



G9SA-TH301 (100 to 240 VAC)



- Note: 1. Use terminals A and B to switch reset mode. A to B open: Manual reset
 - A to B closed: Auto-reset
 - 2. Use terminals C and D to switch input conditions.
 - C to D open: DPDT input.
 - C to D closed: DPST-NC input. (Make sure T11 and T21 are open.)
 - Use terminal T23 with + common 2-channel input. When using T23, make sure that T21 and T22 are open. For 1-channel input, make sure T12 and T23 are closed.
 - 4. With 100 to 240-VAC type, be sure to connect PE to a protective ground. With 24-VAC/VDC type, if the power supply is not connected to a protective ground, be sure to connect PE to a protective ground.
 - 5. With 24-VAC/VDC type, the power supply terminals A1 and A2 have polarities. A2 is the negative pole.

Safety Precautions

Turn OFF the G9SA before wiring the G9SA. Do not touch the terminals of the G9SA while the power is turned ON, because the terminals are charged and may cause an electric shock.



Precautions for Correct Use

Installation

The G9SA can be installed in any direction.

Wiring

Use the following to wire the G9SA.

Stranded wire: 0.75 to 1.5 mm² Solid wire: 1.0 to 1.5 mm²

Tighten each screw to a torque of 0.78 to 1.18 N·m, or the G9SA may malfunction or generate heat.

External inputs connected to T11 and T12 or T21 and T22 of the G9SA-301 must be no-voltage contact inputs.

PE is a ground terminal.

When a machine is grounded at the positive, the PE terminal should not be grounded.

Connector Cover

Do not remove the connector cover of the G9SA-301, G9SA-501, G9SA-321-T \Box , or G9SA-TH301 unless an Expansion Unit is being used.

Safety Networks and Application Controllers

G9SA

Mounting Expansion Units

Turn OFF the G9SA before connecting the Expansion Unit.

When an Expansion Unit is being used, remove the connector cover from the G9SA Safety Relay Unit (G9SA-301, G9SA-501, G9SA-321□, or G9SA-TH301) and insert the connector of the Expansion Unit's connector cable.

Mounting Multiple Units

When mounting multiple Units close to each other, the rated current will be 3 A. Do not apply a current higher than 3 A.

Connecting Inputs

If using multiple G9SA models, inputs cannot be made using the same switch. This is also true for other input terminals.



Earth Shorts

A positive thermistor is built into the G9SA circuits, so you can detect earth short breakdowns and breakdown shorts between channel 1 and channel 2. If the short breakdown is canceled, reset is automatic.

Applicable Safety Category (EN954-1)

G9SA-series Relays meet the requirements of Safety Category 4 of the EN954-1 standards when they are used as shown in the examples provided by OMRON. The Relays may not meet the standards in some operating conditions. The OFF-delay output of models G9SA-321-T \Box and EX031-T \Box , however, conform to Safety Category 3.

The applicable safety category is determined from the whole safety control system. Make sure that the whole safety control system meets EN954-1 requirements.

Approved Standards

The G9SA-301/501/321T \Box /TH301/EX301/EX031-T \Box conform to the following standards.

- EN standards, certified by BG: EN954-1 EN60204-1 EN574 (G9SA-TH301 only)
- Conformance to EMC (Electromagnetic Compatibility) Certified by TÜV Product Service: G9SA (-TH301) 24 V AC/DC G9SA-EX301/EX031-T

Certified by TÜV Rheinland: EMI (Emission): EMS (Immunity): G9SA-EX301/EX031-T□ G9SA (-TH301) 100-240 V AC EN55011 Group 1 Class A EN61000-6-2

- UL standards: UL508 (Industrial Control Equipment)
- CSA standards: CSA C22.2 No. 14 (Industrial Control Equipment)