



PRODUCT DATA SHEET

Controlled Document - Engineering Drive

1530 Shields Drive
Waukegan, IL 60085
Toll-Free (800) 323-9355
Fax: (847) 689-1192

PART NUMBER: 51016
DESCRIPTION: 10 AWG STRANDED TYPE THHN/THWN INSULATED WIRE
CONSTRUCTION: This cable consists of one bare copper conductor with integral insulation and jacket.
APPROVALS: UL Standard 83 and Subject 758
APPLICATION: Insulated Wire, Appliance Wiring Material, Canada T90-Nylon, Canada TWN75

Construction Parameters:

Conductor	10 AWG Bare Copper
Stranding	19/.0234"
Insulation Material	PVC/Nylon
Insulation Thickness	0.021" Nom.
Nylon Insulation Thickness	0.005" Nom.
Insulated Conductor Diameter	0.164" Nom.
Approximate Cable Weight	39.1 Lbs/1M' Nom.

Electrical & Environmental Properties:

Temperature Rating	-20°C to 105°C
Operating Voltage	600 V RMS Max.
DC Resistance per Conductor @ 20°C	0.99 Ohms/1M' Nom.

Insulation/Jacket Color Varies (Consult factory for availability)

Legend (Surface Ink Print) CCI TRIANGLE 10 AWG (5.26mm²) THHN OR THWN E101736 (UL) 600V OR AWM STYLE 1317 & 1409 & 1453 GASOLINE & OIL RESISTANT I -- C(UL) T90 NYLON OR TWN75 FT1

This product complies with European Directive 2002/95/EC (RoHS)
On special orders, the customer will accept all factory lengths and +/- 10 percent of total order requested.
Wire is packaged on standard metal or wooden reels depending on the putup - consult factory.

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of products(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman Cable disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.

Customer Name _____
Customer Approval _____

Specification Issue Date: March 1, 2010