

T2008 Small Tongue-Operated Safety Interlock Switch

- Small size—these switches are ideal for guarding applications with space restrictions. Fits on 1 inch square tubing.
- NEMA 6 (IP67) enclosure enables these switches to withstand water washdown cleaning.
- Rotatable head gives eight possible actuator entry points for versatile installation. A blanking plug is supplied for the unused entry.

- Long life—these switches, with their stainless steel actuators, are designed for a minimum of one million actuations.
- Available with two contact poles. Contact configurations of 1 N/O and 1 N/C or 2 N/C are available to meet requirements of Dual Channel Safety Monitoring.
- An optional stainless steel guide is available for demanding applications.



Conforms to EN1088, EN292, EN60947-5-1, EN60204-1 UL and C-UL listed

Actual Size





Go to the Engineering Guide For in-depth information on

For in-depth information on safety standards and use.



For More Guarding Products

See Section N for safeguarding cutting and turning machines








Head Position 1

Head Position 2

Head Position 3

n 3 Head Position 4







Optional Slide Bolts

- Allows easy installation of switch on machine guards
- Actuator included (order switch separately)
- Integral handle included
- Metal construction is suitable for demanding applications
- Yellow color for easy recognition



Contact Arrangements





Optional stainless steel alignment guide aids actuator entry and is easily installed.



Optional SLD Series

Optional switch locking devices are available. See accessories section for details.








Universal Mounting Brackets can be used with this product. See page G241 for details.




Applications

Typical applications are on sliding guard doors or swinging guard doors.





For a full explanation of the circuit operating principle and fault detection, see "Common Circuit Examples" in the Engineering Section of this catalog.






Go to the Engineering Guide

For in-depth information on safety standards and use.



For More Guarding Products







■ Specifications


<u> </u>	N/O + 1 N/C, 2 N/C		
ety Contacts: 1 N	1 N/C positive break, 2 N/C positive break		
itching Ability			
AC: 23	230 V, 4 A		
DC : 24	24 V, 4 A		
ntact Material: Silv	Silver alloy, gold flashed		
ciliary Contacts: 1 M	1 N/O (T2008-11 models only)		
nimum Switching Voltage: 12	12 V at 10 mA		
nimum Switching Current: 1 r	1 mA at 24 V		
nical			
unting: An	Any position		
unting Hardware: 2 x	2 x M4 screws (not supplied)		
Operating Radius: 15	150 to 200 mm based upon orientation of actuator to switch		
ak Contact Min Force: 6 N	6 N (0.23 lb.)		
x Actuation Speed: 20	20 m/min.		
x Actuation Frequency: 70	7000 cycles/hour		
e Material: Gla	Glass-fibre reinforced thermoplastic		
uator Material: Sta	Stainless steel		
ing Entry: 1 x	1 x M16		
ight: 55	55 g (1.8 oz.)		
or: Bla	Black with red lid		
chanical Life: 1 x	1 x 10 ⁶ minimum		
nmental			
tection: IP6	IP67 (NEMA 6)		
erating Temperature: -20	-20 to 80°C (-4 to 176°F)		
aning: Wa	Water washdown		
iance			
ndards: EN	EN1088, EN292, EN60947-5-1, EN60204-1		
orovals/Listings: CE	CE marked for all applicable directives, UL and C-UL (BG pending)		

Specifications are subject to change without notice.

Note: The safety contacts of the Omron STI switches are described as normally closed (N/C)—i.e., with the guard closed, actuator in place, and the machine able to be started.



■ Dimensions — mm/in.





For More Guarding Products

See Section N for safeguarding cutting and turning machines





Ordering

T2008 90-DEGREE ACTUATOR	Contacts	Wiring Entry	Part No.
T2008-11SM	1 N/C + 1 N/O	1 x M16 + NPT adapter	44540-0010
T2008-02SM	2 N/C	1 x M16 + NPT adapter	44540-0020
T2008 FLAT ACTUATOR			
T2008-11TM	1 N/C + 1 N/O	1 x M16 + NPT adapter	44540-0110
T2008-02TM	2 N/C	1 x M16 + NPT adapter	44540-0120
T2008 FLAT ACTUATOR WITH RUBBER BUSHING			
T2008-11TRM	1 N/C + 1 N/O	1 x M16 + NPT adapter	44540-0210
T2008-02TRM	2 N/C	1 x M16 + NPT adapter	44540-0220
T2008 SWITCH ONLY (no actuators and no adapt	ers included)		
T2008-11	1 N/C + 1 N/O	1 x M16	44540-2010
T2008-02	2 N/C	1 x M16	44540-2020
ACCESSORIES			
Spare Actuators			
SA40-S00 90-degree actuator			44540-0700
SA40-T10 flat actuator			44540-0710
SA40-TR20 flat actuator with rubber bushings			44540-0720
Stainless Steel Guide			
SM40-SG50 stainless steel guide			44540-0750
Slide Bolt			
SB40-M00 slide bolt left or right hand door with bracket			44540-8000
Mounting Bracket			
SB40-M10 right angle bracket only for mounting T2008/T2011 switches			44540-8010
Adapter			
SC12-M16A00 M16 to 1/2 in. NPT adapter			44512-0300



Universal Mounting Brackets can be used with this product. See page G241 for details.

