Safety Relay Unit


G9SA

 Four kinds of 45-mm wide Units are available:
 A 3-safety contact model, a 5-safety contact model, and models with 3 safety contacts and 2 OFF-delay safety contacts.

Also available are 17.5-mm wide Expansion Units with 3 safety contacts and 3 OFF-delay safety contacts

- Two hand controller (III C, EN 574)
- Simple expansion connection.
- OFF-delay models have 15-step OFF-delay settings.
- Conforms to EN standards. (BG approval)
- Approved by UL and CSA.
- Both DIN track mounting and screw mounting are possible.

The G9SA Series Offers a Complete Line-up of Compact Units.



Ordering Information

Emergency-stop Units

Main contacts	Auxiliary contact	Number of input channels	Rated voltage	Model	Category
3PST-NO	SPST-NC	1 channel or 2 channels possible	24 VAC/VDC	G9SA-301	4
3F31-NO	3531-110		100 to 240 VAC		
5PST-NO SPST-NC		1 channel or 2 channels possible	24 VAC/VDC	G9SA-501	7
5P51-NO	SPS1-NC	T charmer of 2 charmers possible	100 to 240 VAC	G95A-501	

Emergency-stop OFF-delay Units

Main contacts	OFF-delay contacts	Auxiliary contact	Number of input channels	OFF-delay time	Rated voltage	Model	Category		
				7.5 s	24 VAC/VDC	G9SA-321-T075	4		
3PST-NO	DPST-NO SPST-NC		1 channel or 2 channels possible	7.5 \$	100 to 240 VAC	G93A-321-1075			
		CDCT NC		15.0	24 VAC/VDC	G9SA-321-T15			
						15 s	100 to 240 VAC	G95A-321-115	contacts:
				30 s	24 VAC/VDC	G9SA-321-T30	3		
				30.5	100 to 240 VAC				

Note: The following 15-step OFF-delay time settings are available: T075: 0.5, 1, 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7, and 7.5 s T15: 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, and 15 s T30: 2, 4, 6, 8, 10, 12, 14, 16, 18, 20, 22, 24, 26, 28, and 30 s

Two-hand Controller

Main contacts	Auxiliary contact	Number of input channels	Rated voltage	Model	Category
3PST-NO	SPST-NC	2 abannala	24 VAC/VDC	G9SA-TH301	4 (IIIc, EN574)
		2 channels	100 to 240 VAC		

Expansion Unit

The Expansion Unit connects to a G9SA-301, G9SA-501, G9SA-321, or G9SA-TH301.

Main contacts	Auxiliary contact	Model	Category
3PST-NO	SPST-NC	G9SA-EX301	4

Expansion Units with OFF-delay Outputs


The Expansion Unit connects to a G9SA-301, G9SA-501, G9SA-321, or G9SA-TH301.

Main contact form	Auxiliary contact	OFF-delay time	Model	Category
		7.5 s	G9SA-EX031-T075	
3PST-NO	SPST-NC	15 s	G9SA-EX031-T15	3
		30 s	G9SA-EX031-T30	

Note: The following 15-step OFF-delay time settings are available:

T075: 0.5, 1, 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7, and 7.5 s T15: 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, and 15 s T30: 2, 4, 6, 8, 10, 12, 14, 16, 18, 20, 22, 24, 26, 28, and 30 s

Model Number Legend



1. Function

None: Emergency stop
EX: Expansion Unit
TH: Two-hand Controller

2. Contact Configuration (Safety Output)

0: None3: 3PST-NO5: 5PST-NO

3. Contact Configuration (OFF-delay Output)

0: None2: DPST-NO3: 3PST-NO

4. Contact Configuration (Auxiliary Output)

0: None 1: SPST-NC

5. Input Configuration (for G9SA-301/501/321)

None: 1-channel or 2-channel input possible

6. OFF-delay Time (Max. setting time)

None: No OFF-delay T075: 7.5 seconds T15: 15 seconds T30: 30 seconds

G9SA D-49

Specifications

Ratings

Power Input

Item	G9SA-301/TH301	G9SA-501	G9SA-321-T□		
Power supply voltage	24 VAC/VDC:24 VAC, 50/60 Hz, or 24 VDC 100 to 240 VAC:100 to 240 VAC, 50/60 Hz				
Operating voltage range	85% to 110% of rated power supply voltage				
Power consumption (See note.)	24 VAC/VDC: 1.8 VA/1.7 W max. 100 to 240 VAC: 9 VA max.	24 VAC/VDC: 2.8 VA/2.6 W max. 100 to 240 VAC: 11 VA max.	24 VAC/VDC: 3.5 VA/3.3 W max. 100 to 240 VAC: 12.5 VA max.		

Note: When an Expansion Unit is connected, the power consumption is increased by 2 VA/2 W max.

Inputs

Item	G9SA-301/321-T□/TH301	G9SA-501
Input current (See note.)	40 mA max.	60 mA max.

Note: When an Expansion Unit is connected, the input current is increased by 30 mA max.

Contacts

Item	G9SA-301/501/321-T□/TH301/EX301/EX031-T□	
пеш	Resistive load (cos φ =1)	
Rated load	250 VAC, 5 A	
Rated carry current	5 A	


Characteristics

Item		G9SA-301/TH301	G9SA-501/321-T□	G9SA-EX301/EX031-T		
Contact resist	ance (see note 1)	100 mΩ				
Operating time		30 ms max. (not including bounce time)				
Response time (see note 2)		10 ms max. (not including	bounce time)			
Insulation resistance (see note 3)		100 MΩ min. (at 500 VDC)				
	Between different outputs					
Dielectric	Between inputs and outputs					
strength	Between power inputs and outputs	2,500 VAC, 50/60 Hz for 1	min			
ou ongui	Between power inputs and other inputs (only for 100 to 240-V models)					
Vibration resis	stance	10 to 55 Hz, 0.75-mm double amplitude				
Shock	Destruction	300 m/s ²				
resistance Malfunction		100 m/s ²				
Durability	Mechanical	5,000,000 operations min. (at approx. 7,200 operations/hr)				
Durability	Electrical	100,000 operations min. (at approx. 1,800 operations/hr)				
Minimum pern	nissible load (reference value)	5 VDC, 1 mA				
Ambient temp	erature	Operating:-25°C to 55°C (with no icing or condensation) Storage:-25°C to 85°C (with no icing or condensation)				
Ambient humi	dity	Operating:35% to 85% Storage:35% to 85%				
Terminal tightening torque		0.98 N·m				
Weight (see note 4)		Approx. 210 g	Approx. 270 g	Approx. 130 g		
Approved star	ndards	EN954-1, EN60204-1, EN574 (-TH301), UL508, CSA C22.2 No. 14				
EMC		EMI: EN55011 group 1 class A EMS: EN50082-2 group 1				


- Note: 1. The contact resistance was measured with 1 A at 5 VDC using the voltage-drop method.
 - 2. The response time is the time it takes for the main contact to open after the input is turned OFF.
 - 3. The insulation resistance was measured with 500 VDC at the same places that the dielectric strength was checked.
 - 4. Weight shown is for 24-VAC/VDC type. For 100 to 240-VAC type, add approximately 20 g.

G9SA-301 (24 VAC/VDC) with 2-channel Limit Switch Input/Auto-reset

Application Examples




G9SA-301 (24 VAC/VDC) with 2-channel Limit Switch Input/Manual-reset




D-51 G9SA


G9SA-301 (100 to 240 VAC) with 2-channel Limit Switch Input/Auto-reset



G9SA-301 (24 VAC/VDC) with 2-channel Emergency Stop Switch Input/Manual-reset





G9SA-321-T□ (24 VAC/VDC) with 2-channel Limit Switch Input/Manual-reset



G9SA D-53


G9SA-321-T□ (24 VAC/VDC) + G9SA-EX031-T□ with 2-channel Limit Switch Input/Manual-reset






G9SA D-55

G9SA-TH301 (24 VDC) with 2-hand Inputs/Auto-reset



G9SA-501 (24 VAC/VDC) and G9SA-EX301 with 2-channel Limit Switch Input/Manual-reset



S1: Safety Limit Switch

with direct opening mechanism (D4D or D4B) (⇒


(D4D or D4B) (5) Limit switch Reset switch


S3: Reset switch
KM1 and KM2: Magnetic Contactor
M: 3-phase motor

Timing Chart

S2:

Limit switches S1 and S2
Reset switch S3
G9SA-501
K1, K2, K3 and K4 (NC)
G9SA-501
K1, K2, K3, and K4 (NO)
G9SA-EX301
K1 and K2 (NC)
G9SA-EX301
K1 and K2 (NO)
KM1 and KM2 (NO)
KM1 and KM2 (NO)
KM1 and KM2 (NO)






Note: This circuit achieves EN954-1 Safety Category 4.


G9SA

Note: All units are in millimeters unless otherwise indicated. The diagrams are drawn in perspective.




Installation

Internal Connections




(See note 3.) (See note 1.)


G9SA-501 (24 VAC/VDC)





G9SA-321-T□ (24 VAC/VDC)




G9SA-TH301 (24 VAC/VDC)









G9SA-301 (100 to 240 VAC)




G9SA-501 (100 to 240 VAC)



G9SA-321-T (100 to 240 VAC)



G9SA-TH301 (100 to 240 VAC)



Note: 1. Use terminals A and B to switch reset mode.

A to B open: Manual reset

A to B closed: Auto-reset

- 2. Use terminals C and D to switch input conditions. C to D open: DPDT input. C to D closed: DPST-NC input. (Make sure T11 and
 - T21 are open.)
- 3. Use terminal T23 with + common 2-channel input. When using T23, make sure that T21 and T22 are open. For 1-channel input, make sure T12 and T23 are
- 4. With 100 to 240-VAC type, be sure to connect PE to a protective ground. With 24-VAC/VDC type, if the power supply is not connected to a protective ground, be sure to connect PE to a protective ground.
- 5. With 24-VAC/VDC type, the power supply terminals A1 and A2 have polarities. A2 is the negative pole.

G9SA D-59

— ⚠ Caution

Do not touch the terminal area of the Relays or the socket terminal area (charged area) while power is ON. Electric shock will result.

Wiring

Turn OFF the G9SA before wiring the G9SA. Do not touch the terminals of the G9SA while the power is turned ON, because the terminals are charged and may cause an electric shock.

Use the following to wire the G9SA Stranded wire: 0.75 to 1.5 mm² Solid wire: 1.0 to 1.5 mm²

Tighten each screw to a torque of 0.78 to 1.18 N·m, or the G9SA may malfunction or generate heat.

External inputs connected to T11 and T12 or T21 and T22 of the G9SA-301 must be no-voltage contact inputs.

PE is a ground terminal.

When a machine is grounded at the positive, the PE terminal should not be grounded.

Mounting Expansion Units

Turn OFF the G9SA before connecting the Expansion Unit.

When an Expansion Unit is being used, remove the connector cover from the G9SA Safety Relay Unit (G9SA-301, G9SA-501, G9SA-321 \square , or G9SA-TH301) and insert the connector of the Expansion Unit's connector cable.

Applicable Safety Category (EN954-1)

G9SA-series Relays meet the requirements of Safety Category 4 of the EN954-1 standards when they are used as shown in the examples provided by OMRON. The Relays may not meet the standards in some operating conditions. The OFF-delay output of models G9SA-321-T□ and EX031-T□, however, conform to Safety Category 3.


The applicable safety category is determined from the whole safety control system. Make sure that the whole safety control system meets EN954-1 requirements.

Mounting Multiple Units

When mounting multiple Units close to each other, the rated current will be 3 A. Do not apply a current higher than 3 A.

Connecting Inputs

If using multiple G9SA models, inputs cannot be made using the same switch. This is also true for other input terminals.



Earth Short

A positive thermistor is built into the G9SA circuits, so you can detect earth short breakdowns and breakdown shorts between channel 1 and channel 2. If the short breakdown is canceled, reset is automatic.