






MALE END VIEW	FEMALE END VIEW	WIRING DIAGRAM	SPECIFICATIONS	
			CONTACT CARRIER MATERIAL	NYLON OR TPU
			MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW
			CONTACT MATERIAL/PLATING	BRASS/GOLD
			COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
			RATED CURRENT [A]	4.0 A
			RATED VOLTAGE [V]	250 VAC/300 VDC
			TEMPERATURE RATING	-40°C to +105°C (-40°F to +221°F)
			PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68



SOURCE DRAWING - FOR REFERENCE ONLY

<div>RELATED DOCUMENTS</div> <div>1. 2. 3. 4.</div>					<div>3RD ANGLE PROJECTION</div>		<div>THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</div>		<div><div>TURCK INC</div><div>High Technology Sensors and Automation Controls</div></div> <div>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com</div>					
					<div></div>									
					<div>MATERIAL</div>		<div>DRFT SWC</div>				<div>DATE 09/18/95</div>		<div>DESCRIPTION VB2-FSM 4.4/2FKM 4</div>	
							<div>DSGN</div>				<div>SCALE 1 = 1.0</div>			
<div>FINISH</div>					<div>ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY</div>		<div>UNIT OF MEASUREMENT MILLIMETER [INCH]</div>		<div>IDENTIFICATION NO. U0098</div>		<div>REV E</div>			
									<div>CONTACT TURCK FOR MORE INFORMATION</div>		<div>DO NOT SCALE THIS DRAWING</div>		<div>FILE: U0098</div>	
<div>E</div>		<div>DRAWING PROCESSED AS PART OF ECO 33971</div>		<div>CBM 04/07/11</div>		<div>33971</div>								
<div>REV</div>		<div>DESCRIPTION</div>		<div>BY</div>		<div>DATE</div>		<div>ECO NO.</div>						