PATLITE

■ LCE-U / 40mm



















The LCE-U Series is a silver-color body LED towers that is versatile and attractive.

SIZE:	40mm diameter
INPUT VOLTAGE OPTIONS:	AC/DC24V
FUNCTIONS	- Continuous only
AVAILABLE:	- Continuous, Flashing, Alarms
MOUNTING OPTIONS:	- Pole mount: with 300mm steel pole, SZ-012 angle bracket,
	2 nuts, 2 washers
	- Direct mount: includes 3 mounting nuts
BODY STYLE:	- Pre-assembled, pre-wired
	- Interchangeable and stackable after purchase
BODY COLOR:	Gray
TIERS:	1-5 modules can be stacked
MODULE COLORS:	Red / Amber / Green / Blue / Clear
ALARMS (FB STYLE	- Alarm 1: selectable, single-tone, intermittent (fast beep)
ONLY):	alarm, 85dB (at 1m)
	- Alarm 2: selectable, single tone, intermittent (slow beep)
	alarm, 85dB (at 1m)
RATINGS:	- CE
	- UL Component Recognition (US)
	- UL Component Recognition (Canada)
	- RoHS
PROTECTION:	- IP-65
	- Type 4 / 4X / 13 (indoor, direct-mount only)
CONTROL OPTIONS:	- Dry contact closure such as switches or relay contacts
	- Open-collector transistor (NPN or PNP for DC24V
	- Direct voltage control for DC24V, continuous and alarm
	functions only

PART NUMBER GUIDE



U : Silver body color




Mounting Dimensions

Mounting Hole 3 - \$\phi 4\$ 1200 Direction of Audible Alarm

Side-mount Bracket

(Supplied)



Specifications LCE-U

Input Voltage			Op	Options AC/DC24V								
			Rated	Rated Voltage AC/DC24V (50-60 Hz)								
			Operation	Operating Voltage					Rated Voltage + or - 10%			
Operating temperature Range				-25°C ~ +60°C								
Relative Humio		Less than 90%										
Flashing Cycle ("FB" styles only)				60 + or – 12 flashes per minute								
Alarm Sound Level ("FB" styles only)				Max: 85 + or – 4dB (at 1m) Min: 70 + or – 4dB (at 1m)								
Alarm Sound Description ("FB" styles only)				Intermittent, single-tone; Alarm 1: fast beep, Alarm 2: slow beep								
Mounting Location Options				Indoor use only								
Mounting Direction Options				Upright only								
Protection Rating				IP-65								
Vibration				19.6m/s ² (30Hz) (2 hours each: front-back, right-left, up-down)								
Insulation Resistance			More than	More than 1 Megohm between terminals and chassis at DC500V								
Withstand Volt	age (AC/DC24V)		AC500V a	AC500V applied between terminals and chassis for 1 minute without breaking insulation								
Luminous Intensity			Red	Red		r	Green		Blue	Blue		
(mcd = millicandela)		760mdc		830mc	d	1290mcd		210mcd	210mcd 400mcd			
Applicable Standards CE UL RoHS			EN60958-1: 1993									
		UL		UL Component Recognition per UL-508 (File No. E215660)								
		RoHS		RoHS Directive 2005/95/EC								
Power Consumption		Red	Amber	Greer	n Blue		Clear	Steady	Inrush	Steady	Inrush	
AC/DC24V	Current (mA @ 24V)	28	28	22	23		23	40	250	40	250	
	Watts	0.7	0.7	0.6	0.6		0.6	1.0		1.0		
Contact Capac	city (I _S = current capac	ity; V _S = with	stand voltage;	V _C = die	lectric break	down	voltage; IL	= leakage	current)			
· ·		<u>, </u>	Contact Capacity					Transistor Capacity (NPN and PNP)				
AC/DC24V	LED Light Module		$I_S >= 100 \text{mA}; V_S >= AC35 \text{V}$					$I_{C} >= 100 \text{mA}; \ V_{C} >= 35 \text{V}$				
	Alarm		$I_S >= 300 \text{mA}; V_S >= AC35 \text{V}$					$I_{C} >= 300 \text{mA}; \ V_{C} >= 35 \text{V}$				
	Power Supply		l _s :	$I_S >= 500 \text{mA}; V_S >= AC35 \text{V}$								
Leakage Current				I _L = 0.1mA or less								
Fuse (not included)				1A (250V)								