


Ultra-slim Photoelectric Sensor

The EX-10 series is one of the smallest sensors on the market today. The ultra small size allows for mounting in the smallest areas. The size is achieved by locating all of the electronics and controls in an in-line amplifier. A bright 2-color indicator on the sensor head allows for quick determination of the sensor state. The EX-10 series is also equipped with a 0.5ms response time for high-speed detection and an IP-67 rated housing for wash-down environments. The mounting options available include a front sensing type as well as a side sensing type. Each type has two, metal reinforced M3 mounting holes for stable sensor placement. All types are available as either Light ON or Dark ON and PNP or NPN.

Model Name	Model Pic	Туре	Output Operation	Output Configuration	Emitting Element	Max. Range (mm)	Max. Range (in)	
Sort 🔺 🔻		Sort 🔺 🔻	Sort 🔺 🔻	Sort 🔺 🔻	Sort 🔺 🔻	Sort 🔺 🔻	Sort 🔺 🔻	
EX-11A		Thrubeam Front Sensing	Light-ON	NPN	Red LED	150	5.9	
EX-11A-PN		Thrubeam Front Sensing	Light-ON	PNP	Red LED	150	5.9	
EX-11B		Thrubeam Front Sensing	Dark-ON	NPN	Red LED	150	5.9	
EX-11B-PN		Thrubeam Front Sensing	Dark-ON	PNP	Red LED	150	5.9	
EX-11EA		Thrubeam Side Sensing	Light-ON	NPN	Red LED	150	5.9	
EX-11EA-PN		Thrubeam Side Sensing	Light-ON	PNP	Red LED	150	5.9	
EX-11EB		Thrubeam Side Sensing	Dark-ON	NPN	Red LED	150	5.9	
EX-11EB-PN		Thrubeam Side Sensing	Dark-ON	PNP	Red LED	150	5.9	
EX-13A		Thrubeam Front Sensing	Light-ON	NPN	Red LED	500	19.7	
EX-13A-PN		Thrubeam Front Sensing	Light-ON	PNP	Red LED	500	19.7	
EX-13B		Thrubeam Front Sensing	Dark-ON	NPN	Red LED	500	19.7	
EX-13B-PN		Thrubeam Front Sensing	Dark-ON	PNP	Red LED	500	19.7	

EX-10

DIMENSIONS (Unit: mm in)



SPECIFICATIONS

		Thru-beam					Convergent reflective (Diffused beam type)	reflective Thru-beam • with operation mode switch on bifu						
		Туре	Front sensing	Side sensing	Front sensing	Side sensing	Front sensing	Front sensing	Front sensing	Side sensing	Front sensing	Side sensing		
	Model	Light-ON	EX-11A(-PN)	EX-11EA(-PN)	EX-13A(-PN)	EX-13EA(-PN)	EX-19A(-PN)	EX-14A(-PN)	EX-15	EX-15E	EX-17	EX-17E		
lte	em (Note 1)	Dark-ON	EX-11B(-PN)	EX-11EB(-PN)	EX-13B(-PN)	EX-13EB(-PN)	EX-19B(-PN)	EX-14B(-PN)	(Note 2)	(Note 2)	(Note 2)	(Note 2)		
Sensing range		150 mm 5.906 in		500 mm 19.685 in 1 m		1 m 3.281 ft	2 to 25 mm 0.079 to 0.984 in (Note 3) (Conv. point: 10 mm 0.394 in)	150 mm 5.906 in		500 mm 19.685 in				
Min. sensing object						¢0.1 mm ¢0.004 in copper wire (Setting distance: 10 mm 0.394 in)				nce between eceiver:				
Hysteresis							15 % or less of operation distance							
Repeatability (perpendicular to sensing axis)		0.05 mm 0.002 in or less					0.1 mm 0.004 in or less	0.05 mm 0.002 in or less						
Supply voltage						Ripple P-P 1	0 % or less							
Current consumption		'n	Emitter: 10 mA or less, Receiver: 15 mA or less 20						s 30 mA or less					
Output		<npn output="" type=""> NPN open-collector transistor • Maximum sink current: 50 mA • Applied voltage: 30 V DC or less (between output and • Residual voltage: 1 V or less (at 50 mA sink current) 0.4 V or less (at 16 mA sink current) <pnp output="" type=""> PNP open-collector transistor • Maximum source current: 50 mA • Applied voltage: 30 V DC or less (between output and • Residual voltage: 1 V or less (at 50 mA source current 0.4 V or less (at 16 mA source current 0.4 V or less (at 16 mA source current</pnp></npn>					t) d + V) nt)	NPN open-collector transistor • Maximum sink current: 100 mA • Applied voltage: 30 V DC or less (between output and 0 V) • Residual voltage: 1.5 V or less (at 100 mA sink current) 0.4 V or less (at 16 mA sink current)						
[Utilization cate	gory		DC-12 or DC-13										
	Short-circuit pro	otection	Incorporated											
Res	ponse time						0.5 ms	or less						
Operation indicator			Red LED (lights up when the output is ON)						Orange LED (lights up when the output is ON), located on the bifurcation					
Incio	dent beam indic	ator							Red LED (lig located on th		r light receive	d condition),		
Stability indicator			Green LED (lights up under stable light received condition or stable dark condition)						Green LED (lights up under stable light received condition or stable dark condition), located on the receiver					
-	Pollution degre	е	3 (Industrial environment)											
	Protection		IP67 (IEC)											
ance	Ambient tempe	rature	- 25 to + 55 °C - 13 to + 131 °F (No dew condensation or icing allowed), Storage: - 30 to + 70 °C - 22 to + 158 °F											
esist	Ambient humid	ity	35 to 85 % RH, Storage: 35 to 85 % RH											
tal re	Ambient illumin	ance	Sunlight: 10,000 ℓx at the light-receiving face, Incandescent light: 3,000 ℓx at the light-receiving face											
men	EMC		EN 50081-2, EN 50082-2, EN 60947-5-2											
Ambient humidity Ambient illuminance EMC Voltage withstandability Insulation resistance		indability	1,000 V AC for one min. between all supply terminals connected together and enclosure											
Ъ	Insulation resis	tance	20 M Ω , or more, with 250 V DC megger between all supply terminals connected together and enclosure											
	Vibration resist	ance	10 to 500 Hz frequency, 3 mm 0.118 in amplitude in X, Y and Z							Z directions for two hours each				
Shock resistance 500 m/s ² acceler						eleration (50 G approx.) in X, Y and Z directions for three times each								
Emitting element		Red LED (modulated)												
Material		Enclosure: Polyethylene terephthalate Lens: Polyalylate						Enclosure: Polyethylene terephthalate Lens: Polyalylate, Bifurcation: Polyalylate						
Cable (Note 4)			0.1 mm ² 3-core (thru-beam type emitter: 2-core) cabtyre cable, 2 m 6.562 ft long						0.2 mm² 3-core cabtyre cable, 2 m $6.562~{\rm ft}$ long (beyond bifurcation; from emitter / receiver to bifurcation: 0.5 m 1.640 ft long)					
Cable extension		Extension up to total 50 m 164.042 ft is possible with 0.3 mm ² , or m (thru-beam type: emitter and receiver).					more, cable	Extension up to total 100 m 328.084 ft is possible with 0.3 mm ² , or more, cable.						
Weight			Err	nitter: 20 g ap	prox., Receiv	/er: 20 g app	rox.	20 g approx.		55 g a	g approx.			
Accessories		Mounting screws: 1 set				Mounting screws: 1 set	Mounting so	crews: 1 set, A	djusting screw	driver: 1 pc.				

Notes: 1) Model Nos. having the suffix '-PN' are PNP output type.
2) Either Light-ON or Dark-ON can be selected by the operation mode switch (located on the bifurcation).
3) The sensing range of convergent reflective type sensor is specified for white non-glossy paper (50 × 50 mm 1.969 × 1.969 in) as the object.
4) The flexible cable type (model Nos. having suffix '-R') has a 0.1 mm² 3-core (thru-beam type emitter : 2-core) flexible cabtyre cable, 2 m 6.562 ft long.