

American Electrical, Inc.

456 Southlake Blvd,
Richmond, VA 23236

Phone: 804-379-2899 • **Fax:** 804-379-8935

Email: sales@americanelectrical.com • **Website:** www.americanelectrical.com

Item # TRAP22-10, Trap 22-10 Wire Ferrule Hand Crimping Tool



Trap 22-10 Wire Ferrule Hand Crimping Tool

Trapezoid Crimping with Ratchet, Front Entry, Universal Die
Range: 22-10 AWG (0.5-6.0 mm²) for Single Conductor Ferrules
20-14 AWG (0.5-2.5 mm²) for Twin Ferrules (Two Wires)
Length: 8.25 inches (209 mm)
Weight: 14.8 ounces (460 g)

SPECIFICATIONS

Range for Single Conductor Ferrules	22 - 10 AWG 0.5 - 6.0 mm ²
Range for Twin Ferrules	20 - 14 AWG 0.5 - 2.5 mm ²
Length	8.25 in 209 mm
Weight	14.8 oz 460 g

CERTIFICATIONS

Certifications	 RoHS (EU directive 2002/95/EC)
----------------	--
