

D series

high voltage reed relays 15kV, 50W











Very high isolation voltages, up to 15kV, are achieved through the use of high vacuum reed switches with either Rhodium or Tungsten contacts and make these relays suitable for high reliability applications such as cardiac defibrillators, test equipment and high voltage power supplies.

The Rhodium contacts have low contact resistance while the Tungsten contacts can switch higher voltages.

Printed Circuit Board (PCB) or Panel mount, via nylon studs, versions are available.

Connection options include PCB, solder turret tag, flying lead and Faston* style Spade Terminals.

Available as Form A (SPNO) or Form B (SPNC) contact configurations.

Contact	Units	Conditions	ΙΟΚΫ	FORM A	TUKV	I DKV FORM A			
Contact Materials			Rhodium	Tungsten	Rhodium	Tungsten	Τι	ingsten	
Isolation Across Contacts	kV	DC or AC peak	10	10	10	10 10		15	
Max. Switching Power	W		50	50 50		50 50		50	
Max. Switching Voltage	V	DC or AC peak	1000 7000		1000 7000		10000		
Max. Switching Current	А	DC or AC peak	3 2		3 2		2		
Max. Current Carry	А	DC or AC peak	4	3	4 3		2		
Capacitance Across Contacts	pF	Coil/Screen Grounded	<0.2	<0.2	<0.2 <0.2		<0.2		
Lifetime	Operations	Dry Switching	10 ⁹	109	10 ⁹	10 ⁹	109		
Lifetime	Operations	50W Switching	106	106	106	106	108		
Contact Resistance	mOhms	Maximum (Typical)	50 (15)	250 (100)	50 (15) 250 (100)		250 (100)		
Insulation Resistance	Ohms	Minimum (Typical)	10 ¹⁰ (10 ¹³)	10 ¹⁰ (10 ¹³)	10 ¹⁰ (10 ¹³) 10 ¹⁰ (10		10 ¹⁰ (10 ¹³)		
Coil at 20°C				12V 24V	5V 1	2V 24V	5V	12V	24V
Must Operate	٧	DC	3.7	9 20	3.7	9 20	3.7	9	20
Must Release	٧	DC	0.5	1.25 4	0.5 1	.25 4	0.5	1.25	4
Operate Time	ms	Diode Fitted	3.0	3.0 3.0	2.0 2	2.0 2.0	3.0	3.0	3.0
Release Time	ms	Diode Fitted	2.0	2.0 2.0	3.0 3	3.0 3.0	2.0	2.0	2.0
Resistance	Ohms		28	150 780	38 2	40 925	16	95	350
Construction									
Isolation Contact to Coil	kV	DC or AC peak	17		17		17		
Insulation Resistance Contact									
to All Other Terminals	Ohms	Minimum (Typical)	10 ¹⁰ (10 ¹³)		10 ¹⁰ (10 ¹³)		10 ¹⁰ (10 ¹³)		
Environmental									
Operating Temperature Range	°C		-20 to +70		-20 to +70		-20 to +70		
Weight Version		Standard	Pa	inel	Sp	Flying Lead			
Form A	gm	23		28	2	38			
Form B	gm	31		36	3	46			

- 15kV Isolation
- Low Contact Resistance
- High Power Switching
- PCB or Panel Mount
- Flying Lead, Solder and Faston* Style Spade **Terminal Options**

Contact	Units	Conditions	10kV Form A			10kV Form B			15kV Form A		
Contact Materials			Rhodium	Tunş	gsten	Rhodiun	n Tu	ngsten	Tungsten		
Isolation Across Contacts	kV	DC or AC peak	10	1	10	10		10	15		
Max. Switching Power	W		50	Ę	50	50 50		50			
Max. Switching Voltage	٧	DC or AC peak	1000	7(000	1000	7000		10000		
Max. Switching Current	А	DC or AC peak	3		2	3		2	2		
Max. Current Carry	А	DC or AC peak	4	3		4		3		2	
Capacitance Across Contacts	pF	Coil/Screen Grounded	<0.2	<	<0.2			<0.2	<0.2		
Lifetime	Operations	Dry Switching	10 ⁹	10 ⁹		10 ⁹		109	109		
Lifetime	Operations	50W Switching	106	1	106			106	108		
Contact Resistance	mOhms	Maximum (Typical)	50 (15)	250	(100)	50 (15) 250 (10		0 (100)	250 (100)		
Insulation Resistance	Ohms	Minimum (Typical)	10 ¹⁰ (10 ¹³) 10 ¹⁰	(1013)	10 ¹⁰ (10 ¹	¹³) 10 ¹	⁰ (10 ¹³)	10 ¹⁰ (10 ¹³))
Coil at 20°C				12V	24V	5V	12V	24V		12V	24V
Must Operate	٧	DC	3.7	9	20	3.7	9	20	3.7	9	20
Must Release	٧	DC	0.5	1.25	4	0.5	1.25	4	0.5	1.25	4
Operate Time	ms	Diode Fitted	3.0	3.0	3.0	2.0	2.0	2.0	3.0	3.0	3.0
Release Time	ms	Diode Fitted	2.0	2.0	2.0	3.0	3.0	3.0	2.0	2.0	2.0
Resistance	Ohms		28	150	780	38	240	925	16	95	350
Construction											
Isolation Contact to Coil	kV	DC or AC peak	17		17		17				
Insulation Resistance Contact											
to All Other Terminals	Ohms	Minimum (Typical)	10 ¹⁰ (10 ¹³)		1010 (1013)		10 ¹⁰ (10 ¹³)				
Environmental											
Operating Temperature Range	°C		-20 to +70		-20 to +70		-20 to +70				
Weight Version		Standard	Panel		Spade		Flying Lead				
Form A	gm	23	28			29			38		
FD		21	20		27			10			



D series high voltage reed relays 15kV, 50W



IS09001 Certified

USA

Sales & Tech Support(866) 258-5057 Email: sales@cynergy3.com Cynergy3 Components 2320 Paseo de las Americas, Suite 104 San Diego, CA 92154 EUROPE - UK

Telephone +44 (0) 1202 897969 Fax +44 (0) 1202 891918 Email:sales@cynergy3.com Cynergy3 Components Ltd. 7 Cobham Road Ferndown Industrial Estate Wimborne, Dorset BH21 7PE

ASIA - Thailand

Telephone +66 (0)2 665 2517 Fax +66 (0)2 665 2588 Cynergy 3 Components, Asia 18/8 Fico Place 12th Floor Soi Sukhumvit 21 (Asoke) Klongtoey Nua, Wattana Bangkok, Thailand 10110