

■ BOM Qty. (# of Pkgs.)

SE50P-CR0



- Provides continuous abrasion resistance for wires cables and tubing
 - Lightweight durable protection
 - Highly flexible open weave will not trap heat or humidity
 - Rated for use up to 257°F (125°C)
 - Allows for use with irregular shapes
 - Stock colors: Black gray and white

■ Part Number	SE50P-CR0
■ RoHS Compliancy Status	Compliant
■ Part Description	Braided Expandable Sleeving provides continuous abrasion resistance for wires, cables and tubing. The highly
	flexible open weave will not trap heat or humidity.
■ Material	Polyethylene Terephthalate
■ Color	Black
■ CSA Certified	Yes
■ UL Recognized	E116868
■ Length (m)	30.5
 Flammability Rating 	UL94 HB
■ Inside Diameter (mm)	12.7
■ Length Per Reel (ft.)	100
■ Length Per Reel (m)	30.5
■ Nominal Diameter Range (In.)	.250 to .750
■ Nominal Diameter Range (mm)	6.4 to 19.1
■ Nominal I.D. (In.)	.50
■ Nominal I.D. (mm)	12.7
■ Pricing Description	Exp. Sleeving, .50" (12.7mm),Black
■ Temperature Range	-94°F to 257°F (-70°C to 125°C)
■ Min. Order UOM	RL
■ Min. Order Qty.	1