

BT1.5I-C

• • For indoor use

• Dome-top head features unique patented design with round, smooth edges

• Stainless steel locking barb provides consistent performance, reliability and infinite adjustability through entire bundle range

• High strength and low thread force

• Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation (Light-Heavy cross section ties have a straight tip)

 Part Number 	BT1.5I-C
 RoHS Compliancy Status 	Compliant
 Part Description 	Cable Tie with metal barb, 6.1", Intermediate cross section
 Product Type 	Cable Ties
 Material 	Nylon 6.6
 Color 	Natural
 CSA Certified 	Yes
 Mil. Std. Part Number 	MS3367-5-9
 UL Listed (File #E56854) 	Yes
 UL Recognized (File #E56854) 	Yes
■ Length (In.)	6.1
■ Length (mm)	155
■ Width (In.)	.141
■ Width (mm)	3.6
 CE Compliant 	Yes
 Cross Section 	Intermediate
 Head Height (In.) 	.185
 Head Height (mm) 	4.7
 Head Width (In.) 	.248
 Head Width (mm) 	6.3
 Locking Style 	Locking
 Material Flammability Rating 	UL 94V-2
 Max. Bundle Diameter (In.) 	1.50
 Max. Bundle Diameter (mm) 	38
 Max. Continuous Use Temperatur 	e 185°F (85°C)

 Min. Loop Tensile Strength (Lbs.) 	40
 Min. Loop Tensile Strength (N) 	178
 Pricing Description 	Cable Tie, Metal Barb, 6.1"L (155mm), Intermediate, Nylon, Natural
 Thickness (In.) 	.041
 Thickness (mm) 	1.0
■ Tool	GTS, GTSL, GS2B, PTS, PPTS, STS2
 Min. Order UOM 	PC
 Min. Order Qty. 	100

BOM Qty. (# of Pkgs.)

	THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.																				
	ļ	B±.01(.25)																			
	_ <u>r</u>																				
	T REF.																				
															- A±.01(.25)						
	D		<u>'</u>										V								
	4		<u> </u>										4								
	I												Ι								
		PANDUIT BUNDLE DIA. A B C D E											F MIN. LOOP CROSS WEIGHT TENSILE US. SECTION US: (100 pcs.)								
		PARI NU. MIN. (mm) MAX. (mm) in (mm) in (in (mm		_	(mm)	in (mm		(mm)			SECTION	(g)					
							.141 (3.6	.142 (3.6)		185 1.7)	.248 (6.3) (5.1 155)	40 (178)			.12 (56)				
						.141 (3.6	.142 (3.6)		185 1.7)	.248 (6.3		8.0 203)	40 (178)	INT	ERMEDIATE	.16 (72)					
				.03 (0.8)	3.00 (76)	.049 (1.2)	.141 (3.6	.142 (3.6)		185 1.7)	.248 (6.3		1.3 287)	40 (178)	INT	ERMEDIATE	.27 (121)				
		BT4I		4 I	.03 (0.8)	4.00 (102)	.049 (1.2)	.141 (3.6	.142 (3.6)		185 1.7)	.248 (6.3		4.3 363)	40 (178)	INT	ERMEDIATE	.35 (156)			
		BT2S BT3S		25	.06 (1.5)	2.00 (51)	.045 (1.2)	.185 (4.7			220 5.6)	.320 (8.1		3.0 203)	50 (222)	S	TANDARD	.25 (113)			
				35	.06 (1.5)	3.00 (76)	.052 (1.3)	.185 (4.7	.205	205 .220 .3 .2) (5.6) (8		.320 (8.1		2.0 305)	50 (222)	S	TANDARD	.40 (183)			
					.185 (4.7		.5	.220 .32 (5.6) (8.			15.1 50 384) (222)		S	TANDARD	.51 (230)						
DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS														rs							
															TINLEY PARK, IL	LINOIS					
															DOME - T	TOP E)P Barb Ty CABLE TIES				
																	BT SERĪ	1			
														DIM (,X	ESS OTHERWI ENSIONAL TO () ±.10(2.5 (X) ±.02(.5)	UNLESS OTHERWISE SPEC ALL DIMENSIONS ARE GIV IN INCHES, THIRD ANGLE	VEN				
														DRAWN BY MAT'L: SCALE							
9	5/2/06	Лаво		REMOVEL	D STRAIGH YLE COLUN	HT TIP R	EFERENCE	5 S	0037	9				DATE 6-24-93 NYLON 6.6 BT-00					Dwg 7 A		
REV	DATE	вγ	снк							сият	SUP		снк • о 	VL			SHT. 2 OF				