

CAGE/NCAGE Code: 3FNFO

CCR Certified

The Leader in Industrial Control & Data Acquisition

### **DP-660**





Dual Output Power Supply, 24V @ 2.5A & 5V @ 0.5A

**Product Pricing:** 

DP-660:





#### **Features**

DP-660 is a 65 watt, universal input switching mode power supply.

It is with 24V @ 2.5A & 5V @ 0.5A output options. DP-660 is intended for a powere device like a motor or solenoid application. The built in +5V 3T-regulator for DP-660 is for if there is a logical control circuit.

## **Specifications & Additional Information**

- Input voltage: 85VAC to 270VAC
- Input frequency: 47Hz to 63HzInrush current (Cold start):
- less than 30A at 115Vac less than 60A at 230Vac
- DC Outputs :
  - O +24V/2.5A
  - +5V/0.5A
- Efficiency: higher than 70% at rated load and 115Vac
- Holdup time: 16ms at rated load and 115Vac
- Over voltage protection : hiccup mode
- Short circuit protection : latch off
- Over voltage protection : latch off
- Environment:
  - Operating temperature : 0 to 50°C
  - O Cooling: free air convection
  - O Storage temperature : -40°C to 85°C
- Din Rail Mount



# **Embedded Control and Data Acquisition**

### **DP-660**



## Dual Output Power Supply, 24V @ 2.5A, 5V @0.5 A

It is with 24V/5V output options. DP-660 is intended for a power device like a motor or solenoid application. The built in +5V 3T-regulator of DP-660 is for the application which will have a logical control circuit.

## **Specifications**

- Input voltage: 85VAC to 270VAC
- Input frequency: 47Hz to 63Hz
- Inrush current (Cold start): less than 30A at 115Vac less than 60A at 230Vac
- DC Outputs :
  - o +24V/2.5A
  - o +5V/0.5A
- 65 watts, universal input switching mode power supply.
- Efficiency: higher than 70% at rated load and 115Vac
- Holdup time: 16ms at rated load and 115Vac
- Over voltage protection : hiccup mode
- Short circuit protection : latch off
- · Over voltage protection: latch off
- Environment:
  - Operating temperature : 0 to 50°C
  - Cooling : free air convection
  - Storage temperature : -40°C to 85°C
- Din Rail Mount