

World Leader in Network and Electrical Solutions

HOME | SOLUTIONS | RESOURCES | PRODUCTS | SERVICES | LEARNING

SEARCH

Current refinements (click **x** to remove)

Search Tips (7)

Printer Friendly

□ Region I USA □ Product Family I One-Hole, Single Barrel Lug □ Text Search: 'LAMA500-38-6Y'

Your search criteria matched only one product, shown below.

Joint Compounds




For Use with Stranded Aluminum or Copper Code Conductors

- · Made from high strength, extruded aluminum alloy to provide premium electrical and mechanical performance
- Tin-plated to inhibit corrosion
- Compact design saves space
- Wide wire range-taking capability minimizes inventory requirements
- Inspection window to visually assure full conductor insertion
- Plated steel or aluminum set screw provides high strength, durable electrical contact between conductor and connector
- UL Listed and CSA Certified for use up to 600 V and UL temperature rated 90°C

Part Number:	LAMA500-38-6Y
RoHS Compliancy Status:	Compliant
Note:	LAMA500-38-6Y replaces LAMA500-38-6
Part Description:	Aluminum, single barrel, one-hole tongue connector, type LAMA.
Product Type:	Mechanical Connectors - Lugs
CSA Certified:	Yes
UL Listed:	Yes
Height (In.):	1.50
Height (mm):	38.1
Length (In.):	2.75
Length (mm):	70.0
Stud Hole Size (In.):	3/8
Tongue Width (In.):	1.38
Aluminum or Copper Conductor Size Range:	#4 AWG – 500 kcmil
Hex Key Size (In.):	1/2
Tightening Torque (In-Lbs):	500
Tongue Length:	1.50
Tongue Thickness:	.31
Tongue Width (mm):	35.1
Min. Order UOM:	PC
Min. Order Qty.:	1
BOM Qty. (# of Pkgs.)	
Add to My Catalog	

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

- 1. U.L. LISTED PER 486B.
- 2. C.S.A. CERTIFIED EXCEPT LAMA800-58-6.
- 3. PART AND SCREWS ARE TIN PLATED ALUMINUM.
- 4. TO BE USED WITH COPPER OR ALUMINUM STRANDED WIRE.
- 5. MADE IN U.S.A.
- 6. THIS PART IS ROHS COMPLIANT.

ALUMINUM MECHANICAL CONNECTORS TYPE: LAMA

CAT. NO.	WIRE RANGE	WIRE STRIP	BOLT	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F	DIM G	INSTALLATION TORQUE	HEX
	COPPER/ALUMINUM	LENGIH IN. (mm)	SIZE IN.	IN.	IN.	IN.	IN.	IN.	IN.	IN.	in-lbs (N-m)	KEY
LAMA300-56-QY	300MCM-6AWG	1.00 (25.4)	5/16	. 44	2.00	1.00	.22	. 90	1.06	.56	2-6AWG-275 (31.1)	3/8
											300MCM-1AWG-375 (42.4)	
LAMA350-38-QY	350MCM-6AWG	1.12 (28.4)	3/8	.50	2.25	1.13	. 25	1.13	1.25	.63	2-6AWG-200 (22.6)	3/8
											350MCM-1AWG-375 (42.4)	
LAMA500-38-6Y	500MCM-4AWG	1.25 (31.8)	3/8	.62	2.75	1.25	. 31	1.38	1.50	. 88	500 (56.5)	1/2
LAMA600-38-6Y	600MCM-4AWG	1.25 (31.8)	3/8	.62	2.75	1.25	. 31	1.38	1.50	. 88	500 (56.5)	1/2
LAMA6005-38-6Y	600MCM-4AWG	1.31 (33.3)	3/8	.62	2.81	1.31	. 31	1.38	1.81	. 88	500 (56.5)	1/2
LAMA800-58-6Y	800-350MCM	1.63 (41.4)	5/8	. 88	3.38	1.63	. 38	1.63	1.94	. 88	600 (67.8)	9/16
LAMA1000-58-6Y	1000-500MCM	1.75 (44.5)	5/8	. 88	3.50	1.75	. 44	1.75	2.13	. 88	600 (67.8)	9/16

						CAD FILENAME/LAYE	C415	567_01			
							CORP TINLEY PARK, ILLII				
							LAMA SERIES 300 THRU 1000M			M	
							ALUMINUM MECHANICAL LUGS				
							DIMEN	S OTHERWISE SPECIFIED, ISIONAL TOLERANCES ARE:	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE GIVEN		
							(.X) ± (.XX) ±		INCHES, THIRD ANGLE PROJECTION		
01 3/06	JHNL	JLEM	REVISED ROHS NOTE	PC00334			DRAWN BY JHNU	MAT'L:	SCALE \\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \		
00 2/06	JHNL	JLEM	DRAWING RELEASED - ROHS COMPLIANT	PC00299			DATE 2/06	SEE NOTES	DRAWING NO.	DWG	
REV DATE	BY	СНК	DESCRIPTION	ECN	CUST	PM	CHK 'D		C41567	SIZE	