MODEL 260

Voltage Sensor

- Monitors for Over or Under Voltage
- LED status indicator
- Plug-in Mounting
- Automatic or Manual Reset
- 5 Year Unconditional Warranty

DESCRIPTION

The **Model 260 Voltage Sensor** is a single setpoint voltage sensor. Input voltages above the setpoint cause the output contacts to energize *(contacts 1 & 8 closed)*. Input voltages below the setpoint cause the output contacts to de-energize *(contacts 1 & 2 closed)*. The dead band between pull-in and drop-out is less than 2%.

The standard unit has a screwdriver, or fingertip adjustable setpoint range of approximately 35% of the maximum voltage. This device can also be provided with a factory calibrated trip point.

AC versions of the Model 260 Voltage Sensor are not frequency sensitive, and may be used in systems from 50Hz to 400 Hz. DC models are not polarity sensitive.

This device requires a standard 8-pin socket, such as Time Mark's Model 51X120.

ORDERING STANDARD MODELS:

AUTOMATIC RESET			
AC	DC		
AC260B-80-130	DC260B-20-24		
#AC260B-90-150	DC260B-30-46		
AC260B-160-250	DC260B-42-64		
AC260B-215-290	DC260B-60-92		
AC260B-380-480	DC260B-90-150		
#AC260B-400-560	DC260B-160-250		
	#DC260B-250-350		
MANUAL RESET			

MANUAL RESET			
AC	DC		
AC260BM-80-130	DC260BM-20-24		
#AC260BM-90-150	DC260BM-30-46		
AC260BM-160-250	DC260BM-42-64		
AC260BM-215-290	DC260BM-60-92		
AC260BM-380-480	DC260BM-90-150		
#AC260BM-400-560	DC260BM-160-250		
	#DC260BM-250-350		







on most models

SPECIFICATIONS

MODEL	260		
Input voltage	see Ordering Info tables		
Transient protection	2500 VRMS for 10 msecs		
Polarity protection	not required		
Supply current	10mA max.		
Setpoint stability	± 1%		
Response time	100 msecs		
Operation	Continuous duty		
Output contacts	SPDT 10 Amps at 240 VAC resistive		
Expected relay life	Mech: 10 million operations Elec: 100,000 operations at rated load		
Operating temperature	-40° to +131° F		
Humidity tolerance	0 - 97% without condensation		
Enclosure material	ABS plastic		
Mounting	8-pin socket (**order separately)		
Weight	5 oz.		
Agency approval	Most AC & DC Auto Reset versions: UL Recognized* and CSA Certified*		
	* condition of acceptability: Units receiving input voltages of 300 volts or more must use a UL Recognized 600V socket, like Time Mark's 8-pin Model # 51X120.		
	# Exception: Models listed with # do not have agency approval		

Voltage	G NON-	STANDARD VERS Adjustment	Reset	Setpoint or Range	
DC	260	A=factory calibrated	M=manual reset	xxx or	
AC		B =screwdriver adjust	or auto reset	xxx-xxx	
			is assumed		
example: AC260 AM 230 orders an AC voltage sensor with manual reset, factory calibrated to trip at 230vac					

Telephone: Main - (918) 438-1220 Sales - (800) 862-2875

Fax: (918) 437-7584

E-mail: sales@time-mark.com Internet: http://www.time-mark.com



11440 East Pine Street Tulsa, Oklahoma 74116

Doc No. 87A133 12/05 © 2005 TIME MARK CORPORATION



MODEL 260 Voltage Sensor

READ ALL INSTRUCTIONS BEFORE INSTALLING, OPERATING OR SERVICING THIS DEVICE.

KEEP THIS DATA SHEET FOR FUTURE REFERENCE.

GENERAL SAFETY

POTENTIALLY HAZARDOUS VOLTAGES ARE PRESENT AT THE TERMINALS OF THE MODEL 260.
ALL ELECTRICAL POWER SHOULD BE REMOVED WHEN CONNECTING OR DISCONNECTING WIRING.
THIS DEVICE SHOULD BE INSTALLED AND SERVICED BY QUALIFIED PERSONNEL.

Installation Instructions

INSTALLATION

Mount the unit in a suitable enclosure. A NEMA-1 enclosure, designed for socket-mounted relays is available from Time Mark.

Connect the voltage to be monitored to terminals 6 and 7. These terminals are not polarity sensitive for any of the listed AC or DC models.

WARNING

IN APPLICATIONS WHERE VOLTAGES IN EXCESS OF 300 VAC ARE TO BE MONITORED, BE CERTAIN TO USE THE **TIME MARK MODEL 51X120** 8-PIN SOCKET, OR AN EQUIVALENT UL APPROVED 600VAC RATED SOCKET.

Connect the load control wiring to the appropriate terminals on the socket:

For motor control applications; use terminals 1 and 8. For phase loss alarm applications; use terminals 1 and 2.

Insert the Model 260 into the socket and apply power. If the contact does not transfer (*green light ON*), use a voltmeter to insure that the proper voltage is present. If voltage is correct, rotate the level adjustment fully counter-clockwise. The contact should transfer to provide a signal path between pins 1 and 8.

NOTE: When installing the Model 260 Sensor in areas of high humidity or contamination, it is recommended that the base area and all exposed metal parts of the socket be coated liberally with a good quality silicon grease, such as Dow Corning DC-4 or DC-4X. Insert the unit into the socket and wipe off excess grease around the base. This will prevent the entrance of moisture and other contaminates into the base and socket areas.

ADJUSTMENT PROCEDURE


The following procedure will allow the Model 260 Voltage Sensor to be adjusted to achieve a trip point just below the nominal voltage being monitored.

Rotate the adjustment control fully clockwise, or until the red (TRIP) indicator illuminates.


On manual reset versions, it will be necessary to hold the reset button down during this next step:

Slowly rotate the adjustment control in a counter-clockwise direction, just until the green (NORM) indicator comes on.


DIMENSIONS



PIN DIAGRAM



TYPICAL APPLICATION



Shows No Power Applied

At this point, the Model 260 Voltage Sensor is the most sensitive to irregular power line conditions. If nuisance tripping occurs, turn the control slightly farther counter-clockwise.

A more accurate setting will require the use of an adjustable voltage source, and a voltmeter to achieve an exact setting.

TROUBLESHOOTING

Should the Model 260 Voltage Sensor fail to operate properly, check that proper voltage is being applied to pins 6 and 7. **On manual reset versions**, place a jumper across pins 3 and 4 if an external, normally-closed reset switch is not connected. Should problems persist, contact your local Time Mark Distributor, or the factory at 800-862-2875 (Monday-Friday; 8 a.m. to 5 p.m. CST), for further assistance.

WARRANTY

The **Model 260 Voltage Sensor** is warranted to be free from defects in materials and workmanship, and is covered by our exclusive **5-year Unconditional Warranty**. If the Model 260 fails to operate, for any reason, we will repair or replace it free, for five years from the date of purchase. Contact the Time Mark Sales department, Monday through Friday; 8 a.m. to 5 p.m., CST, for further details.

Telephone: Main - (918) 438-1220 Sales - (800) 862-2875

Fax: (918) 437-7584

E-mail: sales@time-mark.com Internet: http://www.time-mark.com



11440 East Pine Street Tulsa, Oklahoma 74116

Doc No. 87A133 12/05 © 2005 TIME MARK CORPORATION

