BT2S-C



| T | | Profinition use Dome-top head features unique pater Stainless steel locking barb provides of through entire bundle range High strength and low thread force Curved tip is easy to pick up from flat installation (Light-Heavy cross section to | | | | | | | |
|---|--|--|--|--|--|--|--|--|--|
| | Part Number | BT2S-C | | | | | | | |
| | RoHS Compliancy Status | Compliant | | | | | | | |
| | Part Description | Cable Tie with metal barb, 8.0", Standard cross section | | | | | | | |
| | Product Type | Cable Ties | | | | | | | |
| | Material | Nylon 6.6 | | | | | | | |
| | ■ Color | Natural | | | | | | | |
| | CSA Certified | Yes | | | | | | | |
| | Mil. Std. Part Number | MS3367-1-9 | | | | | | | |
| | UL Listed (File #E56854) | Yes | | | | | | | |
| | UL Recognized (File #E56854) | Yes | | | | | | | |
| | ▪ Length (In.) | 8.0 | | | | | | | |
| | ■ Length (mm) | 203 | | | | | | | |
| | ■ Width (In.) | .185 | | | | | | | |
| | Width (mm) | 4.7 | | | | | | | |
| | CE Compliant | Yes | | | | | | | |
| | Cross Section | Standard | | | | | | | |
| | Head Height (In.) | .220 | | | | | | | |
| | Head Height (mm) | 5.6 | | | | | | | |
| | Head Width (In.) | .320 | | | | | | | |
| | Head Width (mm) | 8.1 | | | | | | | |
| | Locking Style | Locking | | | | | | | |
| | Material Flammability Rating | UL 94V-2 | | | | | | | |
| | Max. Bundle Diameter (In.) | 2.00 | | | | | | | |
| | | | | | | | | | |

 Max. Bundle Diameter (mm) 51

Max. Continuous Use Temperature 185°F (85°C)

- For indoor use
 - e patented design with round, smooth edges
 - ovides consistent performance, reliability and infinite adjustability
 - orce
 - rom flat surfaces and allows faster initial threading to speed section ties have a straight tip)

| Min. Loop Tensile Strength (Lbs.) | 50 | | | | | | |
|---|--|--|--|--|--|--|--|
| Min. Loop Tensile Strength (N) | 222 | | | | | | |
| Pricing Description | Cable Tie, Metal Barb, 8.0"L (203mm), Standard, Nylon, Natural | | | | | | |
| Thickness (In.) | .045 | | | | | | |
| Thickness (mm) | 1.1 | | | | | | |
| ■ Tool | GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2 | | | | | | |
| Min. Order UOM | PC | | | | | | |
| Min. Order Qty. | 100 | | | | | | |
| BOM Qtv. (# of Pkas.) | | | | | | | |

BOM Qty. (# of Pkgs.)

| | THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. | | | | | | | | | | | | | | | | | | | |
|--|--|---|------|---|--------------|---------------|---------------|---------------|---------------|-----------------------|--------------------------------|------------------------------|--|--------------|------------------------|------------|-------------|--------------|--|--|
| | ļ | B±.01(.25) | | | | | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | | | | | | | |
| | FREF. | | | | | | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | - A±.01(.25) | | | | | | |
| | | | | | | | | | | | | | V | | | | | | | |
| | | | | | | | | | | | | 4 | | | | | | | | |
| | I | | | | | | | | | | | | Ι | | | | | | | |
| | | PANDUIT BUNDLE DIA. A B C D E | | | | | | | | | | | | F | MIN. LOOP CROSS WEIGHT | | | | | |
| | | PARI NU. MIN. (mm) MAX. (mm) in (mm) in (| | | | | in (mm | | _ | (mm) | in (mm | | (mm) | | | SECTION | (g) | | | |
| | | | | | | | .141 (3.6 | .142 (3.6) | | 185 1.7) | .248 (6.3 |) (| 5.1 155) | 40 (178) | INTERMEDIATE | | .12 (56) | | | |
| | | BT2I | | .03 (0.8) | 2.00 (51) | .041 (1.0) | .141 (3.6 | .142 (3.6) | | .185 .24 (4.7) (6. | | | 8.0 203) | 40 (178) | | | .16 (72) | | | |
| | | BT3I | | | .03 (0.8) | 3.00 (76) | .049 (1.2) | .141 (3.6 | .142 (3.6) | | 185 1.7) | .248 (6.3 | | 1.3 287) | 40 (178) | INT | ERMEDIATE | .27 (121) | | |
| | | | BT4I | | .03 (0.8) | 4.00 (102) | .049 (1.2) | .141 (3.6 | .142 (3.6) | | 185 1.7) | .248 (6.3 | | 4.3 363) | 40 (178) | INT | ERMEDIATE | .35 (156) | | |
| | | | ΒT | 25 | .06 (1.5) | 2.00 (51) | .045 (1.2) | .185 (4.7 | | | .220 .320 (5.6) (8.1) | | | 3.0 203) | 50 (222) | S | TANDARD | .25 (113) | | |
| | | | BT: | 35 | .06 (1.5) | 3.00 (76) | .052 (1.3) | .185 (4.7 | .205 | | 220 5.6) | .320 (8.1) | | 2.0 305) | 50 (222) | S | TANDARD | .40 (183) | | |
| | | | ΒT | 4S | .06 (1.5) | 4.00 (102) | .052 (1.3) | .185 (4.7 | | .5 | 220 5.6) | .320 (8.1 | | 5.1 384) | 50 (222) | | | .51 (230) | | |
| DIMENSIONS IN PARENTHESES ARE IN METRIC UNIT | | | | | | | | | | | | | rs | | | | | | | |
| | | | | | | | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | CORP. TINLEY PARK, ILLINOIS | | | | | | | |
| | | | | | | | | | | | | | DOME-TOP Barb Ty CABLE TIES | | | | | | | |
| | | | | | | | | | | | BT SERIES | | | | | | | | | |
| | | | | | | | | | | | | | UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±.10(2.5)(.XXX) ±.020(.51) (.XX) ±.02(.5) ANGLES ± IN INCHES, THIRD ANGLE P | | | | | VEN | | |
| | | | | | | | | | | | | DRAWN BY PMH MAT'L: SCALE | | | | | | | | |
| 9 | 5/2/06 | Лаво | | REMOVED STRAIGHT TIP REFERENCE & 0037 9 | | | | | | | DATE 6-24-93 NYLON 6.6 BT-0 | | | | | Dwg 7 A | | | | |
| REV | DATE | вγ | снк | | | ECN - | R | сият | SUP | | снк • р | VL | | | SHT. 2 OF | | | | | |