	u	su	upport locate distributor about panduit	careers worldwide
	JUIT World Leader i	n Network and E	lectrical Solutions	Printer Friendly
	ESOURCES PRODUCTS SERVICE		SEARCH	
Current refinements	(click 🗙 to remove)			Search Tips 👩
🔀 Region 🕨 USA 🔀 Pr	oduct Family) Ring Terminal, Vinyl Inst			
	Your search crite	eria matched only one product, s	shown below.	
	 Ring tongue of Brazed seam UL Flammabi Internal barre UL and CSA ‡UL and CSA 	oport helps to prevent wire damage design assures a secure connectio protects terminal barrel from splitti ility UL 94V-0, maximum insulation el serrations assure good wire conta rated up 600 V per UL 486 approved tooling/product combinat es #26 – #22 AWG, are not UL List	n in high vibration applications ing during the crimp process temperature 221°F (105°C) act and maximum tensile strength tions.	
Part Number:	PV14-10R-C			
RoHS Compliancy Status:	Compliant			
Part Description:	Ring Terminal, 16 – 14 AWG, #10 stud	size, vinyl insulated, funnel entry.		
Product Type:	Terminals			
CSA Certified:	Yes			
UL Listed:	Yes			
Length (In.):	.92			
Length (mm):	23.4			
Width (In.):	.31			
Width (mm):	7.87			
Clearance:	.25			
Max. Ins.:	.170			
Panduit Color Code:	Blue			
Stock:	.03			
Stud Size:	#10			
Tool:	CT-100A‡, CT-600-A‡, CT-1550‡, CT-1	1551‡, CT-2500‡		
Wire Range:	16 – 14 AWG			
Min. Order UOM:	PC			
Min. Order Qty.:	100			
BOM Qty. (# of Pkgs.)				
Add to My Catalog				
	Please register to utilize the	'Bill of Materials', 'Submit Quotes' a	and 'My Catalog' features.	

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

-H DIA

TERMINAL

HOUSING

BRAZED SEAM

FUNNEL WIRE ENTRY

TINLEY PARK, ILLINOIS

A41184

DRAWING NO.

SCALE

NONE

DRAWN BY

FES

ECN #

CUST

PM

CHK 'D

PANDUIT	STUD	DIMENSIONS in.					◄──── ₩ ───►				
	SIZE	A ^{±.03} W	N ±.01	C ^{±.02}	M ±.03	H ±.01		4			
PV14-4R -C -M	#4		.25 (6.4)	.19 (4.8)	.71 (18.0)	.12 (3.1)					
PV14-6RN -C -M	#6	.84 (21.3) (.25 (6.4)	.19 (4.8)	.71 (18.0)	.15 (3.8)		-			
PV14-6R -C -M	#6	.92 (23.4) (.31 (7.9)	.25 (6.4)	.76 (19.3)	.15 (3.8)					
PV14-8R -C -M	#8	.92 (23.4) (.31 (7.9)	.25 (6.4)	.76 (19.3)	.17 (4.3)					
PV14-10R -C -M	#10	.92 (23.4) (.31 (7.9)	.25 (6.4)	.76 (19.3)	.20 (5.1)		A	C RAD		
PV14-14R -C -M	1/4"	1.12 (28.5) (.46 11.7)	.38 (9.7)	.89 (22.6)	.27 (6.9)					
PV14-56R -C -M	5/16"	1.12 (28.5) (.46 11.7)	.38 (9.7)	.89 (22.6)	.34 (8.6)					
PV14-38R -L -M	3/8"	1.21 (30.7) (.43 (10.9)	.94 (23.9)	.40 (10.2	1		BR		
PV14-12R -L	1/2"	1.42 (36.1) (:	.72 18.3) (.53 13.5)	1.06 (26.9)	.52 (13.2			s s		
A. B. C. 2. MA A. B. 3. STF 4. PAC	600 V. N (1000 V. AND LUM 18-14 AV COPPER V TEMP RA CT-550, 16-14 AV COPPER V TEMP RA INSTALL/ TERIAL: STAMPINI HOUSING RIP LENGT XAGE OTY	STD PKG	E RATING IGNS, FIX STRANDED (105°C) IN STRANDED (75°C) M HE CT-100 8) THK CC LUE -L=50 G-C=100 (G-M=1000	MAX 0 & STALLAT AX DPPER, T	IN PLATED		CERTIF	M/ IN	70 (4.3) AX. WIRE ISUL. DIA LISTED 587H E52164 A41184_05		
12/02SAC	FOR PV M WAS	14-12R DIN 1.05	M A WAS	1.41 8	S. DIM				CORP. TINLEY PAR		
	HANGED	(DIMS.)T	FO 1 PL	ACE D	ECIMAL	10231	LA	TRO	2PC. VINYL INSULATED,		
4/02 SRBSKB		ADDED P	PV14-12	2R		10171	LA	TRO	#16-14 BARREL, RINGS		

05

04

0З

REV

DATE

BY

CHK

DESCRIPTION